



FIBER MANAGEMENT

EFA52 03 ASS

Quick Panel Mount Strain Relief
Gland, Slot in Version



A Europlus/Richco Product

Material: Flame Retardant Nylon 6 UL94 VO, RMS-178; Color: Black
Standard Pack: 250 per bag
EFA52 03 ASS
All dimensions in millimeters


OFCC/OFCG

Optical Fiber Coiling Clip



Features

- Two extruded clips snap into each other to form a clip with a smooth, curved surface to accommodate fiber optic bundles
- Wall thickness: .070 (1.8) typical



TYPICAL ASSEMBLY

Fig. 1





Fig. 2




Material: Rigid PVC, RMS-04; Adhesive, RMS-15; Color: Black
Standard Pack: 100 per bag

Part Number	Figure
OFCC-16-A-RT	1
OFCG-16	2



OFCP-50-19

Chain Plate



Features

- Connect multiple OFCP's together to form a "chain" for routing fiber
- Complete the circle for an excess fiber spool to form a "Y" for breakout points
- All connections maintain a bend radius greater than 30mm
- Ø4.75mm center mounting hole to fit any standard Richco routing component



Material: Flame Retardant Nylon 6/6 UL94 VO; RMS-19; Color: White

Standard Pack: 500 per bag

OFCP-50-19

All dimensions in millimeters