





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC.. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	INITIAL RELEASE	12/9/04	T.CLARK
B	ECN# 2731 - UPDATE DRAWING FORMAT	10/22/07	D.GRIFFIN
C	ECN 3174: REVISED FINISH TO NICKEL PLATE	2/4/08	D.FRISIELLO



NOTES:

MATERIAL:

HOOD: DIE-CAST ZINC ALLOY
JACKSCREWS: STEEL
ASSEMBLY HARDWARE: STEEL
STRAIN RELIEF GROMMETS: PVC BLACK


FINISH:

HOOD: NICKEL PLATED, MATTE FINISH ON MAJOR SURFACES
JACKSCREWS: NICKEL PLATED
ASSEMBLY HARDWARE: NICKEL PLATED

MISCELLANEOUS:

INTENDED FOR USE WITH 9-PIN STANDARD AND 15-PIN HIGH DENSITY D-SUBMINIATURE CONNECTORS.
SUPPLIED WITH 5 STRAIN RELIEF GROMMETS FOR CABLES HAVING DIAMETERS RANGING FROM .190 TO .335 INCH.

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES [mm]
TOLERANCES TO BE:
.X ±.1 [2.5] ANGLES ±2°
.XX ±.01 [.25]
.XXX ±.005 [.13]
OVERALL CABLE LENGTH TOL:
≤ 60 [1524] +3 [76.2] / -0
> 60 [1524] +5% / -0%



APPROVALS	DATE
DRAWN BY T CLARK	12/6/2004
CHECKED BY D PARHAM	12/7/2004
APPROVED BY C MCCORMICK	12/8/2004

CONFIGURATION DETAILS OF
UNDIMENSIONED FEATURES
MAY VARY

L-com
CONNECTIVITY
PRODUCTS

45 BEECHWOOD DRIVE
NORTH ANDOVER, MA
01845

CATEGORY	DATA CABLING		
PRODUCT DESCRIPTION	DB9 & HD15 HOOD KIT		
SIZE A	FSCM NO. 43321	DWG. NO. SDC9AG	REV. C
SCALE: NONE CAD FILE: SDC9AG.SLDDRW SHEET 1 OF 1			