


PANDUIT PART NO.	PACKAGE QTY	MAX BUNDLE DIAMETER	LENGTH "L" $\pm .3$ [7]
MLT2H-LP	50	2" [51]	7.9" [201]
MLT2.7H-LP	50	2.7" [69]	10.2" [259]
MLT4H-LP	50	4" [102]	14.3" [362]
MLT6H-LP	50	6" [152]	20.5" [521]
MLT8H-LP	50	8" [203]	26.8" [679]
MLT10H-LP	50	10" [254]	33.0" [838]
MLT12H-Q	25	12" [304]	39.3" [998]
MLT14H-Q	25	14" [355]	45.5" [1156]
MLT2H-TL	250	2" [51]	7.9" [201]
MLT4H-TL	250	4" [102]	14.3" [362]



NOTES:

1. APPLICATION TOOLS - GS4MT, PPTMT, ST2MT, ST3MT, HTMT
2. MINIMUM LOOP TENSILE STRENGTH - 450 LBS. (2000 NEWTONS)
WHEN TESTED ON A 1.5" MANDREL.
3. BRACKETS [] DENOTE DIMENSIONS IN MILLIMETERS, AND ARE
SHOWN FOR REFERENCE ONLY
4. TOLERANCES:
.XXX = $\pm .010$ [.25] .XX = $\pm .02$ [.5]
.X = $\pm .03$ [.8] ANGLES = $\pm 2^\circ$
5. MATERIAL: 304 STAINLESS STEEL

FULLY ROUNDED
EDGES ALONG
STRAP BODY

SECTION A-A
SCALE 6:1

						PANDUIT TM	TINLEY PARK, ILLINOIS
						METAL LOCKING TIE HEAVY SERIES - 304 STAINLESS STEEL - CUSTOMER DRAWING -	
06A	2/12	MIM	RGRO	NOTE #3 METRIC DIMENSIONS NOTED AS BEING SHOWN FOR REFERENCE ONLY			
REV	DATE	BY	CHK	DESCRIPTION		DRAWN BY JAMB	CHK'D DPN
						SCALE 2x	DRAWING NO. N41115BS_DC