


## SMD POWER INDUCTORS





### • Features

1. Open frame construction
2. Excellent Power Density
3. Engineered to Provide High Efficiency

## ELECTRICAL CHARACTERISTICS



| Part Number | Inductance<br>(uH)<br>(1) | Test<br>Frequency | DC Resistance<br>(Ω MAX)<br>(2) | Saturation<br>Current <sup>(3)</sup><br>(A) | Temperature<br>Current <sup>(4)</sup><br>(A) |
|-------------|---------------------------|-------------------|---------------------------------|---------------------------------------------|----------------------------------------------|
| SCB75F-1R0  | 1.0                       | 1KHZ              | 23m                             | 2.88                                        | 5.50                                         |
| SCB75F-1R5  | 1.5                       | 1KHZ              | 28m                             | 2.56                                        | 5.00                                         |
| SCB75F-2R2  | 2.2                       | 1KHZ              | 32m                             | 2.36                                        | 4.20                                         |
| SCB75F-3R3  | 3.3                       | 1KHZ              | 38m                             | 2.16                                        | 3.80                                         |
| SCB75F-4R7  | 4.7                       | 1KHZ              | 49m                             | 1.88                                        | 3.50                                         |
| SCB75F-6R8  | 6.8                       | 1KHZ              | 60m                             | 1.68                                        | 3.24                                         |
| SCB75F-100  | 10                        | 1KHZ              | 70m                             | 1.56                                        | 2.70                                         |
| SCB75F-120  | 12                        | 1KHZ              | 80m                             | 1.44                                        | 2.50                                         |
| SCB75F-150  | 15                        | 1KHZ              | 90m                             | 1.36                                        | 2.30                                         |
| SCB75F-180  | 18                        | 1KHZ              | 0.10                            | 1.28                                        | 2.10                                         |
| SCB75F-220  | 22                        | 1KHZ              | 0.12                            | 1.17                                        | 1.90                                         |
| SCB75F-270  | 27                        | 1KHZ              | 0.14                            | 1.07                                        | 1.70                                         |
| SCB75F-330  | 33                        | 1KHZ              | 0.18                            | 1.00                                        | 1.55                                         |
| SCB75F-390  | 39                        | 1KHZ              | 0.21                            | 0.91                                        | 1.40                                         |
| SCB75F-470  | 47                        | 1KHZ              | 0.25                            | 0.84                                        | 1.30                                         |
| SCB75F-560  | 56                        | 1KHZ              | 0.29                            | 0.72                                        | 1.22                                         |
| SCB75F-680  | 68                        | 1KHZ              | 0.34                            | 0.66                                        | 1.14                                         |
| SCB75F-820  | 82                        | 1KHZ              | 0.46                            | 0.58                                        | 1.00                                         |
| SCB75F-101  | 100                       | 1KHZ              | 0.55                            | 0.51                                        | 0.85                                         |
| SCB75F-121  | 120                       | 1KHZ              | 0.67                            | 0.42                                        | 0.78                                         |
| SCB75F-151  | 150                       | 1KHZ              | 0.90                            | 0.37                                        | 0.68                                         |
| SCB75F-181  | 180                       | 1KHZ              | 1.05                            | 0.35                                        | 0.60                                         |
| SCB75F-221  | 220                       | 1KHZ              | 1.35                            | 0.29                                        | 0.50                                         |
| SCB75F-271  | 270                       | 1KHZ              | 1.55                            | 0.28                                        | 0.47                                         |
| SCB75F-331  | 330                       | 1KHZ              | 2.05                            | 0.23                                        | 0.44                                         |
| SCB75F-391  | 390                       | 1KHZ              | 2.30                            | 0.215                                       | 0.41                                         |
| SCB75F-471  | 470                       | 1KHZ              | 2.60                            | 0.195                                       | 0.38                                         |



- (1). Inductance tolerance for 1.0uH~3.3uH:  $\pm 30\%$ , for 4.7uH~100uH:  $\pm 20\%$ , for 120uH~470uH:  $\pm 10\%$ . Tested at 0.25V, 0ADC and 25°C.
- (2). DCR measured at 25°C.
- (3). The DC current at which the inductance decreases by 10% from its initial value.
- (4). The DC current that results in a 40°C temperature rise from 25°C ambient.

[Click here for QUANTITY PER REEL & PACKING INFORMATION](#)

**Custom versions available upon request.**

©2011 Signal Transformer – Specification subject to change without notice. 07.11