


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
CM	00		F4	REVISED PER ECO-11-004820	11MAR11	RK HMR

- 1 WIRE RANGE: 0.13–0.32mm² (26–22 AWG).
- 2 INSULATION RANGE: 1.20–1.75 DIA.
- 3

FINISH: 0.76 MIN GOLD OVER 1.27µm MIN NICKEL REQUIRED ON INNER SURFACE, PERMITTED ON OUTER SURFACE.
- 4

FINISH: 2.54µm MIN PRE-TIN ON ALL SURFACES IN THIS AREA.
- 5

FINISH: 2.54µm MINIMUM PRE-TIN ALL OVER.



SECTION A–A

SECTION B–B

SECTION C–C

GOLD 3 4	PHOS. BRZ.	794958–4
PRE-TIN 5	PHOS. BRZ.	794958–3
GOLD 3 4	BRASS	794958–2
PRE-TIN 5	BRASS	794958–1
FINISH:	MATERIAL:	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HAMM 10-SEP-2001		TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK D. COLEY 10-SEP-2001				
		APVD D. COLEY 10-SEP-2001		NAME TERMINAL SOCKET VAL – U – LOK(TM)		
		PRODUCT SPEC				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC		SIZE A2		
0 PLC ± 1 PLC ± 0.15 [.006] 2 PLC ± 0.10 [.004] 3 PLC ± 0.050 [.0020] 4 PLC ± ANGLES ±		WEIGHT				
MATERIAL		FINISH		DRAWING NO C=794958		
		CUSTOMER DRAWING		RESTRICTED TO —		
				SCALE 10:1		
				SHEET 1 of 1		
				REV F4		

