

## Lower Voltage Disc Capacitors

### 12V TO 1KV

Lower Voltage Capacitors are stocked in distribution. See "Packaging Options" section for other electrical and mechanical options, including Tape & Reel.

Fig 1




Fig 2





Fig 3



#### STANDARD WIRE SIZE:

- C and E Sizes - 24 gauge (.020") Tinned Copper Clad Steel Wire.
- F through Q Sizes - 22 gauge (.025") Tinned Copper Wire.

#### TAPE & REEL OPTIONS:

- Tape & Reel available on diameter sizes .250" to .680".
- To specify T & R, add two letter suffix to catalog number for example: TGS10 QA-suffix describes alternate wire lead forms & lead spacing options - see complete description in "Packaging Options" section.
- 10,000 piece minimum shipment for T & R.

| SIZE<br>CODE   | DIAMETER<br>"D" MAX |      | THICKNESS<br>"T" MAX |     | LEAD SPACING<br>"LS" FIG 1 & 3 |     |
|----------------|---------------------|------|----------------------|-----|--------------------------------|-----|
|                | in                  | mm   | in                   | mm  | in                             | mm  |
| C              | .250                | 6.4  | .156                 | 4.0 | .250                           | 6.4 |
| E              | .290                | 7.4  | .156                 | 4.0 | .250                           | 6.4 |
| E <sub>7</sub> | .330                | 8.4  | .156                 | 4.0 | .250                           | 6.4 |
| F              | .370                | 9.4  | .156                 | 4.0 | .250                           | 6.4 |
| F <sub>7</sub> | .400                | 10.2 | .156                 | 4.0 | .250                           | 6.4 |
| G              | .440                | 11.2 | .156                 | 4.0 | .250                           | 6.4 |
| G <sub>7</sub> | .460                | 11.7 | .156                 | 4.0 | .250                           | 6.4 |
| H              | .490                | 12.4 | .156                 | 4.0 | .250                           | 6.4 |
| H <sub>3</sub> | .490                | 12.4 | .156                 | 4.0 | .375                           | 9.5 |
| H <sub>7</sub> | .530                | 13.5 | .156                 | 4.0 | .375                           | 9.5 |
| J              | .560                | 14.2 | .156                 | 4.0 | .375                           | 9.5 |

| SIZE<br>CODE | DIAMETER<br>"D" MAX |      | THICKNESS<br>"T" MAX |     | LEAD SPACING<br>"LS" FIG 1 & 3 |     |
|--------------|---------------------|------|----------------------|-----|--------------------------------|-----|
|              | in                  | mm   | in                   | mm  | in                             | mm  |
| K            | .630                | 16.0 | .156                 | 4.0 | .375                           | 9.5 |
| L            | .680                | 17.3 | .156                 | 4.0 | .375                           | 9.5 |
| M            | .760                | 19.3 | .156                 | 4.0 | .375                           | 9.5 |
| P            | .890                | 22.6 | .156                 | 4.0 | .375                           | 9.5 |
| R            | .510                | 13.0 | .200                 | 5.1 | .375                           | 9.5 |
| T            | .580                | 14.7 | .200                 | 5.1 | .375                           | 9.5 |
| U            | .640                | 16.3 | .200                 | 5.1 | .375                           | 9.5 |
| W            | .700                | 17.8 | .200                 | 5.1 | .375                           | 9.5 |
| X            | .770                | 19.6 | .200                 | 5.1 | .375                           | 9.5 |
| Y            | .900                | 22.9 | .200                 | 5.1 | .375                           | 9.5 |
| Q            | .950                | 24.1 | .200                 | 5.1 | .375                           | 9.5 |

| VOLTAGE<br>CLASS | LEAD OFFSET<br>"LO" (nom) |     |
|------------------|---------------------------|-----|
|                  | in                        | mm  |
| 100              | .040                      | 1.0 |
| 500              | .040                      | 1.0 |
| 1000             | .050                      | 1.3 |

### 12/25/50/100V HYPERCON CONSTRUCTION HIGH-CAPACITANCE DISCS

- Application:  
Low Voltage Bulk Filter

| 12 VDC, Y5R, 2.5ΩF, 5% DF |         |        |        |      |
|---------------------------|---------|--------|--------|------|
| VALUE                     | CATALOG | SIZE   |        |      |
| μF                        | TOL.    | NUMBER | FIGURE | CODE |
| .05                       | Y       | HY105  | 3      | E    |
| .10                       | M       | HY110  | 1      | G    |
| .22                       | M       | HY122  | 1      | J    |
| .47                       | M       | HY147  | 1      | P    |

| 25 VDC, Y5R, 5ΩF, 5% DF |         |        |        |      |
|-------------------------|---------|--------|--------|------|
| VALUE                   | CATALOG | SIZE   |        |      |
| μF                      | TOL.    | NUMBER | FIGURE | CODE |
| .01                     | M       | HY820  | 3      | C    |
| .022                    | M       | HY825  | 3      | E    |
| .033                    | M       | HY530  | 3      | E    |
| .047                    | M       | HY835  | 3      | F    |
| .10                     | M       | HY850  | 1      | G    |

| 50 VDC, Y5R, 25ΩF, 4% DF |         |        |        |      |
|--------------------------|---------|--------|--------|------|
| VALUE                    | CATALOG | SIZE   |        |      |
| μF                       | TOL.    | NUMBER | FIGURE | CODE |
| .01                      | M       | HY920  | 3      | C    |
| .022                     | M       | HY925  | 3      | E    |
| .047                     | M       | HY935  | 1      | G    |
| .10                      | M       | HY950  | 1      | H    |

| 100 VDC, Y5S, 100ΩF, 3% DF |         |        |        |      |
|----------------------------|---------|--------|--------|------|
| VALUE                      | CATALOG | SIZE   |        |      |
| μF                         | TOL.    | NUMBER | FIGURE | CODE |
| .0022                      | M       | HMMD22 | 2      | C    |
| .0047                      | M       | HMMD47 | 2      | C    |
| .01                        | M       | HMMS10 | 3      | E    |
| .10                        | M       | HMMP10 | 1      | L    |

### 100 VOLT GENERAL PURPOSE

- Application Range:  
Up to 250 VDC, 75 VAC RMS\*\*

| VALUE | CATALOG | SIZE   |        |      | TEMP.<br>COEF. |
|-------|---------|--------|--------|------|----------------|
| μF    | TOL.    | NUMBER | FIGURE | CODE |                |
| 10    | D       | TSQ10  | 2      | C    | NP0            |
| 22    | J       | TSQ22  | 2      | C    | NP0            |
| 33    | K       | TSQ33  | 2      | C    | U2J            |
| 47    | K       | TSQ47  | 2      | C    | U2J            |
| 100   | K       | TST10  | 2      | C    | X7R            |
| 220   | K       | TST22  | 2      | C    | X7R            |
| 330   | K       | TST33  | 2      | C    | X7R            |

- Insulation Resistance: 10,000 MΩ minimum, 500ΩF
- Dissipation Factor: 3.0% maximum

| VALUE  | CATALOG | SIZE   |        |      | TEMP.<br>COEF. |
|--------|---------|--------|--------|------|----------------|
| μF     | TOL.    | NUMBER | FIGURE | CODE |                |
| 470    | K       | TST47  | 2      | C    | X7R            |
| 1000   | K       | TSD10  | 2      | C    | X7R            |
| 2200   | K       | TSD22  | 2      | F    | X7R            |
| 3300   | K       | TSD33  | 2      | F    | X7R            |
| 4700   | K       | TSD47  | 2      | G    | X7S            |
| 6800   | K       | TSD68  | 2      | H    | X7S            |
| 0.01μF | K       | TSS10  | 2      | J    | X7S            |

| VALUE | CATALOG | SIZE   |        |      | TEMP.<br>COEF. |
|-------|---------|--------|--------|------|----------------|
| μF    | TOL.    | NUMBER | FIGURE | CODE |                |
| .005  | M       | TGD50  | 1      | E    | Z5U            |
| .01   | M       | TGS10  | 1      | F    | Z5U            |
| .02   | M       | TGS20  | 1      | G    | Z5U            |
| .022  | M       | TSS22  | 1      | T    | X7S            |
| .047  | M       | TGS47  | 1      | R    | Z5U            |
| .050  | M       | TGS50  | 1      | R    | Z5U            |
| .10   | M       | TGP10  | 1      | W    | Z5U            |

\*\* See "Application Data" section for limits on AC voltage.



# GA, HK, HM, HY, TC, TG, TS Series

## Lower Voltage Disc Capacitors

## Vishay Cera-Mite

### 500 VOLT GENERAL PURPOSE

- Application Range:  
Up to 600 VDC, 100 VAC RMS\*\*

- Insulation Resistance: 15,000 M $\Omega$  minimum, 750 $\Omega$ F
- Dissipation Factor: 3.0% maximum

### 562C Series

- Dielectric Strength:  
1500 VDC, 300 VAC RMS

| VALUE |      | CATALOG NUMBER | SIZE |      | TEMP. COEF. |
|-------|------|----------------|------|------|-------------|
| pF    | TOL. |                | FIG. | CODE |             |
| 1000  | K    | 5TSD10         | 3    | E    | X7R         |
| 1000  | M    | 5TSSD10        | 3    | C    | Y5U         |
| 1500  | K    | 5TSD15         | 3    | F    | X7R         |
| 2200  | K    | 5TSD22         | 3    | F    | X7R         |
| 3300  | K    | 5TSD33         | 1    | G    | X7R         |
| 4700  | K    | 5TSD47         | 1    | H    | X7R         |
| 5000  | Z    | 5TSD50         | 1    | F    | Z5U         |

| VALUE   |      | CATALOG NUMBER | SIZE |      | TEMP. COEF. |
|---------|------|----------------|------|------|-------------|
| $\mu$ F | TOL. |                | FIG. | CODE |             |
| .0068   | K    | 5TSD68         | 1    | H    | X7S         |
| .01     | K    | 5TSS10         | 1    | J    | X7S         |
| .01     | M    | 5GASS10        | 1    | G    | Z5U         |
| .01     | Z    | 5HKSS10        | 1    | G    | Z5U         |
| .02     | M    | 5GASS20        | 1    | J    | Z5U         |
| .022    | M    | 5TSS22         | 1    | L    | X7S         |
| .033    | M    | 5TSS33         | 1    | X    | X7S         |

| VALUE   |      | CATALOG NUMBER | SIZE |      | TEMP. COEF. |
|---------|------|----------------|------|------|-------------|
| $\mu$ F | TOL. |                | FIG. | CODE |             |
| .05     | M    | 5GAS50         | 1    | P    | Z5U         |
| .05     | Z    | 5HKS50         | 1    | T    | Z5U         |
| .10     | M    | 5GAP10         | 1    | X    | Z5U         |
| .10     | Y    | 5HKSP10        | 1    | Q    | Y5V         |
| .10     | Z    | 5HKP10         | 1    | X    | Z5U         |
| .15     | Y    | 5GAP15         | 1    | Y    | Z5U         |
| .20     | M    | 5GAP20         | 1    | Q    | Z5U         |

### 1000 VOLT GENERAL PURPOSE

- Application Range:  
Up to 1000 VDC, 150 VAC RMS\*\*

- Insulation Resistance: 20,000 M $\Omega$  minimum, 1000 $\Omega$ F
- Dissipation Factor: 2.5% maximum

### 562C Series

- Dielectric Strength:  
2500 VDC, 500 VAC RMS

| VALUE |      | CATALOG NUMBER | SIZE |      | TEMP. COEF. |
|-------|------|----------------|------|------|-------------|
| pF    | TOL. |                | FIG. | CODE |             |
| 10    | M    | 5GAQ10         | 3    | C    | NP0         |
| 20    | M    | 5GAQ20         | 3    | C    | NP0         |
| 33    | M    | 5GAQ33         | 3    | E    | U2J         |
| 47    | M    | 5GAQ47         | 3    | E    | U2J         |
| 100   | M    | 5GAT10         | 3    | C    | X5F         |
| 150   | M    | 5GAT15         | 3    | C    | X5F         |
| 200   | M    | 5GAT20         | 3    | C    | X5F         |
| 220   | M    | 5GAT22         | 3    | C    | X5F         |
| 330   | M    | 5GAT33         | 3    | C    | X5F         |
| 470   | M    | 5GAT47         | 3    | C    | X5F         |
| 500   | M    | 5GAT50         | 3    | C    | X5F         |

| VALUE |      | CATALOG NUMBER | SIZE |      | TEMP. COEF. |
|-------|------|----------------|------|------|-------------|
| pF    | TOL. |                | FIG. | CODE |             |
| 1000  | M    | 5GAD10         | 3    | E    | X7R         |
| 1000  | P    | 5HKD10         | 3    | E    | Y5U         |
| 1200  | M    | 5GAD12         | 3    | E    | Z5U         |
| 1500  | M    | 5GAD15         | 3    | E    | Z5U         |
| 2000  | M    | 5GAD20         | 3    | E    | Z5U         |
| 2200  | M    | 5GAD22         | 3    | E    | Z5U         |
| 2500  | M    | 5GAD25         | 3    | E    | Z5U         |
| 2700  | M    | 5GAD27         | 3    | E    | Z5U         |
| 3000  | M    | 5GAD30         | 3    | E    | Z5U         |
| 3300  | M    | 5GAD33         | 3    | E    | Z5U         |
| 4700  | M    | 5GAD47         | 1    | F    | Z5U         |

| VALUE        |      | CATALOG NUMBER | SIZE   |                | TEMP. COEF. |
|--------------|------|----------------|--------|----------------|-------------|
| pF           | TOL. |                | FIGURE | CODE           |             |
| 5000         | M    | 5GAD50         | 1      | F              | Z5U         |
| 6800         | M    | 5GAD68         | 1      | G              | Z5U         |
| 8200         | M    | 5GAD82         | 1      | G              | Z5U         |
| 0.01 $\mu$ F | M    | 5GAS10         | 1      | H <sub>3</sub> | Z5U         |
| .01          | M    | 5HKMS10        | 1      | H              | Z5U         |
| .01          | P    | 5HKS10         | 1      | H <sub>3</sub> | Z5U         |
| .015         | M    | 5GAS15         | 1      | J              | Z5U         |
| .020         | M    | 5GAS20         | 1      | L              | Z5U         |
| .050         | M    | 10HKS50        | 1      | X              | Z5U         |
| .10          | M    | 10GAP10        | 1      | Q              | Z5U         |
| .15          | M    | 10GAP15        | 1      | Q              | Y5V         |

### 1KV TEMP. & VOLTAGE STABILIZED, 10% TOL.

- Application Range:  
Up to 1250 VDC, 200 VAC RMS\*\*

- Insulation Resistance: 50,000 M $\Omega$  minimum, 1000 $\Omega$ F
- Dissipation Factor: 2.0% maximum

### 562C Series

- Dielectric Strength:  
2500 VDC, 750 VAC RMS

| VALUE<br>pF | CATALOG<br>NUMBER | SIZE |      | TEMP.<br>COEF. |
|-------------|-------------------|------|------|----------------|
|             |                   | FIG. | CODE |                |
| 10          | 10TSQ10           | 3    | C    | NP0            |
| 25          | 10TSQ25           | 3    | E    | NP0            |
| 27          | 10TSQ27           | 3    | C    | U2J            |
| 30          | 10TSQ30           | 3    | C    | U2J            |
| 33          | 10TSQ33           | 3    | E    | U2J            |
| 39          | 10TSQ39           | 3    | E    | U2J            |
| 47          | 10TSQ47           | 3    | E    | U2J            |
| 50          | 10TSQ50           | 3    | E    | U2J            |
| 56          | 10TSQ56           | 3    | C    | X5F            |
| 68          | 10TSQ68           | 3    | C    | X5F            |

| VALUE<br>pF | CATALOG<br>NUMBER | SIZE |      | TEMP.<br>COEF. |
|-------------|-------------------|------|------|----------------|
|             |                   | FIG. | CODE |                |
| 75          | 10TSQ75           | 3    | C    | X5F            |
| 82          | 10TSQ82           | 3    | C    | X5F            |
| 100         | 10TST10           | 3    | C    | X5F            |
| 120         | 10TST12           | 3    | C    | X5F            |
| 150         | 10TST15           | 3    | C    | X5F            |
| 180         | 10TST18           | 3    | C    | X5F            |
| 200         | 10TST20           | 3    | C    | X5F            |
| 220         | 10TST22           | 3    | C    | X5F            |
| 250         | 10TST25           | 3    | C    | X5F            |

| VALUE<br>pF | CATALOG<br>NUMBER | SIZE |      | TEMP.<br>COEF. |
|-------------|-------------------|------|------|----------------|
|             |                   | FIG. | CODE |                |
| 270         | 10TST27           | 3    | C    | X5F            |
| 300         | 10TST30           | 3    | C    | X5F            |
| 330         | 10TST33           | 3    | C    | X5F            |
| 390         | 10TST39           | 3    | C    | X5F            |
| 470         | 10TST47           | 3    | C    | X5F            |
| 500         | 10TST50           | 3    | C    | X5F            |
| 560         | 10TST56           | 3    | E    | X5F            |
| 680         | 10TST68           | 3    | E    | X5F            |
| 750         | 10TST75           | 3    | E    | X5F            |

| VALUE<br>pF | CATALOG<br>NUMBER | SIZE |                | TEMP.<br>COEF. |
|-------------|-------------------|------|----------------|----------------|
|             |                   | FIG. | CODE           |                |
| 820         | 10TST82           | 3    | E              | X5F            |
| 1000        | 10TSD10           | 3    | E              | X5F            |
| 1500        | 10TSD15           | 1    | G              | X5F            |
| 2000        | 10TSD20           | 1    | H <sub>3</sub> | X5F            |
| 2200        | 10TSD22           | 1    | H <sub>3</sub> | X5F            |
| 2700        | 10TSD27           | 1    | J              | X5F            |
| 3300        | 10TSD33           | 1    | J              | X5F            |
| 4700        | 10TSD47           | 1    | L              | X5F            |
| .01μF       | 10TSS10           | 1    | L              | X5S            |

### 1KV NP0/N750 PRECISION DISC CAPACITORS, 5% TOL

- Application Range:  
Up to 1500 VDC, 300 VAC RMS\*\*
- dv/dt up to 10,000 V/usec

- Insulation Resistance: 100,000 M $\Omega$  minimum, 1000 $\Omega$ F
- Dielectric Strength: 2500 VDC, 750 VAC RMS
- High Q: 1000, Dissipation Factor: 0.1% max

### 561C Series

#### Temperature/Frequency/Voltage Stable

- Application: NP0 capacitors are used when the ultimate in stability is required
- N750/S3L are smaller & ideal for "lossless snubbers".

| VALUE |          | CATALOG NUMBER | SIZE |      | TEMP. COEF. |
|-------|----------|----------------|------|------|-------------|
| pF    | TOL.     |                | FIG. | CODE |             |
| 1.0   | 10TCCV10 | 3              | C    |      |             |
| 2.2   | 10TCCV22 | 3              | C    |      |             |
| 2.7   | 10TCCV27 | 3              | C    |      |             |
| 3.0   | 10TCCV30 | 3              | C    |      |             |
| 3.3   | 10TCCV33 | 3              | C    |      |             |
| 3.9   | 10TCCV39 | 3              | C    |      |             |
| 4.7   | 10TCCV47 | 3              | C    |      |             |
| 5.0   | 10TCCV50 | 3              | C    |      |             |
| 5.6   | 10TCCV56 | 3              | C    |      |             |
| 6.8   | 10TCCV68 | 3              | C    |      |             |
| 8.2   | 10TCCV82 | 3              | C    |      |             |

| VALUE |          | CATALOG NUMBER | SIZE |      | TEMP. COEF. |
|-------|----------|----------------|------|------|-------------|
| pF    | TOL.     |                | FIG. | CODE |             |
| 10    | 10TCCQ10 | 3              | C    |      |             |
| 12    | 10TCCQ12 | 3              | C    |      |             |
| 15    | 10TCCQ15 | 3              | C    |      |             |
| 18    | 10TCCQ18 | 3              | E    |      |             |
| 20    | 10TCCQ20 | 3              | E    |      |             |
| 22    | 10TCCQ22 | 3              | E    |      |             |
| 25    | 10TCCQ25 | 3              | E    |      |             |
| 27    | 10TCCQ27 | 3              | F    |      |             |
| 30    | 10TCCQ30 | 3              | F    |      |             |
| 33    | 10TCCQ33 | 3              | F    |      |             |
| 39    | 10TCCQ39 | 3              | F    |      |             |

| VALUE |          | CATALOG NUMBER | SIZE           |      | TEMP. COEF. |
|-------|----------|----------------|----------------|------|-------------|
| pF    | TOL.     |                | FIG.           | CODE |             |
| 47    | 10TCCQ47 | 1              | G              |      |             |
| 50    | 10TCCQ50 | 1              | G              |      |             |
| 56    | 10TCCQ56 | 1              | G              |      |             |
| 68    | 10TCCQ68 | 1              | H              |      |             |
| 82    | 10TCCQ82 | 1              | H <sub>3</sub> |      |             |
| 100   | 10TCCT10 | 1              | J              |      |             |
| 120   | 10TCCT12 | 1              | J              |      |             |
| 150   | 10TCCT15 | 1              | K              |      |             |
| 180   | 10TCCT18 | 1              | L              |      |             |
| 220   | 10TCCT22 | 1              | M              |      |             |
| 270   | 10TCCT27 | 1              | P              |      |             |

| VALUE<br>pF              | CATALOG<br>NUMBER | SIZE |      | TEMP.<br>COEF. |
|--------------------------|-------------------|------|------|----------------|
|                          |                   | FIG. | CODE |                |
| N750/S3L Disc Capacitors |                   |      |      |                |
| 33                       | 10TCUQ33          | 3    | E    | U              |
| 47                       | 10TCUQ47          | 3    | E    | U              |
| 68                       | 10TCUQ68          | 3    | F    | U              |
| 100                      | 10TCUT10          | 3    | F    | U              |
| 220                      | 10TCUT22          | 1    | G    | V              |
| 330                      | 10TCUT33          | 1    | H    | V              |
| 470                      | 10TCUT47          | 1    | J    | V              |
| 560                      | 10TCUT56          | 1    | J    | V              |
| 680                      | 10TCUT68          | 1    | K    | Y              |
| 1000                     | 10TCUD10          | 1    | L    | Y              |

\*1.0 to 10pF are D tolerance

\*\*See "Application Data" section for limits on AC voltage.



### Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.