

FMW-2206

Schottky Barrier Rectifier

Mar. 2008

General Description

FMW-2206 is a Schottky Barrier Diode, and has achieved low leakage current and low VF by selecting the best barrier metal.

Applications


- DC-DC converters
- AC adapter
- High frequency rectification circuit

Features

- Super-high speed & low noise switching.
- Low forward voltage drop.

Package



TO220F(3Pin)



Key Specifications

Symbol	Unit	Rating	Conditions
V_{RM}	V	60	
V_F	V	0.70	$I_F=10A$
$I_{F(AV)}$	A	20	

Typical Characteristics



The information included herein is believed to be accurate and reliable. However, SANKEN ELECTRIC CO., LTD assumes no responsibility for its use ; nor for any infringements of patents or other rights of third parties that may result from its use.

FMW-2206

Mar. 2008

Schottky Barrier Rectifier

★ Absolute maximum ratings

No.	Parameter	Symbol	Unit	Rating	Conditions
1	Transient Peak Reverse Voltage	V_{RSM}	V	60	
2	Peak Reverse Voltage	V_{RM}	V	60	
3	Average Forward Current	$I_{F(AV)}$	A	20	
4	Peak Surge Forward Current	I_{FSM}	A	120	Half sinewave, one shot
5	I^2t Limiting Value	I^2t	A ² s	72	1msec< t < 10msec
6	Junction Temperature	T_j	°C	-40 to +150	
7	Storage Temperature	T_{stg}	°C	-40 to +150	

No.1,2,4&5 show ratings per one chip.

★ Electrical characteristics (Ta=25°C, unless otherwise specified)

No.	Parameter	Symbol	Unit	Rating	Conditions
1	Forward Voltage Drop	V_F	V	0.70 max.	$I_F=10A$
2	Reverse Leakage Current	I_R	mA	1.0 max.	$V_R=V_{RM}$
3	Reverse Leakage Current Under High Temperature	$H \cdot I_R$	mA	250 max.	$V_R=V_{RM}$, $T_j=150^\circ C$
4	Thermal Resistance	$R_{th(j-c)}$	°C /W	4.0 max.	Between Junction and Case

No.1,2,&3 show characteristics per one chip.


FMW-2206

Schottky Barrier Rectifier


Mar. 2008

★ Characteristics


Forward Power Dissipation



Reverse Power Dissipation



Current Derating $V_R=60\text{V}$




FMW-2206

Schottky Barrier Rectifier

Mar. 2008

★ Outline drawings, mm



★ Connection Diagram

