





LOC		DIST		REVISIONS					
GP		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
					E	REVISED PER ECO-13-010626	31 JUL 2013	KH	RP



SECTION W-W



- 1 MATERIAL:
CONTACT - PHOS BRONZE
HOUSING - LCP, UL 94V-0, COLOR - BLACK
- 2 FINISH:
CONTACT AREA FINISH CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPECIFICATION 108-2303; BASED ON TELCORDIA GR-1217-CORE FOR SYSTEM QUALITY LEVEL III, APPLICATIONS IN CONTROLLED ENVIRONMENTS (CENTRAL OFFICE).
COMPLIANT PIN AREA- 0.5µm MIN MATTE TIN OVER 1.27µm MIN NICKEL.
- 3 CONNECTOR MARKED WITH PART NUMBER, DATE CODE AND STANDARD IN APPROXIMATE AREA SHOWN
- 4 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 5. CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT. TECHNICAL REFERENCE GR-1217-CORE, ISSUE 1, NOVEMBER 1995.
- 6 REFERENCE APPLICATION SPEC 114-13202 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESSES.

○ = SIGNAL
⊗ = GROUND
RECOMMENDED PC BOARD
LAYOUT BACKPLANE,
COMPONENT SIDE SHOWN
SCALE 4:1

1934326-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. SHOBER 18FEB2008	TE Connectivity	
DIMENSIONS:		CHK R. PATTERSON 23JUN2008		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD R. PATTERSON 4APR2009	NAME	
	0 PLC ±	PRODUCT SPEC	HEADER ASSEMBLY, DOUBLE ENDED, 5 PAIR, 10 COLUMN TinMan	
	1 PLC ±	APPLICATION SPEC		
	2 PLC ±		SIZE	
	3 PLC ±		A100779C=1934326	
	4 PLC ±		RESTRICTED TO	
MATERIAL	FINISH	WEIGHT	SCALE 8:1	
			SHEET 1 OF 1	
CUSTOMER DRAWING			REV E	