


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION , 19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC		DIST		P		ZONE		LTR		REVISIONS		DATE	APPD
G		14								REVISED & REDRAWN PER 0720-0303-93		8-27-93	SPB BB



NOTE:
1. WIRE INSULATION DIA 11.30[.445] MAX

AMP
WIRE RANGE
2 AWG
STRANDED

METRIC
DIMENSIONS LISTED IN mm [INCHES]

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 105°C		DO NOT SCALE PRINT. UNLESS SPECIFIED TOLERANCES ON: 2 P.L.C DEC ± 0.20(.008) 3 P.L.C DEC ± . ANGLES		DR 8-27-93 S.S. GULDEN	QTY 50	LOOSE PC		324623	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 600 V MAX		CHK 8-27-93 R. HERSEY		PACKAGE TYPE		PART NO	
FOR APPLICATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 26.65-45.41mm² [52,600-83,700] STRANDED		APPD 8-27-93 B. BLAIR		NAME		AMP Incorporated Harrisburg, PA 17105-3608	
TOOLING INFORMATION		1-800-526-5142		FINISH TIN PLATE PER MIL-T-10727		APPD 8-27-93 N. BLAIR		SPLICE, BUTT, SINGLE TO SINGLE, TERMINYL, WIRE SIZE: 2 AWG			
FOR ORDER ENTRY				MATERIAL COPPER PER ASTM B-152 ANNEAL, COLOR, RED		PRODUCT SPEC		SIZE		CAGE CODE	
						APPLICATION SPEC		SCALE		DRAWING NO	
						WEIGHT		00779		G-324623	
								NTS		SHEET	
								1 OF 1			