

BRIGHT LED ELECTRONICS CORP.

LED DISPLAY SPECIFICATION

● COMMODITY : 2.30"(56.90mm) SINGLE DIGIT LED DISPLAY

PAGE : 2

● DEVICE NUMBER : BS-CD16RD

VERSION : 1.0


● ELECTRICAL AND OPTICAL CHARACTERISTICS (Ta=25°C)

Chip		Absolute Maximum Rating				Electro-optical Data (At 10mA)		Surface Color	Segment Color	
Emitted Color	Peak Wave Length λ_p (nm)	$\Delta \lambda$ (nm)	Pd (mW)	If (mA)	Peak If(mA)	Vf(V)	Iv Typ. (mcd)			
		Typ.		Max.		Typ.	Max.			
Super Red	660	20	300	30	150	6.8	10.0	18.0	Black	White


● ABSOLUTE MAXIMUM RATINGS (Ta=25°C)

Reverse Voltage	5V
Reverse Current (V _R =5V)	100µA
Operating Temperature Range	-40°C ~ 80°C
Storage Temperature Range	-40°C ~ 85°C
Lead Soldering Temperature (1/16" From Body).....	260°C For 5 Seconds

PACKAGE DIMENSIONS:



PIN FUNCTIONS:



BRIGHT LED ELECTRONICS CORP.


TYPICAL CHARACTERISTICS

PAGE: 3


DEVICE NUMBER: BS-CD16RD

VERSION: 1.0


SPECTRAL DISTRIBUTION




FORWARD CURRENT VS.
FORWARD VOLTAGE




RELATIVE LUMINOUS
INTENSITY VS. AMBIENT
TEMPERATURE



RELATIVE LUMINOUS
INTENSITY VS. FORWARD
CURRENT



FORWARD CURRENT
DERATING CURVE



RELIABILITY TEST

DEVICE NUMBER: BS-CD16RD

PAGE: 4
VERSION:1.0

Classification	Test Item	Reference Standard	Test Conditions	Result
Endurance Test	Operation Life	MIL-STD-750:1026 MIL-STD-883:1005 JIS C 7021 :B-1	Connect with a power If=30mA Ta=Under room temperature Test time=1,000hrs(-24hrs,+72hrs)	0/10
	High Temperature High Humidity Storage	MIL-STD-202:103B JIS C 7021 :B-11	Ta=65°C ±5 °C RH=90%-95% Test time=240hrs±2hrs	0/10
	High Temperature Storage	MIL-STD-883:1008 JIS C 7021 :B-10	High Ta=85°C ±5 °C Test time=1,000hrs(-24hrs,+72hrs)	0/10
	Low Temperature Storage	JIS-C-7021 :B-12	Low Ta= -35°C ±5 °C Test time=1,000hrs(-24hrs,+72hrs)	0/10
Environmental Test	Temperature Cycling	MIL-STD-202:107D MIL-STD-750:1051 MIL-STD-883:1010 JIS C 7021 :A-4	-35°C ~ 25°C ~ 85°C ~ 25°C 30min 5min 30min 5min Test Time=10cycle	0/10
	Thermal Shock	MIL-STD-202:107D MIL-STD-750:1051 MIL-STD-883:1011	85°C ±5 °C ~ -35°C ±5 °C 10min 10min Test Time=10cycle	0/10
	Solder Resistance	MIL-STD-202:201A MIL-STD-750:2031 JIS C 7021 :A-1	T.sol=260 ±5 °C Dwell Time=10 ±1 sec.	0/10
	Solderability	MIL-STD-202:208D MIL-STD-750:2026 MIL-STD-883:2003 JIS C 7021 :A-2	T.sol=230 ±5 °C Dwell Time=5 ±1 sec.	0/10

JUDGMENT CRITERIA OF FAILURE FOR THE RELIABILITY

Measuring items	Symbol	Measuring conditions	Judgement criteria for failure
Forward voltage	VF	IF=10mA	Over Ux1.2
Reverse current	IR	VR=5V	Over Ux2
Luminous intensity	IV	IF=10mA	Below Sx0.5

Note: 1.U means the upper limit of specified characteristics. S means initial value.

2.Measurment shall be taken between 2 hours and after the test pieces have been returned to normal ambient conditions after completion of each test.