

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION






.19

(C) COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
CM	53		C	REV & REDWN PER EC 0G1B-0217-98	29OCT98	TB R5

1. WIRE RANGE: 2 - 6 mm² (14 - 10 AWG)
2. INSULATION RANGE: 2.54 - 4.57



1.52	.060	4.06	.160	5.46	.215	-	-
0.51	.020	3.94	.155	5.08	.200	-	-
0.36	.014	3.56	.140	4.57	.180	25.27	.995
0.35	.014	2.54	.100	4.45	.175	6.05	.238
0.13	.005	2.03	.080	4.32	.170	5.48	.216
MM	IN	MM	IN	MM	IN	MM	IN
CONVERSION TABLE							

METRIC

PRE TIN	0.36 PH BRZ	350391-2
PRE TIN	0.35 BRASS	350391-1
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. BECK	29OCT1998	AMP AMP Incorporated Harrisburg, PA 17105-3608					
		CHK R. SWING	29OCT1998						
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME					
		APVD C. MARTIN	16NOV1998	PIN, LOOSE PIECE, .140 PIN & SOCKET CONNECTOR					
		PRODUCT SPEC -							
		APPLICATION SPEC -							
		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO				
		MATERIAL SEE TABLE		FINISH SEE TABLE	WEIGHT -	A200779	C- 350391	-	
CUSTOMER DRAWING				SCALE	5:1	SHEET	1 OF 1	REV	C