




PROTECTIVE COVER

1

TE CONNECTIVITY LOGO, ATTENUATION VALUE, PART NUMBER, AND SERIAL NUMBER ARE PRINTED ON THE LABEL.

PERFORMANCE REQUIREMENTS:

OPERATING WAVELENGTH : 1310/1550 ±25nm

REFLECTANCE : ≤ -65dB

OPERATING TEMPERATURE : -40°C TO +75°C

ATTENUATION TOLERANCE, AMBIENT : ±10% OF NOMINAL ATTENUATION VALUE

FOR ATTENUATORS ≥ 5dB : ±0.50dB

FOR ATTENUATORS < 5dB : ±0.50dB

MEASURED WITH REFERENCE QUALITY LAUNCH LEADS

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm[INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

FINISH -

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

05DEC2005

05DEC2005

05DEC2005

S. BUCHTER

NAME

ATTENUATOR, OPTICAL, BUILDOUT SC/APC 8 DEGREE, SM, DUAL WINDOW

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

5209597

4:1

SHEET

OF

REV

BI

1471-9 (3/11)

Pro/ENGINEER DRAWING