

4		3		2		1																																																																											
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		LOC		DIST		REVISIONS																																																																									
© COPYRIGHT - By -		ALL RIGHTS RESERVED.		G		86		P	LTR	DESCRIPTION	DATE	DWN	APVD																																																																				
									C1	REVISED PER ECO-12-019895	15NOV2012	KH	DR																																																																				
SERRATIONS SLEEVE BODY																																																																																	
1 FOR .105 TO .140 WIRE INSULATION DIA 2 MARKING 22-18 FOR MILITARY COMMERCIAL RANGE 22-16. 3 BODY & SLEEVE: COPPER PER ASTM-B152 4 TIN PLATE .000100 MIN THK PER ASTM-B545																																																																																	
<table><tr><td>5000</td><td>31777 ON TAPE</td><td>2-31777-1</td></tr><tr><td>1000</td><td>LOOSE PIECE</td><td>31777</td></tr><tr><td>QTY</td><td>PACKAGE TYPE</td><td>PART NO</td></tr></table>														5000	31777 ON TAPE	2-31777-1	1000	LOOSE PIECE	31777	QTY	PACKAGE TYPE	PART NO																																																											
5000	31777 ON TAPE	2-31777-1																																																																															
1000	LOOSE PIECE	31777																																																																															
QTY	PACKAGE TYPE	PART NO																																																																															
<table><tr><td colspan="2">THIS DRAWING IS A CONTROLLED DOCUMENT.</td><td colspan="2">DWN RAGAHVENDRA 07AUG08</td><td colspan="4" rowspan="2"> TE Connectivity</td></tr><tr><td colspan="2">CHK T MICHIELUTTI 07AUG08</td><td colspan="2">APVD T MICHIELUTTI 07AUG08</td></tr><tr><td colspan="2">DIMENSIONS: INCHES</td><td colspan="2">TOLERANCES UNLESS OTHERWISE SPECIFIED:</td><td colspan="4">NAME</td></tr><tr><td colspan="2"></td><td colspan="2">0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .008 4 PLC ± - ANGLES ± 5°</td><td colspan="4">PRODUCT SPEC</td></tr><tr><td colspan="2">MATERIAL</td><td colspan="2">FINISH</td><td colspan="4">APPLICATION SPEC</td></tr><tr><td colspan="2">3</td><td colspan="2">4</td><td colspan="4">WEIGHT -</td></tr><tr><td colspan="4">CUSTOMER DRAWING</td><td colspan="4">SCALE 5:1</td></tr><tr><td colspan="4"></td><td colspan="4">SHEET 1 OF 1</td></tr><tr><td colspan="4"></td><td colspan="4">REV C1</td></tr></table>														THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGAHVENDRA 07AUG08		TE Connectivity				CHK T MICHIELUTTI 07AUG08		APVD T MICHIELUTTI 07AUG08		DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME						0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .008 4 PLC ± - ANGLES ± 5°		PRODUCT SPEC				MATERIAL		FINISH		APPLICATION SPEC				3		4		WEIGHT -				CUSTOMER DRAWING				SCALE 5:1								SHEET 1 OF 1								REV C1			
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGAHVENDRA 07AUG08		TE Connectivity																																																																													
CHK T MICHIELUTTI 07AUG08		APVD T MICHIELUTTI 07AUG08																																																																															
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME																																																																													
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .008 4 PLC ± - ANGLES ± 5°		PRODUCT SPEC																																																																													
MATERIAL		FINISH		APPLICATION SPEC																																																																													
3		4		WEIGHT -																																																																													
CUSTOMER DRAWING				SCALE 5:1																																																																													
				SHEET 1 OF 1																																																																													
				REV C1																																																																													

1470-19

(3/11)