

3mm Infrared LED ,T-1MODEL NO : IR264C**■ Features :**

- High radiant intensity
- Peak wavelength λ p=940nm
- View angle 40°
- High reliability


■ Description :

- EVERLIGHT's Infrared Emitting Diode (IR264C) is a high intensity diode, molded in a water clear plastic package.
- The device is spectrally matched with phototransistor, photodiode and infrared receiver module.

■ Applications :

- Free air transmission system
- Optoelectronic switch
- Infrared remote control units with high power requirement

PART NO.	CHIP	LENS COLOR
	MATERIAL	
IR	GaAlAs	Water clear

3mm Infrared LED ,T-1MODEL NO : IR264C**■ Package Dimensions:****■ Notes :**

1. All dimensions are in millimeter.
2. Protruded resin under flange 1.5 mm Max.
3. Lead spacing is measured where the lead emerge from the package.
4. Lens color : Water clear.
5. Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.
6. These specification sheets include materials protected under copyright of EVERLIGHT corporation . Please don't reproduce or cause anyone to reproduce them without EVERLIGHT's consent.
7. When using this product , please observe the absolute maximum ratings and the instructions for use outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.

DEVICE NUMBER : DIR-026-207 REV : 1.0
 ECN : _____ PAGE : 3/8
3mm Infrared LED ,T-1

 MODEL NO : IR264C
■ Absolute Maximum Ratings at $T_A = 25^\circ\text{C}$

Parameter	Symbol	Rating	Unit	Notice
Continuous Forward Current	I_F	100	mA	
Peak Forward Current Pulse width=100 μs , Duty cycle=1%	I_{FP}	1.0	A	
Reverse Voltage	V_R	5	V	
Operating Temperature	T_{opr}	-40 ~ +85	$^\circ\text{C}$	
Storage Temperature	T_{stg}	-40 ~ +85	$^\circ\text{C}$	
Soldering Temperature	T_{sol}	260	$^\circ\text{C}$	4mm from mold body less than 5 seconds
Power Dissipation at(or below) 25 $^\circ\text{C}$ Free Air Temperature	P_d	150	mW	

■ Electronic Optical Characteristics :

Parameter	Symbol	Min.	Typ.	Max.	Unit	Condition
Radiant Intensity	Ee	4.0	5.6	----	mW/sr	$I_F=20\text{mA}$
		----	30	----		$I_F=100\text{mA}, t_p=100 \mu\text{s}, t_p/T=0.01$
		----	300	----		$I_F=1\text{A}, t_p=100 \mu\text{s}, t_p/T=0.01$
Peak Wavelength	λ_p	----	940	----	nm	$I_F=20\text{mA}$
Spectral Bandwidth	$\Delta \lambda$	----	45	----	nm	$I_F=20\text{mA}$
Forward Voltage	V_F	----	1.2	1.5	V	$I_F=20\text{mA}$
		----	1.4	1.8		$I_F=100\text{mA}, t_p=100 \mu\text{s}, t_p/T=0.01$
		----	2.6	4.0		$I_F=1\text{A}, t_p=100 \mu\text{s}, t_p/T=0.01$
Reverse Current	I_R	----	----	10	μA	$V_R=5\text{V}$
View Angle	$2\Theta 1/2$	----	40	----	deg	$I_F=20\text{mA}$

3mm Infrared LED ,T-1MODEL NO : IR264C**■ Typical Electrical/Optical/Characteristics Curves**

Fig.1 Forward Current vs. Ambient Temperature




Fig.2 Spectral Distribution




Fig.3 Peak Emission Wavelength vs. Ambient Temperature









Fig.4 Forward Current vs. Forward Voltage



3mm Infrared LED ,T-1MODEL NO : IR264C**■ Typical Electrical/Optical/Characteristics Curves**Fig.5 Relative Intensity vs.
Forward CurrentFig.7 Relative Intensity vs.
Ambient Temperature (° C)Fig.6 Relative Radiant Intensity vs.
Angular DisplacementFig.8 Forward Current vs.
Ambient Temperature



3mm Infrared LED ,T-1

MODEL NO : IR264C

■ Reliability Test Item And Condition

The reliability of products shall be satisfied with items listed below.

Confidence level:90%


LTPD:10%

NO.	Item	Test Conditions	Test Hours/Cycles	Sample Sizes	Failure Judgement Criteria	Ac/Re
1	Solder Heat	TEMP : 260°C ± 5 °C	10 sec	22 pcs		0/1
2	Temperature Cycle	H : +85°C 30 min L : -55°C 30 min 5 min	50 cycle	22 pcs	$I_R \geq U_x$ 2 $E_e \leq L_x$ 0.8 $V_F \geq U_x$ 1.2	0/1
3	Thermal Shock	H : +100°C 5 min L : -10°C 5 min 10 sec	50 cycle	22 pcs	U :Upper specification limit L :Lower specification limit	0/1
4	High Temperature Storage	TEMP. : +100°C	1000 hrs	22 pcs		0/1
5	Low Temperature Storage	TEMP. : -55°C	1000 hrs	22 pcs		0/1
6	DC Operating Life	$I_F=20mA$	1000 hrs	22 pcs		0/1
7	High Temperature / High Humidity	85°C / 85% R.H.	1000 hrs	22 pcs		0/1

DEVICE NUMBER : DIR-026-207 REV : 1.0
ECN : _____ PAGE : 7/8**3mm Infrared LED ,T-1**MODEL NO : IR264C**■ Test Method For Power :**Condition : $I_F=20$ mA

Test Item : Radian Intensity

Unit : mW/sr

**■ To Distinguish Intensity:**Condition: $I_F=20$ mA

Unit : mW/sr

Bin Number	K	L	M
Min	4.00	5.60	7.80
Max	6.40	8.90	12.50


DEVICE NUMBER : DIR-026-207 REV : 1.0
 ECN : _____ PAGE : 8/8

3mm Infrared LED ,T-1


MODEL NO : IR264C

■ Packing Specifications


1. Bag



2. Box



3. Carton



EVERLIGHT

CPN:

P/N:



IR264C

QTY:



CAT:



HUE:

LOT NO:

MADE IN TAIWAN

CPN : Customer's Production Number

P/N : Production Number

QTY : Packing Quantity

CAT : Ranks

HUE : Peak Wavelength

REF : Reference

LOT NO : Lot Number

MADE IN TAIWAN : Production place

■ Packing Quantity Specification

1. 1000 Pcs/1Bag , 4 Bags/1Box
2. 10 Boxes/1Carton