



- DC fans with electronically commutated external rotor motor. Fully integrated commutation electronics. With electronic protection against reverse polarity and blocking.
- Metal fan housing and impeller.
- Air exhaust over struts. Rotational direction CCW looking at rotor.
- Electrical connection via leads AWG 22, TR 64. Stripped and tinned ends. Housing with ground lug for screw M4.
- Mass 650 g.

Series 5100 N 135 x 135 x 38 mm

Air flow		Nominal Voltage	Voltage Range	Noise		Sinter-Sleeve Bearings	Ball Bearings	Power Input	Nominal Speed	Temperature Range	Service Life L ₁₀		Curve	Type	Specials
m³/h	CFM										at 40 °C	at t _{max}			
250	147.2	12	6...15	48	6.1	■	■	9.5	2900	-25...+72	80 000 / 37 500		2	5112 N	59/63
250	147.2	24	12...30	48	6.1	■	■	9.5	2900	-25...+72	80 000 / 37 500		2	5114 N	59
122	21.8	48	24...60	28	4.1	■	■	2.6	1400	-25...+72	85 000 / 40 000		1	5118 NL	
250	147.2	48	24...60	48	6.1	■	■	9.5	2900	-25...+72	80 000 / 37 500		2	5118 N	59/61

⊕ 48 V Type with grounding screw M4x6 7500 C.

