








PANEL THICKNESS	X dimension
0.75-1.25 [0.030-0.049]	19.2-0.1 [0.756]
1.25-2.0 [0.049-0.079]	19.4-0.1 [0.764]
2.0-3.0 [0.079-0.118]	19.8-0.1 [0.780]




PANEL CUTOUT
NOT TO SCALE

SWITCH FUNCTION			
POS. 1	POS. 2	POS. 3	
DN	OFF	<DN>	
1-1a	OPEN	1-1b	



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. RATING: 15A @ 125VAC OR
8A @ 250VAC
5. APPROVALS: UL, CSA, NEMKO, SEMKO, FEMKO, DEMKO
TERMINALS: Silver Plated Copper Alloy
CONTACTS: Coin Silver, Silver Plated
6. ELECTRIC LIFE: 10,000 cycles
7. CONTACT RESISTANCE: <20 mΩ-Ohms
8. INSULATION RESISTANCE: >1000 Mega-ΩHM
9. DIELECTRIC STRENGTH: >1500 VAC 1 minute



E-SWITCH®				
TITLE				
R1966H BLK BLK HS				
SCALE		DATE		
1.5:1		5/3/02		
DATE		DR	DWG	REV
5/3/02		CB	M301237	B

B	12297	REVISED DIMENSION/NOTES	7/9/02	CJB
A	12118	RELEASED FOR PRODUCTION	5/3/02	CJB
REV.	ECN No.	DESCRIPTION	DATE	CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				