


SURFACE MOUNT SUPERFAST RECTIFIER
VOLTAGE - 50 - 600 Volts CURRENT - 3.0 Amperes

- For surface mounted applications
- Low profile package
- Built-in strain relief
- Easy pick and place
- Superfast recovery times for high efficiency
- Plastic package has Underwriters Laboratory Flammability Classification 94V-O
- Glass passivated junction
- High temperature soldering:
260°C/10 seconds at terminals

Case: JEDEC DO-214AB molded plastic
Terminals: Solder plated solderable per MIL-STD-750,
Method 2026
Polarity: Indicated by cathode band
Standard Packaging: 16mm tape (EIA-481)
Weight: 0.007 ounces, 0.21 gram



Dimensions in inches and (millimeters)

Ratings at 25°C ambient temperature unless otherwise specified.
Single phase, half wave, 60 Hz, resistive or inductive load.
For capacitive load, derate current by 20%.

[illegible]

1. Reverse Recovery Test Conditions: $I_F = 0.5A$, $I_R = 1.0A$, $I_{RR} = 0.25A$.
2. Measured at 1.0 MHz and applied reverse voltage of 4.0 volts.
3. 8.0mm² (.013mm thick) land areas.

RATING AND CHARACTERISTIC CURVES ER3A THRU ER3J




FIG. 1 - REVERSE RECOVERY TIME CHARACTERISTIC
AND TEST DIAGRAM




FIG. 2 - MAXIMUM AVERAGE
FORWARD CURRENT RATING




FIG. 3 - TYPICAL REVERSE CHARACTERISTICS




FIG. 4 - TYPICAL FORWARD CHARACTERISTICS




FIG. 5 - MAXIMUM NON-REPETITIVE
PEAK FORWARD SURGE CURRENT




FIG. 6 - TYPICAL JUNCTION CAPACITANCE