



PMBFJ308; PMBFJ309; PMBFJ310

N-channel silicon field-effect transistors

Rev. 4 — 20 September 2011

Product data sheet

1. Product profile

1.1 General description

Symmetrical N-channel silicon junction field-effect transistors in a SOT23 package.

CAUTION



This device is sensitive to ElectroStatic Discharge (ESD). Therefore care should be taken during transport and handling.

1.2 Features and benefits

- Low noise
- Interchangeability of drain and source connections
- High gain.

1.3 Applications

- AM input stage in car radios
- VHF amplifiers
- Oscillators and mixers.

1.4 Quick reference data

Table 1. Quick reference data

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
V_{DS}	drain-source voltage		-	-	± 25	V
V_{Goff}	gate-source cut-off voltage					
PMBFJ308		$V_{DS} = 10$ V; $I_D = 1$ μ A	-1	-	-6.5	V
PMBFJ309		$V_{DS} = 10$ V; $I_D = 1$ μ A	-1	-	-4	V
PMBFJ310		$V_{DS} = 10$ V; $I_D = 1$ μ A	-2	-	-6.5	V




Table 1. Quick reference data ...*continued*

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
I_{DSS}	drain current					
	PMBFJ308	$V_{GS} = 0 \text{ V}; V_{DS} = 10 \text{ V}$	12	-	60	mA
	PMBFJ309	$V_{GS} = 0 \text{ V}; V_{DS} = 10 \text{ V}$	12	-	30	mA
P _{tot}	total power dissipation	up to $T_{amb} = 25 \text{ }^{\circ}\text{C}$	-	-	250	mW
$ y_{fs} $	forward transfer admittance	$V_{DS} = 10 \text{ V}; I_D = 10 \text{ mA}$	10	-	-	mS

2. Pinning information

Table 2. Discrete pinning^[1]

Pin	Description	Simplified outline	Symbol
1	source		
2	drain		
3	gate		 sym060

[1] Drain and source are interchangeable.

3. Ordering information

Table 3. Ordering information

Type number	Package			Version
	Name	Description		
PMBFJ308	-	plastic surface mounted package; 3 leads		SOT23
PMBFJ309				
PMBFJ310				

4. Marking

Table 4. Marking

Type number	Marking code ^[1]
PMBFJ308	48*
PMBFJ309	49*
PMBFJ310	50*

[1] * = p: Made in Hong Kong.

* = t: Made in Malaysia.

* = W: Made in China.

5. Limiting values

Table 5. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions	Min	Max	Unit
V_{DS}	drain-source voltage (DC)		-	± 25	V
V_{GSO}	gate-source voltage	open drain	-	-25	V
V_{GDO}	gate-drain voltage	open source	-	-25	V
I_G	forward gate current (DC)		-	50	mA
P_{tot}	total power dissipation	up to $T_{amb} = 25^\circ\text{C}$	-	250	mW
T_{stg}	storage temperature		-65	+150	$^\circ\text{C}$
T_j	junction temperature		-	150	$^\circ\text{C}$




Fig 1. Power derating curve.

6. Thermal characteristics

Table 6. Thermal characteristics

Symbol	Parameter	Conditions	Typ	Unit
$R_{th(j-a)}$	thermal resistance from junction to ambient		[1] 500	K/W

[1] Device mounted on an FR4 printed-circuit board.

7. Static characteristics

Table 7. Static characteristics

$T_j = 25^\circ\text{C}$; unless otherwise specified.


Symbol	Parameter	Conditions	Min	Typ	Max	Unit
$V_{(\text{BR})\text{GSS}}$	gate-source breakdown voltage	$I_G = -1 \mu\text{A}; V_{DS} = 0 \text{ V}$	-25	-	-	V
$V_{G\text{off}}$	gate-source cut-off voltage					V
	PMBFJ308	$I_D = 1 \mu\text{A}; V_{DS} = 10 \text{ V}$	-1	-	-6.5	V
	PMBFJ309	$I_D = 1 \mu\text{A}; V_{DS} = 10 \text{ V}$	-1	-	-4	V
	PMBFJ310	$I_D = 1 \mu\text{A}; V_{DS} = 10 \text{ V}$	-2	-	-6.5	V
V_{GSS}	gate-source forward voltage	$I_G = 1 \text{ mA}; V_{DS} = 0 \text{ V}$	-	-	1	V
I_{DSS}	drain-source leakage current					
	PMBFJ308	$V_{GS} = 0 \text{ V}; V_{DS} = 10 \text{ V}$	12	-	60	mA
	PMBFJ309	$V_{GS} = 0 \text{ V}; V_{DS} = 10 \text{ V}$	12	-	30	mA
	PMBFJ310	$V_{GS} = 0 \text{ V}; V_{DS} = 10 \text{ V}$	24	-	60	mA
I_{GSS}	gate-source leakage current	$V_{GS} = -15 \text{ V}; V_{DS} = 0 \text{ V}$	-	-	-1	nA
$R_{DS\text{on}}$	drain-source on-state resistance	$V_{GS} = 0 \text{ V}; V_{DS} = 100 \text{ mV}$	-	50	-	Ω
$ y_{fs} $	forward transfer admittance	$I_D = 10 \text{ mA}; V_{DS} = 10 \text{ V}$	10	-	-	mS
$ y_{os} $	common source output admittance	$I_D = 10 \text{ mA}; V_{DS} = 10 \text{ V}$	-	-	250	μS

8. Dynamic characteristics

Table 8. Dynamic characteristics


$T_j = 25^\circ\text{C}$; unless otherwise specified.

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
C_{iss}	input capacitance	$V_{DS} = 10 \text{ V}$				
		$V_{GS} = -10 \text{ V}; f = 1 \text{ MHz}$	-	3	5	pF
		$V_{GS} = 0 \text{ V}; T_{\text{amb}} = 25^\circ\text{C}$	-	6	-	pF
C_{rss}	reverse transfer capacitance	$V_{DS} = 0 \text{ V}; V_{GS} = -10 \text{ V}; f = 1 \text{ MHz}$	-	1.3	2.5	pF
g_{is}	input conductance	$V_{DS} = 10 \text{ V}; I_D = 10 \text{ mA}$				
		$f = 100 \text{ MHz}$	-	200	-	μS
		$f = 450 \text{ MHz}$	-	3	-	mS
g_{fs}	transfer conductance	$V_{DS} = 10 \text{ V}; I_D = 10 \text{ mA}$				
		$f = 100 \text{ MHz}$	-	13	-	mS
		$f = 450 \text{ MHz}$	-	12	-	mS
g_{rs}	reverse conductance	$V_{DS} = 10 \text{ V}; I_D = 10 \text{ mA}$				
		$f = 100 \text{ MHz}$	-	-30	-	μS
		$f = 450 \text{ MHz}$	-	-450	-	μS
g_{os}	output conductance	$V_{DS} = 10 \text{ V}; I_D = 10 \text{ mA}$				
		$f = 100 \text{ MHz}$	-	150	-	μS
		$f = 450 \text{ MHz}$	-	400	-	μS
V_n	equivalent input noise voltage	$V_{DS} = 10 \text{ V}; I_D = 10 \text{ mA}; f = 100 \text{ Hz}$	-	6	-	$\text{nV}/\sqrt{\text{Hz}}$




$V_{DS} = 10$ V; $T_j = 25$ °C.

Fig 2. Drain current as a function of gate-source cut-off voltage; typical values.




$V_{DS} = 10$ V; $I_D = 10$ mA; $T_j = 25$ °C.

Fig 3. Forward transfer admittance as a function of gate-source cut-off voltage; typical values.




$V_{DS} = 10$ V; $I_D = 10$ mA; $T_j = 25$ °C.

Fig 4. Common-source output conductance as a function of gate-source cut-off voltage; typical values.




$V_{DS} = 100$ mV; $V_{GS} = 0$ V; $T_j = 25$ °C.

Fig 5. Drain-source on-state resistance as a function of gate-source cut-off voltage; typical values.




$T_j = 25^\circ\text{C}.$
 (1) $V_{GS} = 0\text{ V}.$
 (2) $V_{GS} = -0.25\text{ V}.$
 (3) $V_{GS} = -0.5\text{ V}.$
 (4) $V_{GS} = -0.75\text{ V}.$
 (5) $V_{GS} = -1\text{ V}.$

Fig 6. Typical output characteristics; PMBFJ308.




$V_{DS} = 10\text{ V}; T_j = 25^\circ\text{C}.$

Fig 7. Typical transfer characteristics; PMBFJ308.




$T_j = 25^\circ\text{C}.$
 (1) $V_{GS} = 0\text{ V}.$
 (2) $V_{GS} = -0.25\text{ V}.$
 (3) $V_{GS} = -0.5\text{ V}.$
 (4) $V_{GS} = -0.75\text{ V}.$
 (5) $V_{GS} = -1\text{ V}.$

Fig 8. Typical output characteristics; PMBFJ309.




$V_{DS} = 10\text{ V}; T_j = 25^\circ\text{C}.$

Fig 9. Typical transfer characteristics; PMBFJ309.




$T_j = 25^\circ\text{C}$.
 (1) $V_{GS} = 0\text{ V}$.
 (2) $V_{GS} = -0.5\text{ V}$.
 (3) $V_{GS} = -1\text{ V}$.
 (4) $V_{GS} = -1.5\text{ V}$.
 (5) $V_{GS} = -2\text{ V}$.
 (6) $V_{GS} = -2.5\text{ V}$.

Fig 10. Typical output characteristics; PMBFJ310.




$V_{DS} = 10\text{ V}; T_j = 25^\circ\text{C}$.

Fig 11. Typical transfer characteristics; PMBFJ310.




$V_{DS} = 10\text{ V}; T_j = 25^\circ\text{C}$.

Fig 12. Reverse transfer capacitance as a function of gate-source voltage; typical values.




$V_{DS} = 10\text{ V}; T_j = 25^\circ\text{C}$.

Fig 13. Input capacitance as a function of gate-source voltage; typical values.



$V_{DS} = 10$ V; $T_j = 25$ °C.

Fig 14. Drain current as a function of gate-source voltage; typical values.



$T_j = 25$ °C.

- (1) $I_D = 10$ mA.
- (2) $I_D = 1$ mA.
- (3) $I_D = 100$ μA.
- (4) I_{GSS} .

Fig 15. Gate current as a function of drain-gate voltage; typical values.






Fig 16. Gate current as a function of junction temperature; typical values.




$V_{DS} = 10$ V; $I_D = 10$ mA; $T_{amb} = 25$ °C.

Fig 17. Input admittance; typical values.




$V_{DS} = 10$ V; $I_D = 10$ mA; $T_{amb} = 25$ °C.

Fig 18. Forward transfer admittance; typical values.



$V_{DS} = 10$ V; $I_D = 10$ mA; $T_{amb} = 25$ °C.

Fig 19. Reverse transfer admittance; typical values.



$V_{DS} = 10$ V; $I_D = 10$ mA; $T_{amb} = 25$ °C.

Fig 20. Output admittance; typical values.

9. Package outline

Plastic surface-mounted package; 3 leads

SOT23




Fig 21. Package outline.

10. Revision history

Table 9. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
PMBFJ308_309_310 v.4	20110920	Product data sheet	-	PMBFJ308_309_310 v.3
Modifications:				<ul style="list-style-type: none">The format of this data sheet has been redesigned to comply with the new identity guidelines of NXP Semiconductors.Legal texts have been adapted to the new company name where appropriate.Package outline drawings have been updated to the latest version.
PMBFJ308_309_310 v.3 (9397 750 13403)	20040723	Product data sheet	-	PMBFJ308_309_310 v.2
PMBFJ308_309_310 v.2 (9397 750 01141)	19960911	Product specification	-	-

11. Legal information

11.1 Data sheet status

Document status ^{[1][2]}	Product status ^[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

[1] Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL <http://www.nxp.com>.

11.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between NXP Semiconductors and its customer, unless NXP Semiconductors and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the NXP Semiconductors product is deemed to offer functions and qualities beyond those described in the Product data sheet.

malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at <http://www.nxp.com/profile/terms>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from national authorities.

11.3 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Non-automotive qualified products — Unless this data sheet expressly states that this specific NXP Semiconductors product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. NXP Semiconductors accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without NXP Semiconductors' warranty of the

product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond NXP Semiconductors' specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies NXP Semiconductors for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond NXP Semiconductors' standard warranty and NXP Semiconductors' product specifications.

11.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

12. Contact information

For more information, please visit: <http://www.nxp.com>

For sales office addresses, please send an email to: salesaddresses@nxp.com

13. Contents

1	Product profile	1
1.1	General description	1
1.2	Features and benefits	1
1.3	Applications	1
1.4	Quick reference data	1
2	Pinning information	2
3	Ordering information	2
4	Marking	2
5	Limiting values	3
6	Thermal characteristics	3
7	Static characteristics	4
8	Dynamic characteristics	4
9	Package outline	11
10	Revision history	12
11	Legal information	13
11.1	Data sheet status	13
11.2	Definitions	13
11.3	Disclaimers	13
11.4	Trademarks	14
12	Contact information	14
13	Contents	15

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© NXP B.V. 2011.

All rights reserved.

For more information, please visit: <http://www.nxp.com>

For sales office addresses, please send an email to: salesaddresses@nxp.com

Date of release: 20 September 2011

Document identifier: PMBFJ308_309_310