

Operator Interfaces/HMIs

NS

Quick Link
K012

Complete System Navigation with Fault Reset Capabilities


The NS advanced operator interfaces have brilliant display screens that maximize visualization of graphics. They support Omron's Smart Platform for small and medium size manufacturing operations with fully integrated design, programming, operation, monitoring and troubleshooting accessed from a single operator interface. This affordable solution brings the benefits of high-end interoperability within reach to give you a competitive production advantage on the plant floor.



Class I Div 2, Groups A, B, C, and D.

Direct Device Access

Omron's NS-Series touch screen HMIs offer built-in Ethernet communications, exceptional alarming/recipe/data logging capabilities and live video input/display capabilities. By allowing direct resetting of faults, these HMIs save time and effort in troubleshooting and quickly return your lines to production. The NS-Series achieves flexible data access to a variety of devices. It enables operators to reach the devices on the network including special I/O units, intelligent devices, and PLCs.



Reduced Design Time and Costs

We cut your screen project design time from days to a few hours by preprogramming function blocks that easily drag-and-drop into a program. All you do is specify values for key parameters. Omron already invested the hours and expert know-how programming each function block so you concentrate on the unique aspects of your application. The built-in Smart Active Parts library lets you establish communications and parameters for a wide range of Omron products. Just select the product and drag its icon into your project and it automatically sets the correct protocols.

Specifications

Series	NS8	NS10	NS12
Dimensions (W x H x D mm)	232 x 177 x 48.5	315 x 241 x 48.5	315 x 241 x 48.5
Effective display area	8.4 inch	10.4 inch	12.1 inch
Display device	High-definition TFT		
Resolution	640 x 480 pixels	640 x 480 pixels	800 x 600 pixels
View angle	±65° left/right, 50° top, 60° bottom	±60° left/right, 35° top, 65° bottom	±60° left/right, 45° top, 75° bottom
Maximum screen capacity	60 MB	60 MB	60 MB
Number of switches	768	1200	1900
Display colors	Basic colors (objects, background, etc.)	256 colors	256 colors
	Image data (BMP or JPG images) Images displayed	32,768 colors	32,768 colors
Screen data capacity via video input	260,000 color	260,000 colors	260,000 colors
Backlight life expectancy	50,000 hours min.		
Memory card capacity	64 Mbytes		
Expansion interface	Controller Link and video input board		

Series	NS5		
Dimensions (W x H x D mm)	195 x 142 x 54		
Effective display area	5.7 inch		
Display device	STN (monochrome)	STN (color)	TFT (color)
Resolution	320 x 240 pixels		
View angle	±45° left/right, 20° top, 40° bottom	±50° left/right, 45° top, 50° bottom	±70° left/right, 70° top, 50° bottom
Maximum screen capacity	20 MB		
Number of switches	300		
Display colors	Basic colors (objects, background, etc.)	Monochrome/16 gray scale levels	256 colors
	Image data (BMP or JPG images) Images displayed	Monochrome/16 gray scale levels	32,768 colors
Screen data capacity via video input	—		
Backlight life expectancy	50,000 hours min.		
Memory card capacity	64 Mbytes		
Expansion interface	—		

Ordering Information

NS-Series HMI Terminals

Description	Size	Resolution	Memory size	Features	Model
Full system navigation HMI	5-inch STN monochrome	320 x 240	20 MB onboard	—	NS5-MQ00B-V2
	5-inch STN			Ethernet	NS5-MQ01B-V2
				—	NS5-SQ00B-V2
				Ethernet	NS5-SQ01B-V2
				—	NS5-TQ00B-V2
	5-inch TFT			Ethernet	NS5-TQ01B-V2
		8-inch TFT	640 x 480	60 MB onboard	—
	10-inch TFT	640 x 480	60 MB onboard	Ethernet	NS8-TV01B-V2
				—	NS10-TV00B-V2
	12-inch TFT	800 x 600	60 MB onboard	Ethernet	NS10-TV01B-V2
—				NS12-TS00B-V2	
			Ethernet	NS12-TS01B-V2	

Software

Software name	Description	Quantity	Model
CX-One	Programming and configuration management software that lets you build, configure and program networks, PLCs, HMIs, motion control systems, temperature controllers and sensors	1 license	CXONE-AL01C-E
		3 licenses	CXONE-AL03C-E
		10 licenses	CXONE-AL10C-E

Accessories

Item	Description	Specifications	Model
Video input unit	Enables HMI to display machine vision and CCTV camera images	Inputs 4 channels of NTSC/PAL to display on NS8, NS10 and NS12 HMIs	NS-CA001
		Inputs 2 channels of NTSC/PAL to display on NS8, NS10 and NS12 HMIs	NS-CA002
Vision system console cable	Allows manipulation of vision system parameters from HMI	2 m cable	F150-VKP 2M
		5 m cable	F150-VKP 5M
Controller link interface unit	Establishes HMI as a node for Controller Link communications	Attaches to port on back of HMI	NS-CLK21
RS-422A adapter	Enables monitoring of multiple PLCs	500 m total transmission distance	NS-AL002
		50 m total transmission distance	CJ1W-CIF11
Anti-reflection sheets	For NS10 and NS12 models	5 sheets; applied to screen surface	NS12-KBA04
	For NS8 models		NS7-KBA04
	For NS5 models		NT30-KBA04
Protective covers	For NS10 and NS12 models	5 covers; protects screen surface	NS12-KBA05
	For NS8 models		NS7-KBA05
	For NS5 models		NT31C-KBA05
Chemical resistant covers	For NS5 models	5 covers	NT30-KBA01
			NT31C-KBA01
Memory card	Store screen data and firmware; requires Memory Card Adapter	30 MB	HMC-EF372
		64 MB	HMC-EF672
Memory card adapter	Enables use of Memory Cards	—	HMC-AP001
Battery	Backs up HMI memory	—	CJ1W-BAT01

Cables

Function	Connections	Applicable models	Cable length	Model
Connect NS HMIs to printer	USB to USB	NS8, NS10, NS12	2 m	NS-US22
			5 m	NS-US52
Converts USB to RS-232C	USB to 9-pin D-sub	NS5, NS8, NS10, NS12	0.5 m	CS1W-CIF31
Connect NS-V2 HMIs to Omron PLCs	9-pin to PLC mini-peripheral port	CPM2C, CQM1H, CJ1, CS1	10 cm	CS1W-CN118
Connect NS-V2 HMIs to Omron PLC	9-pin to 9-pin PLC peripheral port	CPM1A, CPM2A, CQM1, C200H/C200HE/ C200HG/C200HX	50 cm	C200H-CN510-EU
			3 m	C200H-CN320-EU
			5 m	C200H-CN520-EU
Connect NS-V2 HMIs to a PC	RS-232C serial port 9-pin to 9-pin	All NS-V2 models	2 m	C200H-CN229-EU CBL-202 in Canada
	USB, commercially available	Connects slave port on all NS-V2 models	Various	—

Terms and Conditions of Sale

1. **Offer; Acceptance.** These terms and conditions (these "Terms") are deemed part of all quotes, agreements, purchase orders, acknowledgments, price lists, catalogs, manuals, brochures and other documents, whether electronic or in writing, relating to the sale of products or services (collectively, the "Products") by Omron Electronics LLC and its subsidiary companies ("Omron"). Omron objects to any terms or conditions proposed in Buyer's purchase order or other documents which are inconsistent with, or in addition to, these Terms.
2. **Prices; Payment Terms.** All prices stated are current, subject to change without notice by Omron. Omron reserves the right to increase or decrease prices on any unshipped portions of outstanding orders. Payments for Products are due net 30 days unless otherwise stated in the invoice.
3. **Discounts.** Cash discounts, if any, will apply only on the net amount of invoices sent to Buyer after deducting transportation charges, taxes and duties, and will be allowed only if (i) the invoice is paid according to Omron's payment terms and (ii) Buyer has no past due amounts.
4. **Interest.** Omron, at its option, may charge Buyer 1-1/2% interest per month or the maximum legal rate, whichever is less, on any balance not paid within the stated terms.
5. **Orders.** Omron will accept no order less than \$200 net billing.
6. **Governmental Approvals.** Buyer shall be responsible for, and shall bear all costs involved in, obtaining any government approvals required for the importation or sale of the Products.
7. **Taxes.** All taxes, duties and other governmental charges (other than general real property and income taxes), including any interest or penalties thereon, imposed directly or indirectly on Omron or required to be collected directly or indirectly by Omron for the manufacture, production, sale, delivery, importation, consumption or use of the Products sold hereunder (including customs duties and sales, excise, use, turnover and license taxes) shall be charged to and remitted by Buyer to Omron.
8. **Financial.** If the financial position of Buyer at any time becomes unsatisfactory to Omron, Omron reserves the right to stop shipments or require satisfactory security or payment in advance. If Buyer fails to make payment or otherwise comply with these Terms or any related agreement, Omron may (without liability and in addition to other remedies) cancel any unshipped portion of Products sold hereunder and stop any Products in transit until Buyer pays all amounts, including amounts payable hereunder, whether or not then due, which are owing to it by Buyer. Buyer shall in any event remain liable for all unpaid accounts.
9. **Cancellation; Etc.** Orders are not subject to rescheduling or cancellation unless Buyer indemnifies Omron against all related costs or expenses.
10. **Force Majeure.** Omron shall not be liable for any delay or failure in delivery resulting from causes beyond its control, including earthquakes, fires, floods, strikes or other labor disputes, shortage of labor or materials, accidents to machinery, acts of sabotage, riots, delay in or lack of transportation or the requirements of any government authority.
11. **Shipping; Delivery.** Unless otherwise expressly agreed in writing by Omron:
 - a. Shipments shall be by a carrier selected by Omron; Omron will not drop ship except in "break down" situations.
 - b. Such carrier shall act as the agent of Buyer and delivery to such carrier shall constitute delivery to Buyer;
 - c. All sales and shipments of Products shall be FOB shipping point (unless otherwise stated in writing by Omron), at which point title and risk of loss shall pass from Omron to Buyer; provided that Omron shall retain a security interest in the Products until the full purchase price is paid;
 - d. Delivery and shipping dates are estimates only; and
 - e. Omron will package Products as it deems proper for protection against normal handling and extra charges apply to special conditions.
12. **Claims.** Any claim by Buyer against Omron for shortage or damage to the Products occurring before delivery to the carrier must be presented in writing to Omron within 30 days of receipt of shipment and include the original transportation bill signed by the carrier noting that the carrier received the Products from Omron in the condition claimed.
13. **Warranties.** (a) **Exclusive Warranty.** Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied. (b) **Limitations.** OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE. Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) **Buyer Remedy.** Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty. See <http://oeweb.omron.com> or contact your Omron representative for published information.
14. **Limitation on Liability; Etc.** OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY. Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.
15. **Indemnities.** Buyer shall indemnify and hold harmless Omron Companies and their employees from and against all liabilities, losses, claims, costs and expenses (including attorney's fees and expenses) related to any claim, investigation, litigation or proceeding (whether or not Omron is a party) which arises or is alleged to arise from Buyer's acts or omissions under these Terms or in any way with respect to the Products. Without limiting the foregoing, Buyer (at its own expense) shall indemnify and hold harmless Omron and defend or settle any action brought against such Companies to the extent based on a claim that any Product made to Buyer specifications infringed intellectual property rights of another party.
16. **Property; Confidentiality.** Any intellectual property in the Products is the exclusive property of Omron Companies and Buyer shall not attempt to duplicate it in any way without the written permission of Omron. Notwithstanding any charges to Buyer for engineering or tooling, all engineering and tooling shall remain the exclusive property of Omron. All information and materials supplied by Omron to Buyer relating to the Products are confidential and proprietary, and Buyer shall limit distribution thereof to its trusted employees and strictly prevent disclosure to any third party.
17. **Export Controls.** Buyer shall comply with all applicable laws, regulations and licenses regarding (i) export of products or information; (ii) sale of products to "forbidden" or other proscribed persons; and (iii) disclosure to non-citizens of regulated technology or information.
18. **Miscellaneous.** (a) **Waiver.** No failure or delay by Omron in exercising any right and no course of dealing between Buyer and Omron shall operate as a waiver of rights by Omron. (b) **Assignment.** Buyer may not assign its rights hereunder without Omron's written consent. (c) **Law.** These Terms are governed by the law of the jurisdiction of the home office of the Omron company from which Buyer is purchasing the Products (without regard to conflict of law principles). (d) **Amendment.** These Terms constitute the entire agreement between Buyer and Omron relating to the Products, and no provision may be changed or waived unless in writing signed by the parties. (e) **Severability.** If any provision hereof is rendered ineffective or invalid, such provision shall not invalidate any other provision. (f) **Setoff.** Buyer shall have no right to set off any amounts against the amount owing in respect of this invoice. (g) **Definitions.** As used herein, "including" means "including without limitation"; and "Omron Companies" (or similar words) mean Omron Corporation and any direct or indirect subsidiary or affiliate thereof.

Certain Precautions on Specifications and Use

1. **Suitability of Use.** Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases but the following is a non-exhaustive list of applications for which particular attention must be given:
 - (i) Outdoor use, uses involving potential chemical contamination or electrical interference, or conditions or uses not described in this document.
 - (ii) Use in consumer products or any use in significant quantities.
 - (iii) Energy control systems, combustion systems, railroad systems, aviation systems, medical equipment, amusement machines, vehicles, safety equipment, and installations subject to separate industry or government regulations.
 - (iv) Systems, machines and equipment that could present a risk to life or property. Please know and observe all prohibitions of use applicable to this Product.
 NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON'S PRODUCT IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.
2. **Programmable Products.** Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.
3. **Performance Data.** Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.
4. **Change in Specifications.** Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.
5. **Errors and Omissions.** Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

Complete "Terms and Conditions of Sale" for product purchase and use are on Omron's website at www.omron.com/oei – under the "About Us" tab, in the Legal Matters section.

ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.



OMRON ELECTRONICS LLC

One Commerce Drive
Schaumburg, IL 60173

847-843-7900

For US technical support or other inquiries:

800-556-6766

OMRON CANADA, INC.

885 Milner Avenue
Toronto, Ontario M1B 5V8

416-286-6465

OMRON ON-LINE

Global - <http://www.omron.com>
USA - <http://www.omron.com/oei>
Canada - <http://www.omron.ca>