


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS				DOC. NO. SPC-F005 * Effective: 12/21/98 * DCP No. 880			
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	DATE
615	A	Released	JMM	4/24/02	HO	4/29/02	4/29/02



Notes:

1. 2 Switch Positions: x1/x10
2. Attenuation: x1/x10
3. Input Resistance: 1Megohm (x1); 10Megohm (x10)
4. Input Capacitance: 46pF (x1); 16pF (x10)
5. Bandwidth (MHz): 15 (x1); 100 (x10)
6. Rise time (ns): 27 (x1); 3.5 (x10)
7. Max. Input (VDC + AC Max): 600
8. Compensation: (pF) 10..35
9. Length: 1.2 meters
10. Meets IEC61010-2-031 CAT I 600V

DISCLAIMER
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TENMA
®

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.		DRAWING TITLE: Insulated BNC, 2-Position, Oscilloscope Probe Kit	
DRAWN BY:	DATE:	SIZE	DWG. NO.
Jeff McVicker	4/24/02	A	76-123
CHECKED BY:	DATE:	ELECTRONIC FILE	REV
Hisham Odiah	4/29/02	18C2263.dwg	A
APPROVED BY:	DATE:	SCALE:	SHEET:
Daniel Carey	4/29/02	NTS	1 OF 1