

PRODUCT NUMBER

71600-YXX

TOTAL NB OF POSITION 04 TO 64
SEE SHEET 2

OPTIONAL STRAIN RELIEF
SEE SHEET 2

TRIANGLE INDICATES
POSITION 1


LEFT POLARIZING

RIGHT POLARIZING

CENTRAL KEY

NEW LATCH DESIGN


SEE NOTE 5



6.1 MAX

NOTES:

- HOUSING MAT'L : GLASS FILLED HIGH TEMPERATURE THERMOPLASTIC. UL94V-0 COLOR: GREY
- PIN MATERIAL : PHOSPHOR BRONZE
- PRODUCT PACKAGED IN TUBES.
- TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS
EXAMPLE : 8 POS $N \times 2.54 = 20.32\text{mm}$
- THE DASH "L" AT THE END OF THE PART NUMBER TO INDICATE A NEW LATCH DESIGN.
"COVER LATCH STYLE" IS THE MANUFACTURER'S OPTION (P/N ENDING WITH OR WITHOUT AN "L").




COVER ORIENTATION

CABLE ENTRY

CABLE ENTRY

TRIANGLE SIDE



D D SECTION

mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		FCI ELECTRONICS	
SEE NOTES								COPY		www.fciconnect.com	
lfr	ecr no	dr	date	linear				projection		title	
Y	V91355	DLE	99.06.25							IDC RECEPT.	
AA	F10121	DLE	01.01.24	angles						DR	
AB	F10199	GCO	01.04.26								
AC	V11866	DLE	01.07.20	dr	D.LE	01.01.24		product family		QUICKIE	
				engr	P.NZ	01.01.24		size		213	
				chr	JF.N	01.01.24		scale		5:1	
				appd	P.NZ	01.01.24		A3		71600	
sheet index	revision sheet	AC	AA							sheet 1 of 2	
		1	2								

This data is provided for informational purposes only. It is not intended to be used as a specification or to replace the manufacturer's data sheet.

FCI

All rights are reserved. Reproduction in whole or in part without the written permission of FCI is prohibited.

CORE RANGE

STRAIN RELIEF	Nbr OF POSITIONS
0/1	04
0/1	06
0/1	08
0/1	10
0/1	14
0/1	16
0/1	20
0/1	24
0/1	26
0/1	30
0/1	34
0/1	40
0/1	50
0/1	60
0/1	64

PLATING

0.76µm GOLD ON CONTACT AREA
1.27 µm Ni REMAINDER OF PRODUCT

CATALOGUE RANGE

STRAIN RELIEF	Nbr OF POSITIONS
2/6	04
2/6	06
2/6	08
2/6	10
2/6	14
2/6	16
2/6	20
2/6	24
2/6	26
2/6	30
2/6	34
2/6	40
2/6	50
2/6	60
2/6	64

PLATING

0.76µm GOLD ON CONTACT AREA
1.27 µm Ni REMAINDER OF PRODUCT


624

304


204 / 224

004


DASHES NOT AVAILABLE




WITHOUT STRAIN RELIEF




WITH LOW PROFILE STRAIN RELIEF




WITH STANDARD STRAIN RELIEF




WITH LATCHING STRAIN RELIEF



LOW PROFILE STRAIN RELIEF



STANDARD STRAIN RELIEF



LATCHING STRAIN RELIEF FOR SLIM HEADER

PRODUCT NUMBER	WITH CENTRAL KEY	WITHOUT CENTRAL KEY	STANDARD	WITHOUT STANDARD	LOW PROFILE	LATCHING
71600-6YY	●	●	●			●
71600-3YY		●	●		●	
71600-2YY	●			●		
71600-1YY	●			●		
71600-0YY	●		●			

mat'l code				tolerances unless otherwise specified		CUSTOMER COPY		ELECTRONICS	
ltr	ecr no	dr	date			projection	title	www.fciconnect.com	
X	F70666	AAN	97.11.05	linear			IDC RECEPT		
Y	F10121	DLE	01.01.24				DR		
AA	F10199	GCO	01.04.26	angles					
				dr	D.LE	01.01.24	product family	QUICKIE	code
				engr	P.NZ	01.01.24	size	dwg no	213
				chr	JF.N	01.01.24	scale	71600	sheet
				appd	P.NZ	01.01.24	N/A		2 of -
sheet index	revision sheet								