

LNC803PS

High Power Output Semiconductor Laser

Overview

The LNC803PS is a GaAlAs laser diode which provides stable, continuous, single mode oscillation of near infrared light at room temperature. This product can be used in a wide range of light source applications, including laser printers, facsimiles, optical disk memory, and optical information devices.

Features

- Low threshold oscillation
- Stable single horizontal mode oscillation
- Built-in PIN photodiode for light output monitors
- Light output is continuously variable as far as 60 mW
- Supports direct modulation
- Near infrared oscillating wavelength
- Long lifetime, high reliability

Absolute Maximum Ratings (Ta = 25°C)

Parameter		Symbol	Ratings	Unit
Radiant power		P _O	40	mW
Reverse voltage	Laser	V _R	1.5	V
	PIN	V _R (PIN)	30	V
Power dissipation		P _d (PIN)	100	mW
Operating ambient temperature		T _{opr}	-10 to +60	°C
Storage temperature		T _{stg}	-40 to +80	°C

Electro-Optical Characteristics (Ta = 25°C)

Parameter		Symbol	Conditions	min	typ	max	Unit
Threshold current		I _{th}	CW	10	25	40	mA
Operating current		I _{OP}	P _O = 32mW	30	50	90	mA
Operating voltage		V _{OP}	P _O = 32mW		2.0	3.0	V
Oscillation wavelength		λ _L	P _O = 32mW	815	830	845	nm
Radiation angle	Horizontal direction	θ *	P _O = 32mW	7	10	13	deg.
	Vertical direction	θ _⊥ *	P _O = 32mW	18	25	28	deg.
Differential efficiency		η	CW P _O = 28mW/I(30mW - 4mW)	0.6	1.0	1.5	mW/mA
Reverse current (DC)		I _R	V _R (PIN) = 5V			0.1	μA
PIN photo current		I _P	P _O = 32mW, V _R (PIN) = 5V				mA
Optical axis accuracy	X direction	θ _X	P _O = 32mW	-2.0		+2.0	deg.
	Y direction	θ _Y	P _O = 32mW	-3.0		+3.0	deg.
Oscillation mode		Single horizontal mode					

* θ_{||} and θ_⊥ are the angles where the optical intensity is a half of its max. value.(half full angle)



