





LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
G		REV PER ECO-15-002995		15MAR15	KG	PD	

43 GRAMS	9.9 ± 0.13 [.390 ± 0.005]	3/8	BODY: COPPER ASTM-B187 ANNEALED TIN PL MIL-T-10727 0.00457[.000150] MIN THK	55835-2
44 GRAMS	6.73 ± 0.13 [.265 ± 0.005]	1/4	INSERT & FUNNEL: BRASS PER ASTM B36 NICKEL PLATE SAE AMS QQ-N-290A, DATED JULY 2000, 0.00254 [.000100] MIN THK	55835-1
WEIGHT	"A"	"B"	MATERIAL AND FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN DK SCHURM 6/15/92		 TE Connectivity			
DIMENSIONS: MM [INCHES]			CHK WJ VOCKROTH 6/16/92					
			APVD AJ KAUFMAN 6/16/92		NAME WIRE TERMINAL, COPALUM SEALED, RING TONGUE, WIRE SIZE: 2 AL, 4 COPPER			
			PRODUCT SPEC 108-11011					
TOLERANCES UNLESS OTHERWISE SPECIFIED:			APPLICATION SPEC 114-2134		SIZE A2			
			WEIGHT SEE TABLE					
MATERIAL SEE TABLE			FINISH SEE TABLE		CAGE CODE 00779		DRAWING NO C=55835	RESTRICTED TO —
CUSTOMER DRAWING					SCALE 4:1		SHEET 1 of 1	REV G