

			REVISIONS																																																														
			REV	DESCRIPTION	DATE	APPROVED																																																											
			01	RELEASED	7/25/97																																																												
			B	REVISED PER ECN 0020-0262-01	G.V. 12/12/02	JGH																																																											
<table><tr><td>ELECTRICAL</td><td>MECHANICAL</td><td>ENVIRONMENTAL</td></tr><tr><td>Nominal Impedance (Ohms) 50</td><td>Interface Dimensions Per MIL-STD-348A Fig. 321.1</td><td>TEMPERATURE RATING -65° TO +125°C</td></tr><tr><td>Frequency Range (GHz) DC to 18</td><td>Mating Characteristics:</td><td>Vibration MIL-STD-202, Method 204, Condition D</td></tr><tr><td>Volt Rating (VRMS MAX) @ Sea Level 335</td><td>Insertion (MAX Lbs) N/A</td><td>Shock MIL-STD-202, Method 213, Condition I</td></tr><tr><td>VSWR 1.04+.006f(GHz)</td><td>Withdrawal (MIN Oz) N/A</td><td>Thermal Shock MIL-STD-202, Method 107, Condition B</td></tr><tr><td>Insertion Loss (dB MAX) .03x V(f(GHz))</td><td>Force to Engage (Lbs MAX) 3 & Disengage (Lbs MAX) 1.5</td><td>Moisture Resistance MIL-STD-202, Method 106</td></tr><tr><td>RF Leakage (dB MIN) (Interface Only, Fully Mated) -(90-f(GHz))</td><td>Center Contact Captivation</td><td>Corrosion - MIL-STD-202, Method 101, Condition B</td></tr><tr><td>Corona, 70,000 Ft (VRMS MIN) 250</td><td>Axial (Lbs) FROM INTERFACE 6 FROM FLANGE 3</td><td></td></tr><tr><td>Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 1000</td><td>Weight (Grams) TBD</td><td></td></tr><tr><td>Contact Resistance (Milliohms MAX)</td><td></td><td></td></tr><tr><td>Center Contact 3.0</td><td></td><td></td></tr><tr><td>Outer Contact 2.0</td><td></td><td></td></tr><tr><td>Cable to Housing 0.5</td><td></td><td></td></tr><tr><td>RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 670</td><td></td><td></td></tr><tr><td>I.R.(Megohms MIN) 5000</td><td></td><td></td></tr></table>			ELECTRICAL	MECHANICAL	ENVIRONMENTAL	Nominal Impedance (Ohms) 50	Interface Dimensions Per MIL-STD-348A Fig. 321.1	TEMPERATURE RATING -65° TO +125°C	Frequency Range (GHz) DC to 18	Mating Characteristics:	Vibration MIL-STD-202, Method 204, Condition D	Volt Rating (VRMS MAX) @ Sea Level 335	Insertion (MAX Lbs) N/A	Shock MIL-STD-202, Method 213, Condition I	VSWR 1.04+.006f(GHz)	Withdrawal (MIN Oz) N/A	Thermal Shock MIL-STD-202, Method 107, Condition B	Insertion Loss (dB MAX) .03x V(f(GHz))	Force to Engage (Lbs MAX) 3 & Disengage (Lbs MAX) 1.5	Moisture Resistance MIL-STD-202, Method 106	RF Leakage (dB MIN) (Interface Only, Fully Mated) -(90-f(GHz))	Center Contact Captivation	Corrosion - MIL-STD-202, Method 101, Condition B	Corona, 70,000 Ft (VRMS MIN) 250	Axial (Lbs) FROM INTERFACE 6 FROM FLANGE 3		Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 1000	Weight (Grams) TBD		Contact Resistance (Milliohms MAX)			Center Contact 3.0			Outer Contact 2.0			Cable to Housing 0.5			RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 670			I.R.(Megohms MIN) 5000			<table><tr><td>HOUSING</td><td>STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303</td><td>PASSIVATE PER QQ-P-35</td></tr><tr><td>DIELECTRIC</td><td>PTFE FLUOROCARBON PER ASTM-D-1457</td><td>N/A</td></tr><tr><td>CENTER CONTACT</td><td>BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H</td><td>GOLD PLATE PER MIL-G-45204</td></tr><tr><td>EMI GASKET</td><td>CONDUCTIVE ELASTOMERS PER MIL-G-83528</td><td>N/A</td></tr><tr><td>O-RING</td><td>FLUOROSILICONE PER MIL-R-25988, CLASS I, TYPE I.</td><td>N/A</td></tr></table>			HOUSING	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	PASSIVATE PER QQ-P-35	DIELECTRIC	PTFE FLUOROCARBON PER ASTM-D-1457	N/A	CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204	EMI GASKET	CONDUCTIVE ELASTOMERS PER MIL-G-83528	N/A	O-RING	FLUOROSILICONE PER MIL-R-25988, CLASS I, TYPE I.	N/A
ELECTRICAL	MECHANICAL	ENVIRONMENTAL																																																															
Nominal Impedance (Ohms) 50	Interface Dimensions Per MIL-STD-348A Fig. 321.1	TEMPERATURE RATING -65° TO +125°C																																																															
Frequency Range (GHz) DC to 18	Mating Characteristics:	Vibration MIL-STD-202, Method 204, Condition D																																																															
Volt Rating (VRMS MAX) @ Sea Level 335	Insertion (MAX Lbs) N/A	Shock MIL-STD-202, Method 213, Condition I																																																															
VSWR 1.04+.006f(GHz)	Withdrawal (MIN Oz) N/A	Thermal Shock MIL-STD-202, Method 107, Condition B																																																															
Insertion Loss (dB MAX) .03x V(f(GHz))	Force to Engage (Lbs MAX) 3 & Disengage (Lbs MAX) 1.5	Moisture Resistance MIL-STD-202, Method 106																																																															
RF Leakage (dB MIN) (Interface Only, Fully Mated) -(90-f(GHz))	Center Contact Captivation	Corrosion - MIL-STD-202, Method 101, Condition B																																																															
Corona, 70,000 Ft (VRMS MIN) 250	Axial (Lbs) FROM INTERFACE 6 FROM FLANGE 3																																																																
Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 1000	Weight (Grams) TBD																																																																
Contact Resistance (Milliohms MAX)																																																																	
Center Contact 3.0																																																																	
Outer Contact 2.0																																																																	
Cable to Housing 0.5																																																																	
RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 670																																																																	
I.R.(Megohms MIN) 5000																																																																	
HOUSING	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	PASSIVATE PER QQ-P-35																																																															
DIELECTRIC	PTFE FLUOROCARBON PER ASTM-D-1457	N/A																																																															
CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204																																																															
EMI GASKET	CONDUCTIVE ELASTOMERS PER MIL-G-83528	N/A																																																															
O-RING	FLUOROSILICONE PER MIL-R-25988, CLASS I, TYPE I.	N/A																																																															
<table><tr><td>COMPONENT</td><td>MATERIAL</td><td>FINISH</td></tr><tr><td>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES</td><td>DRAWN BY DATE 7/18/97</td><td rowspan="3"> AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599</td></tr><tr><td>FRAC. DEC. ANGLES ± 1/64 ± .005 ± 1°</td><td>CHECKED BY </td></tr><tr><td>These drawings and specifications are the property of M/A COM Interconnect Div. and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.</td><td>APP'D BY DATE 7/25/97</td></tr><tr><td colspan="2">USE ASS'Y PROCEDURE</td><td>TITLE DSP 2 HOLE FLANGE MOUNT PLUG RECEPTACLE - ACCEPTS .018±.001 PIN</td></tr><tr><td colspan="2">N/A</td><td>SIZE B CODE IDENT NO. 26805 4551-3356-02 REV 01</td></tr><tr><td colspan="2">SCALE 4:1</td><td>SHEET 1 OF 1</td></tr></table>			COMPONENT	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES	DRAWN BY DATE 7/18/97	AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599	FRAC. DEC. ANGLES ± 1/64 ± .005 ± 1°	CHECKED BY	These drawings and specifications are the property of M/A COM Interconnect Div. and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	APP'D BY DATE 7/25/97	USE ASS'Y PROCEDURE		TITLE DSP 2 HOLE FLANGE MOUNT PLUG RECEPTACLE - ACCEPTS .018±.001 PIN	N/A		SIZE B CODE IDENT NO. 26805 4551-3356-02 REV 01	SCALE 4:1		SHEET 1 OF 1																																												
COMPONENT	MATERIAL	FINISH																																																															
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES	DRAWN BY DATE 7/18/97	AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599																																																															
FRAC. DEC. ANGLES ± 1/64 ± .005 ± 1°	CHECKED BY																																																																
These drawings and specifications are the property of M/A COM Interconnect Div. and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	APP'D BY DATE 7/25/97																																																																
USE ASS'Y PROCEDURE		TITLE DSP 2 HOLE FLANGE MOUNT PLUG RECEPTACLE - ACCEPTS .018±.001 PIN																																																															
N/A		SIZE B CODE IDENT NO. 26805 4551-3356-02 REV 01																																																															
SCALE 4:1		SHEET 1 OF 1																																																															