


DCT 06 2009


DWG. NO. 210962 SH 1 REV. A

REVISIONS

REV.	DESCRIPTION	DATE	APPROVED
A	REV. A' PER ECO NO. 1755	1/22/91	N. Khyat
B	ECO NO. 3501	1/6/99	JR



COUNTER - CLOCKWISE
CIRCULATION



QTY REQD		FSCM NO.	PART OR IDENTIFYING NO.	NOMENCLATURE OR DESCRIPTION		MATERIAL SPECIFICATION	
PARTS LIST							
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:				CONTRACT NO.			
FRACTIONS				DECIMALS			
XX ± .03				ANGLES			
.XXX ± .010				MATERIAL			
FINISH				APPROVALS			
FLAME SPRAY				DRAWN Hagedorn			
DO NOT SCALE DRAWING				CHECKED Hagedorn			
NEXT ASSY				ISSUED			
APPLICATION				DATE 10/10/09			
USED ON				11/2/99			
SIZE A				FSCM NO. 7Y213		DWG. NO. 210962	
CIRCULATOR				C-316S01			
REV. B				SHEET 1 OF 1			

OCT 06 2009



DWG. NO. 22076A SH 1 REV. A

REVISIONS

REV.	DESCRIPTION	DATE	APPROVED
A	REV. A PER ECO No. 1755	1/22/91	N. Kharjat

UNCONTROLLED

FREQUENCY RANGE : 16.11 TO 22.82 GHz
ISOLATION : 20 dB PER JUNCTION
INSERTION LOSS : 0.6 dB PER JUNCTION
1.8 dB MAX. J2 TO J1
0.6 dB MAX. J1 TO J3
VSWR : 1.25 : 1 MAX.
TEMPERATURE : OPERATING 0°C TO +70°C
STORAGE -55°C TO +85°C

QTY REQD		FSCM NO.	PART OR IDENTIFYING NO.	NOMENCLATURE OR DESCRIPTION		MATERIAL SPECIFICATION	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ± .XX ± .XXX ± °				CONTRACT NO.			
MATERIAL		APPROVALS		DATE		PARTS LIST	
FINISH		DRAWN D.N.		10/11/89		mika	
		CHECKED T. Nguyen		11/02/89		SPECS C-316S01	
		ISSUED				SIZE FSCM NO. DWG. NO. REV. A 7Y213 220764 A	
DO NOT SCALE DRAWING		QA A. CHAN		01/28/91		SCALE 1 OF 1	
APPLICATION		NEXT ASSY		USED ON			

