

AN8064SP

Low Drop-out Voltage Regulator


■ Overview

The AN8064SP is a voltage regulator IC with strobe pin capable of switching the output ON/OFF.


Its rated load current is 150mA and output voltage is 4V fixed.

■ Features

- 150mA rated load current and 4V fixed output voltage
- Capable of turning off output by setting the strobe pin to the “L” level
- Minimum input/output voltage difference : typ. 0.25V
- Built-in overcurrent protective circuit
- Surface-mount type 5-pin SIL plastic package



■ Block Diagram



■ 6932852 0012760 45T ■

Panasonic


■ Absolute Maximum Ratings (Ta=25℃)

Parameter	Symbol	Rating	Unit
Supply voltage	V _I	14.4	V
Power dissipation	P _D	500	mW
Operating ambient temperature	T _{opr}	−20 to +75	℃
Storage temperature	T _{stg}	−55 to +125	℃

■ Electrical Characteristics (Ta=25℃)


Parameter	Symbol	Condition	min	typ	max	Unit
Output voltage	V _O	V _I =12V, I _O =150mA	3.84	4	4.16	V
Output voltage range	V _I	V _I =5 to 14.4V, I _O =0 to 150mA	3.76	4	4.24	V
Bias current at no load	I _{bias}	V _I =11V, I _O =0mA	—	2.9	4	mA
Load regulation	REG _L	V _I =11V, I _O =0 to 150mA	—	—	100	mV
Line regulation	REG _{IN}	V _I =5 to 13V, I _O =150mA	—	—	100	mV
Minimum input/output voltage difference	V _{DIF(min.)}	V _I =3.5V, I _O =150mA	—	—	0.6	V
Rush current	I _{rush}	V _I =3.5V, I _O =0mA	—	2.5	—	mA
Output short-circuit current	I _{O(short)}	V _I =11V	350	—	550	mA
Load bias current fluctuation	ΔI _{bias}	V _I =11V, I _O =0 to 150mA	—	—	10	mA
Off-state bias current	I _{OFF}	V _I =11V, V _S =0V	—	—	2	μA
Strobe pin input current	I _S	V _I =11V, V _S =2.5V	—	—	200	μA
Strobe pin threshold voltage	V _{S(TH)}	V _I =11V	0.8	2	2.4	V
Ripple rejection ratio	RR	V _I =9 to 13V, I _O =150mA, f=120kHz	—	55	—	dB

■ Application Circuit



- When using at a low temperature, it is recommended to use capacitors with a low internal impedance (for example, tantalum capacitors) for output capacitors.

■ Characteristics Curve



6932852 0012761 396

Panasonic