



FLEXO® F6 FR

- VW-1, FAR 25
- Easy, Cost And Labor Effective Wraparound Installation
- More Flexible Than Spiral Wrap Of Split Convuluted Tubing
- 25% Edge Overlap
- Resists Chemicals & Solvents
- Cut And Abrasion Resistant



Cut Cleanly
Hot Knife

Material

PET

Grade

F6F

Monofilament Diameter

.008" - .015"

Drawing Number

TF001F6F-WD

Put-Ups

Nominal Size	Part #	Wall Thickness	Monofilament Diameter	Bulk Box	Box A	Box B	Available Colors	Lbs/ 100'
1/8"	F6F0.13TB	.024"	.008"	10,000'	400'	100'	TB	0.20
1/4"	F6F0.25TB	.025"	.010"	3,000'	200'	100'	TB	0.60
3/8"	F6F0.38TB	.025"	.010"	1,200'	150'	75'	TB	1.20
1/2"	F6F0.50TB	.025"	.010"	800'	150'	75'	TB	1.40
3/4"	F6F0.75TB	.025"	.010"	500'	100'	50'	TB	1.60
1"	F6F1.00TB	.038"	.015"	400'	100'	50'	TB	2.00
1 1/4"	F6F1.25TB	.038"	.015"	250'	75'	25'	TB	2.40
1 1/2"	F6F1.50TB	.038"	.015"	200'	75'	25'	TB	2.70
2"	F6F2.00TB	.038"	.015"	150'	50'	25'	TB	3.60


Flexible, Semi-Rigid Split Sleeving Will Not Support Combustion

Flame spread is a vital safety consideration in applications as diverse as home built aircraft wiring and safely managing sound & lighting cables at clubs, concerts and theaters. To accommodate these issues, and to provide unequaled flexibility and access, we've developed this unique sleeving product.


Self-extinguishing F6F fully complies with UL standard VW-1. The addition of a flame inhibitor to our triaxially braided F6 split sleeving provides the perfect solution to a wide range of cable management needs.

Easy slip over installation, complete access along the entire run, economy, durability and UL certified flame retardant make F6F ideal when the goal is to manage wires and cables safely and effectively.

Colors Available:
Black with White Tracer (TB)



The large overlap allows easy installation over splices and incline connectors without exposing wires and cables.



www.techflex.com

800.323.5140 • 973.300.9242 • fax: 973.300.9409
104 Demarest Road • Sparta, NJ 07871

FAR-25 VW-1





FLEXO® F6 FR



Abrasion Resistance
High

Abrasion Test Machine
Taber 5150

Abrasion Test Wheel
Calibrase H-18

Abrasion Test Load
500g

Room Temperature
70°F

Humidity
63%

Slight Scuffing Visible
500 Test Cycles

Visible Wear And Five
Broken Filaments
1,200 Test Cycles

Material Destroyed
1,600 Test Cycles

Pre-Test Weight
3,469.8 mg

Post-Test Weight
3,114.0 mg

Test End Loss Of Mass
Point Of Destruction
355.8 mg



Rating _____ **VW-1**



Chemical Resistance

1=No Effect 4=More Affected
2=Little Effect 5=Severely Affected
3=Affected

Aromatic Solvents	2
Aliphatic Solvents	1
Chlorinated Solvents	3
Weak Bases	1
Salts	1
Strong Bases	2
Salt Water 0-S-1926	1
Hydraulic Fluid MIL-H-5606	1
Lube Oil MIL-L-7808	1
De-Icing Fluid MIL-A-8243	1
Strong Acids	3
Strong Oxidants	2
Esters/Keytones	1
UV Light	1
Petroleum	1
Fungus ASTM G-21	1
Halogen Free	Yes
RoHS	Yes
SVHC	None

Melt Point

ASTM D-2117

446°F (230°C)


Maximum Continuous

Mil-I-23053

257°F (125°C)

Minimum Continuous

-94°F (-70°C)



PHYSICAL PROPERTIES

Monofilament Diameter _____ **.008-.015**
ASTM D-204

Flammability Rating _____ **VW-1**
FMVSS-302 Approved

Recommended Cutting _____ **Scissor/HK**

Colors _____ **1**

Wall Thickness _____ **.024-.038**

Tensile Strength (Yarn) _____ **4-6.5**
ASTM D-2256 Lbs

Specific Gravity ASTM D-792 _____ **1.38**

Moisture Absorption _____ **.1-.2**
% ASTM D-570

Hard Vacuum Data ASTM E-595 at 10-5 torr

TML _____ **.19**

CVM _____ **.04**

WVR _____ **.06**

Smoke D-Max _____ **275**
ASTM E-662

Outgassing _____ **Med**

Oxygen Index _____ **31**
ASTM D-2863