








LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	OWN
AD	00	0		RELEASED PER EC 0512-0235-04	06OCT04	BM

- 1 HOUSING MATERIAL: LIQUID CRYSTAL POLYMER, COLOR: NATURAL.
- 2 CONTACT MATERIAL: PHOSPHOR BRONZE PER UNS ALLOY NO. C51100, TEMPER: H04.
- 3 CONTACT FINISH:(D)
UNDERPLATE (ENTIRE CONTACT):
0.00127 MIN NICKEL PER SAE-AMS-QQ-N-290
ON MATING SURFACES:
FLASH GOLD PER ASTM B 488, OVER
0.00076 MIN PALLADIUM-NICKEL OVER UNDERPLATE, OR
0.00076 MIN GOLD PER ASTM B 488 OVER UNDERPLATE.
ON LEADS:
0.00127 MIN MATTE TIN PER ASTM B 545 OVER UNDERPLATE.
LUBRICATION (MIN MATING SURFACES):
SURFACE CONDITIONER AFTER PLATING.
- 4 PART MARKING LOCATED APPROXIMATELY AS SHOWN.




ROW	D		AB			AC	
	C		AB			AC	
	B		AC			AC	
	A		AB			AB	
	1	2	3	4	5	6	
POWER							
POSITION							
5536626-1							

ROW	D		AC			AC	
	C		AB			AB	
	B		AB			AB	
	A		AC			AC	
	1	2	3	4	5	6	
POWER							
POSITION							
5536626-2							

CODE LETTER	MATING POST LENGTH ± 0.1	LEAD LENGTH (REF)
AC	8	4.25
AB	7.25	4.25

6	1	10	5	11.88	3	8	5536626-2
6	1	10	5	11.88	3	8	5536626-1
E	D	C	B	A	FINISH	NO OF POWER POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.				DIN 9139 01/JUN/93 R. BUCHHEISTER CHK J. SMALLY 10/AUG/93 APVD D.R. BAECHTLE 10/AUG/93		Tyco Electronics Corporation Harrisburg, Pa 17105-3608					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		ASSEMBLY, PIN, POWER, VERTICAL, Z-PACK 2mm FB, 4 ROW, PRESS FIT LEADS, RANDOM SEQUENCED					
		0 PLC ± -		PRODUCT SPEC		SIZE CASE CODE DRAWING NO A1 00779 C=5536626		RESTRICTED TO -			
		1 PLC ± -									
		2 PLC ± 0.1[.005]									
		3 PLC ± -									
4 PLC ± -		APPLICATION SPEC									
ANGLES ± -		FINISH		WEIGHT							
MATERIAL		1 2		3							
CUSTOMER DRAWING				SCALE 4:1		SHEET 1 of 1		REV 0			