

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

75237-0205

Status:

Active

Overview:

GbX® Backplane Connector System

Description:

5-Pair GbX® Backplane Connector System, Open Header, 250 Circuits, Gold (Au)
0.76µm, Pin Length 5.55mm

Documents:

3D Model

Drawing (PDF)

Product Specification PS-75221-999 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Application Tooling Documents

Comments

Component Type

Overview

Product Name

Style

UPC

Backplane Connectors

75237

Backplane

TM-622022099

Open Header

PCB Header

GbX® Backplane Connector System

GbX®

N/A

822348810444

Physical

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Flammability

Guide to Mating Part

Keying to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Columns

Number of Pairs

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Polarized to PCB

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

250

250

Gray (Dark)

200

No

94V-0

No

None

High Performance Alloy (HPA)

Gold

Tin-Lead

High Temperature Thermoplastic

15.821/g

25

5

10

Vertical

2.30mm

No

Yes

1.60mm

Tray

1.85mm

1.85mm

0.762µm


0.762µm

No

Yes

Yes

105°C



Series

image - Reference only

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

75237Series

Mates With

75360 GbX® Daughtercard

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Shield Removal Tool	0622022100
Single Pin Repair Tool	0622022090
Insertion Tool, 5-pair by 25-Wide	0622022050

Termination Interface: Style	Through Hole - Compliant Pin
Electrical	
Current - Maximum per Contact	1A
Data Rate	8.0 Gbps
Real Signals (per 25mm)	135
Shield Type	Ground Plane Shield
Shielded	Yes
Voltage - Maximum	120V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Product Specification	PS-75221-999
Sales Drawing	SD-75237-010

GbX is a registered trademark of Amphenol Corporation.

This document was generated on 01/20/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION