

433.92MHz SUPER HETERODYNE FM/FSK RECEIVER

Cod. 3-2000582

DESCRIPTION:

Super Heterodyne FSK Receiver, manufactured in SMT technology on printed circuit.

HIGHLIGHTS:


Developed according to I-ETS 300 220.

APPLICATIONS:

Security Systems, Data Transmission, Industrial Controls.



MECHANICAL CHARACTERISTICS



Pin functions

- 1 = + 5Vdc
- 2 = GND
- 3 = RF Input(50Ω)
- 7 = GND
- 11 = GND
- 12 = + 5Vdc (PWR Down Control)
- 13 = T.P. - Squelch Out
- 14 = TTL Out
- 15 = RSSI Out
- (T.P. - Audio Out on request)

ABS. MAX. RATINGS:

Power Supply, Vcc, pin 1, 12:	+ 6 Volt
Radio Frequency Input, pin 3:	+10 dBm
Voltage, with respect to GND of output pins:	Vcc
Storage Temperature:	- 40 ÷ + 100 °C
Operational Temperature:	- 20 ÷ + 70 °C

ELECTRICAL CHARACTERISTICS AT THE TEMPERATURE OF + 25°C.

Parameter	Min.	Typ.	Max	Unit	Notes
Power Supply (Vcc)	4.5	5	5.5	Volt	
Supply Current	-	-	9.5	mA	
Receive Frequency	-	433.92	-	MHz	
Overall Frequency Accuracy	-	±50	-	kHz	
Sensitivity (Squelch Threshold) at 25°C	-	-105	-	dBm	Note 1
RF Bandwidth at -3 dB	-	200	-	kHz	
Stopband, fo ± 500KHz	50	-	-	dB	
Antenna Spurious RF Emission	-	-	-65	dBm	
Logic Low	GND	-	0.05	Volt	
Logic High	4.2	-	Vcc	Volt	
Start-up Time	-	-	150	msec	
Max Baud Rate	-	-	19200	Baud	Note 2
Power Down Supply Current	-	-	50	nA	
AF Output Impedance	50	-	-	KΩ	

Note 1.: minimum RF signal level at the nominal frequency, FM modulated with 1KHz square wave and deviation 25KHzp.

Note 2.: -100 dBm input level, modulation with a square wave, deviation 25 KHzp.

Note 3.: all RF parameters measured with the input connected to a 50Ω impd. signal source or load.

Mipot S.p.A. reserves the right to modify the specifications without notice.

MIPOT S.P.A.

Via Corona, n.5
(Zona Ind.)

34701 Cormons (GO)
Italy

Tel.+39 0481 630200 ra.

Fax +39 0481 62387

mipot@mipot.com