




1	2	3	4	5	6	7
				SIGN	DATE	DESCRIPTION
				△	2012.11.12	Updated agency approval data
				APPROVER		
				Janny		
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY Y!!!						
E						
D						
C						
B						
A						



N=Number of poles



Material

- Terminal body (metal housing): Brass(CuZn)
- Terminal screw: Steel Zinc plating “-” slot type
- Wire guard: PhBz ,Tin plated
- Insulator (housing): Thermoplastic (UL94V -0)

Electrical cULus / VDE / TUV

- Voltage rating: 300V/300V/300V
- Current rating: 20A/20A/20A
- Wire range: 2.5mm²/ 0.34-2.5mm²
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque: 5Lb-In/0.5N.m/0.56N.m
- Screw: M3
- Wire strip length: 7-8mm
- Withstanding Voltage: 16KV/2.5KV/2.5KV
- Operating temperature: -30°C to +105°C
- Safety Approval:

Use with OSTOQ 1.0x1.0mm square pin. Withdrawal force: 200-500gf/pole

PART NUMBER:

OSTTJXX5153

- No. of Poles
- 02 2 Poles
 - 03 3 Poles
 -
 - 24 24 Poles

- COLOR
- 0: Black
 - 5: Green (Standard)
 - 6: Blue
 - 8: Grey



ON-SHORE TECHNOLOGY, INC.

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.

TITLE OSTTJ - 5.08mm Series

PART NO.	OSTTJXX5153	DWG NO.	OSTTJXX5153.DWG
APPROVED	CHECKED	DESIGNED	DRAWN
Shi Jun 2006.10.23	Marvin 2006.10.23	Marvin 2006.10.23	Marvin 2006.10.23
SHEET: 01/01		REV.: E	
Tolerance			
X. ±0.50			
X.X ±0.30			
X.XX ±0.10			
X° ±1°			