

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- , - .



© COPYRIGHT - By -

ALL RIGHTS RESERVED.





LOC
DWDIST
—

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B2	REVISED PER ECO-11-005301	16APR11	RK	HMR



MOUNTING SURFACE OF P.C. BOARD
ALL SOLDERING LEADS AND LATCH FEET
MUST BE COPLANAR WITHIN ∇ 0.1 mm.



NOTE:

- MATERIAL:
HOUSING: LCP WITH 30% GF, UL 94V-0, COLOR: NATURE.
CONTACTS: PHOSPHOR BRONZE.
LATCH: STAINLESS.
- FINISH:
CONTACTS: GOLD PLATED (SEE TABLE) ON CONTACT AREA ,
GOLD FLASH ON SOLDER TAILS, WITH ENTIRE
CONTACT UNDERPLATED $1.27\mu\text{m}$ [50 μ] MIN. NICKEL.
LATCH: $2.032\mu\text{m}$ [80 μ] ~ $4.064\mu\text{m}$ [160 μ] MATTE-TIN PLATED
OVER $1.27\mu\text{m}$ [50 μ] MIN. NICKEL PLATED.
- REFLOW SOLDER CAPABLE TO 260°C PER TE CONNECTIVITY TEST SPEC.
109-201, CONDITION B.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± 0.5 1 PLC ± 0.2 2 PLC ± 0.1 3 PLC ± 0.05 4 PLC ± — ANGLES ± 3°
MATERIAL SEE NOTE	FINISH SEE NOTE


QUALIFICATION TEST REPORT
501-57577

DWN J. LAI	15JUN2009
CHK S. CHIEN	15JUN2009
APVD W. KODAMA	15JUN2009
PRODUCT SPEC	108-57503
APPLICATION SPEC	—
WEIGHT	4.43 GRAMS
CUSTOMER DRAWING	—

TRAY	2.5 V	0.762 μm [30 μ] MIN.	1834017-2
TRAY		0.254 μm [10 μ] MIN.	1834017-1
PACKING	VOLTAGE	GOLD PLATED	PART NUMBER

STE TE Connectivity

NAME			
ANGLED SO DIMM SOCKET ASSY, 0.6mm PITCH, 200 POSN, 22.5 DEGRESS TILT			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-1834017	—
SCALE		SHEET	REV
—		1 OF 7	B2




4

3


2

1

LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
DW	—		—	SEE SHEET 1	—	—	—	




RECOMMENDED PCB LAYOUT
TOLERANCE: ± 0.05
FOR 2.5V



RECOMMENDED PCB LAYOUT
TOLERANCE: ± 0.05
FOR 1.8V OF REVERSE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	—	 TE Connectivity		
		CHK	—			
		APVD	—	NAME		
		PRODUCT SPEC	—	ANGLED SO DIMM SOCKET ASSY, 0.6mm PITCH, 200 POSN, 22.5 DEGRESS TILT		
		APPLICATION SPEC	—			
		WEIGHT	—	SIZE	CAGE CODE	DRAWING NO
		CUSTOMER DRAWING		A3	00779	C-1834017
		SCALE	—	SHEET		5 OF 7
		REV	B2			

LOC	DIST	REVISIONS				
DW	—	P	LTR	DESCRIPTION	DATE	APVD
		—	—	SEE SHEET 1	—	—



- (1) DIMENSION

SEMI-HARD TRAY: 330x215x17.5 mm

INNER BOX: 35.5x23x6.5 cm

SHIPPING CARTON: 48x37x23 cm
- (2) MATERIAL

SEMI-HARD TRAY: P.S.

INNER BOX: CORRUGATED FIBER

SHIPPING CARTON: CORRUGATED FIBER
- (3) PACKAGING

15 PCS PER TRAY,

3 TRAYS PER INNER BOX,

6 BOXES PER SHIPPING CARTON.

QUANTITY: 270 PCS
- (4) WEIGHT

N.W.: 1.196 KGs

G.W.: 4.5 KGs

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	—	 TE Connectivity		
		CHK	—			
		APVD	—	NAME		
		PRODUCT SPEC	—	ANGLED SO DIMM SOCKET ASSY, 0.6mm PITCH, 200 POSN, 22.5 DEGRESS TILT		
		APPLICATION SPEC	—			
		WEIGHT	—	SIZE	CAGE CODE	DRAWING NO
		CUSTOMER DRAWING		A3	00779	C-1834017
		SCALE	—	SHEET	6 OF 7	REV B2

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT — By —

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

DW

—

—

SEE SHEET 1

—

—

—

NOTE:

1.MATERIAL:

1.1 EMBOSSED CARRIER: PS

1.2 COVER TAPE: PET

2.QUANTITY:

2.1 PRIMARY: 80 PCS/REEL






2.2 SECONDARY PACKING: 3 REELS/BOX (240 PCS)

3. WEIGHT:

3.1 NET WEIGHT: 1.08 KG/BOX

3.2 GROSS WEIGHT: 3.9 KG/BOX


4. PELLING RESISTANCE: 39g~97g.

5. PELLING SPEED: 300mm/minutes
(400mm MIN.)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	$\pm -$
1 PLC	$\pm -$
2 PLC	$\pm -$
3 PLC	$\pm -$
4 PLC	$\pm -$
ANGLES	$\pm -$
FINISH	$\pm -$

MATERIAL

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

STE

TE Connectivity

NAME

ANGLED SO DIMM SOCKET ASSY, 0.6mm PITCH,
200 POSN, 22.5 DEGRESS TILT

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C-1834017

SCALE

SHEET

7 OF 7

REV

B2