

XXXXX-XY HTLF

LEAD FREE OPTION  
(SEE NOTES 1)

- PACKAGING OPTIONS  
(SEE NOTE 1)

- HIGH TEMPERATURE PLASTIC  
(SEE NOTE 1)

- NO OF  
POSITIONS  
(SEE NOTE 1)

- PIN PLATING  
(SEE SHEET 2

- BASE PART NO.

68000-X XX-XXX XXX LF

- TAIL LENGTH (EXAMPLE BELOW)  
3.0mm=030 12.8mm=128 (SEE NOTE 15 & 16)

- MATTING LENGTH (EXAMPLE BELOW)  
5.0mm=050 25.5mm=255 (SEE NOTE 15 & 16)


- TOTAL NUMBER OF POSITION  
FROM 1 THRU 36 POS. (SEE NOTE 1)

- PIN PLATING (SEE NOTE 13)

 $1=0.76\mu\text{m}$  Au

4= PURE TIN  
8=0.36 $\mu$ m Au

- BASE PART NO.




NOTE 4


□  $.025 \pm .001$   
 $0.64 \pm .03 \text{ TYP}$

□.013 MAX TYP  
0.33


DETAIL P  
TYP BOTH ENDS




TOP VIEW



SIDE VIEW



RECOMMENDED HOLE PATTERN



END VIEW

NOTE 6

## PIN PLATING CODES:

|             |                                                         |
|-------------|---------------------------------------------------------|
| XXXX-1YY    | 30u"/0.76u MIN (SEE NOTE 13) OVER 50u"/1.27u MIN Ni     |
| XXXX-2YY    | 15u"/0.38u MIN (SEE NOTE 13) OVER 50u"/1.27u MIN Ni     |
| XXXX-3YY    | 50u"/1.27u MIN (SEE NOTE 13) OVER 50u"/1.27u MIN Ni     |
| XXXX-4YY    | 100u"/2.54u MIN Sn OVER 50u"/1.27u MIN Ni (SEE NOTE 14) |
| XXXX-4YYHLF |                                                         |
| XXXX-5YY    | 15u"/0.38u MIN (SEE NOTE 13) OVER 50u"/1.27u MIN Ni     |
| XXXX-6YY    | 30u"/0.76u MIN (SEE NOTE 13) OVER 50u"/1.27u MIN Ni     |
| XXXX-7YY    | 30u"/0.76u MIN (SEE NOTE 13) OVER 50u"/1.27u MIN Ni     |
| XXXX-8YY    | 15u"/0.38u MIN (SEE NOTE 13) OVER 50u"/1.27u MIN Ni     |
| XXXX-9YY    | 15u"/0.38u MIN (SEE NOTE 13) OVER 50u"/1.27u MIN Ni     |
| XXXX-0YY    | 30u"/0.76u MIN (SEE NOTE 13) OVER 50u"/1.27u MIN Ni     |

## NOTES

## ①. PART NUMBER OPTIONS:

PIN PLATING CODES (SEE ABOVE)

HIGH TEMP. MATERIAL:

PART NUMBERS WITH AND WITHOUT "H" WILL BE SUPPLIED WITH HIGH TEMPERATURE PLASTIC

NUMBER OF POSITIONS :

ANY NUMBER OF POSITIONS FROM 1 THRU 36.  
 -X00H INDICATES BERGSTRIIP PRODUCT. SEE PAGE 3 FOR SPECIAL GEOMETRY OF THIS CONTINUOUS STRIP PRODUCT.  
 AUTOMATED REELS WILL CONTAIN 36,000 PINS.  
 SEE SPECIFIC PART NUMBERS FOR AVAILABILITY.

PACKAGING :

NO INDICATOR IS STANDARD PACKAGING IN POLY BAGS.

EIGHT DIGIT PART NUMBERS FOLLOWED BY A "T" ARE PACKAGED IN TUBES. SEE SPECIFIC PART NUMBERS FOR AVAILABILITY.

EIGHT DIGIT PART NUMBERS FOLLOWED BY A "C" ARE PACKAGED IN TUBES WITH PICKUP CAP APPLIED. (NOT TOOLED)

BERGSTRIIP™ PART NUMBERS FOLLOWED BY A "B" ARE BULK PRICED.

EIGHT DIGIT PART NUMBERS FOLLOWED BY A "A" ARE PACKAGED IN TAPE AND REEL WITH PICKUP CAP APPLIED.

LEAD FREE :

ADD "HLF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE

## ②. BODY MATERIAL :

BERGSTIK: MANUFACTURER'S OPTION OF NYLON, PCT GLASS FIBER REINFORCED, OR LCP MINERAL FILLED FLAME RETARDENT PER UL-94V-0.  
 COLOR : BLACK

BERGSTRIIP™: PRODUCED WITH HIGH TEMPERATURE LCP THERMOPLASTIC, FLAME RETARDENT PER UL-94V-0.  
 COLOR : BLACK

PART NUMBERS WITH AND WITHOUT "H" SUFFIX WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 20 SECONDS IN WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.

③. PIN MATERIAL : PHOS-BRONZE.

④. MEASURED WITH PART IN RESTRAINED CONDITION.

5. TWO SIDES OF PIN TIPS NOT PLATED. TYPICAL BOTH ENDS.

⑥. 2LBS/0.9KG MIN PIN RETENTION IN EITHER DIRECTION.

⑦. PIN CANNOT PROTRUDE PAST EDGE OF HOUSING. MUST BE .005±.005/.13±.13 FROM END OF HOUSING HOLE.

8. MILITARY BERGSTIK HEADER  
 P/N XXXXX-YYY-MIL.  
 NOT AVAILABLE.

⑨. ±.010/0.25 TOL APPLIES TO ALL "G" TAILS EXCEPT INDICATED PARTS ON TABLE WHERE +.010/0.25 -.000/0.00 APPLIES.

⑩. INDICATED PART NUMBERS ARE PRODUCED AND SOLD IN THE TAIWAN/SINGAPORE AREAS. THESE ARE NOT AVAILABLE IN BERGSTRIIP™ CONTINUOUS STRIP.

⑪. NOTCH CONFIGURATION WILL VARY PER VENDOR'S DISCRETION.

⑫. THESE PRODUCTS MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.

⑬. PLATING OPTIONS:

PERFORMANCE PLATING WILL BE EITHER GOLD OR GXT ON POST OR TAIL, OPTIONALLY (78~295u"/2~7.5u) TIN ON TAIL.

⑭. "THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT ENVIRONMENTS."

⑮. THE OAL DON'T EXCEED 34.5mm

⑯. INCREMENTS BY 0.1mm IN LENGTHS ONLY

17. FOR SPECIAL PACKAGING REQUEST PLEASE CONTACT PRODUCT MANAGER FOR AVAILABILITY

⑰. TO DETERMINE DIMENSIONS:  
 N=NUMBER OF POSITION PER ROW  
 EXAMPLE: 10 POS. N X .100/2.54





|                    |             |          |                                       |                                   |                         |          |              |
|--------------------|-------------|----------|---------------------------------------|-----------------------------------|-------------------------|----------|--------------|
| www.fciconnect.com |             |          | surface<br>ISO 1302                   | tolerance std<br>ISO 406 ISO 1101 | projection<br>ISO 10110 | INCH/MM  |              |
|                    |             |          | TOLERANCES UNLESS OTHERWISE SPECIFIED |                                   |                         |          |              |
| Dr                 | T.BREWBAKER | 01/05/95 | ANGULAR                               | LINEAR                            | 0.X                     | ±0.3     | size<br>A4   |
| Eng                | T.HANNA     | 01/05/95 |                                       |                                   | 0.XX                    | ±0.15    |              |
| Chr                | J.MURPHY    | 01/05/95 | 0°                                    | ±2°                               | 0.XXX                   | ±0.05    | ECN          |
| Appr               | T.HANNA     | 01/05/95 | Product family                        |                                   |                         | Spec ref |              |
|                    |             |          | title                                 |                                   |                         | dwg no   | Rev.         |
|                    |             |          | BERGSTIK® II HEADER                   |                                   |                         | 68000    | DB           |
|                    |             |          | .100/2.54cc SR STRAIGHT               |                                   |                         |          |              |
|                    |             |          | catalog no                            |                                   |                         | CUSTOMER | sheet 2 of 8 |




Copyright FCI.


# BERGSTRIPTM HEADER



NOTE 6



## REEL PACKING DIMENSIONS



|                                       |             |          |                       |                                   |                  |                                                |              |
|---------------------------------------|-------------|----------|-----------------------|-----------------------------------|------------------|------------------------------------------------|--------------|
| www.fciconnect.com                    |             |          | surface<br>ISO 1302 ✓ | tolerance std<br>ISO 406 ISO 1101 | projection<br>A4 | INCH/MM<br>←→                                  |              |
| TOLERANCES UNLESS OTHERWISE SPECIFIED |             |          | ANGULAR               | LINEAR                            | size             | Scale                                          |              |
| Dr                                    | T.BREWBAKER | 01/05/95 |                       |                                   | 0.X              | ±0.3                                           | 1.000        |
| Eng                                   | T.HANNA     | 01/05/95 |                       |                                   | 0.XX             | ±0.15                                          |              |
| Chr                                   | J.MURPHY    | 01/05/95 | 0°                    | ±2°                               | 0.XXX            | ±0.05                                          | ECN          |
| Appr                                  | T.HANNA     | 01/05/95 | Product family        |                                   |                  | BERGSTIK                                       | Spec ref     |
| FCI                                   |             |          | title                 |                                   |                  | BERGSTIK® II HEADER<br>.100/2.54cc SR STRAIGHT | Rev.<br>DB   |
| catalog no                            |             |          | dwg no                |                                   |                  | 68000                                          | sheet 3 of 8 |
|                                       |             |          | CUSTOMER              |                                   |                  |                                                |              |

1

2

3

4

| PRODUCT NUMBER | TOTAL PIN LGTH |        | TAIL LENGTH |        | MATING LENGTH |        | PACKAGING       | NOTES | BERGSTRIPTM<br>AVAILABLE | LF<br>OPTION |
|----------------|----------------|--------|-------------|--------|---------------|--------|-----------------|-------|--------------------------|--------------|
|                | DIM F          | DIM F  | DIM G       | DIM G  | DIM H         | DIM H  |                 |       |                          |              |
|                | ENGLISH        | METRIC | ENGLISH     | METRIC | ENGLISH       | METRIC |                 |       |                          |              |
| 55492-XYH      | 0.315          | 8.00   | 0.095       | 2.41   | 0.120         | 3.05   | POLY BAGS       | ---   | NO                       | OB           |
| 60017-XYH      | 0.620          | 15.75  | 0.210       | 5.33   | 0.310         | 7.87   | POLY BAGS       | ---   | NO                       | OB           |
| 60018-XYH      | 0.660          | 16.76  | 0.250       | 6.35   | 0.310         | 7.87   | POLY BAGS       | ---   | NO                       | OB           |
| 63334-XYH      | 0.435          | 11.05  | 0.095       | 2.41   | 0.240         | 6.10   | POLY BAGS       | ---   | NO                       | OB           |
| 68000-YYY      | 0.425          | 10.80  | 0.095       | 2.41   | 0.230         | 5.84   | POLY BAGS       | -     | YES                      | NOTE 1,12    |
| 68001-YYY      | 0.450          | 11.43  | 0.120       | 3.05   | 0.230         | 5.84   | POLY BAGS/TUBES | -     | YES                      |              |
| 68002-YYY      | 0.480          | 12.19  | 0.150       | 3.81   | 0.230         | 5.84   | POLY BAGS       | -     | YES                      |              |
| 68003-YYY      | 0.525          | 13.34  | 0.195       | 4.95   | 0.230         | 5.84   | POLY BAGS       | ---   | NO                       | OB           |
| 68004-YYY      | 0.525          | 13.34  | 0.107       | 2.72   | 0.318         | 8.08   | POLY BAGS       | -     | YES                      |              |
| 68024-YYY      | 0.568          | 14.43  | 0.150       | 3.81   | 0.318         | 8.08   | POLY BAGS       | -     | YES                      |              |
| 68031-YYY      | 0.513          | 13.03  | 0.183       | 4.65   | 0.230         | 5.84   | POLY BAGS       | -     | NO                       |              |
| 68032-YYY      | 0.543          | 13.79  | 0.213       | 5.41   | 0.230         | 5.84   | POLY BAGS       | ---   | NO                       | OB           |
| 68033-YYY      | 0.708          | 17.98  | 0.473       | 12.01  | 0.135         | 3.43   | POLY BAGS       | -     | NO                       |              |
| 68415-YYY      | 0.615          | 15.62  | 0.115       | 2.92   | 0.400         | 10.16  | POLY BAGS       | -     | NO                       |              |
| 68416-YYY      | 0.813          | 20.65  | 0.483       | 12.27  | 0.230         | 5.84   | POLY BAGS       | -     | NO                       |              |
| 68418-YYY      | 0.730          | 18.54  | 0.400       | 10.16  | 0.230         | 5.84   | POLY BAGS       | -     | NO                       |              |
| 68422-YYY      | 0.631          | 16.03  | 0.213       | 5.41   | 0.318         | 8.08   | POLY BAGS       | -     | NO                       |              |
| 68443-YYY      | 0.755          | 19.18  | 0.425       | 10.80  | 0.230         | 5.84   | POLY BAGS       | ---   | NO                       | OB           |
| 68456-YYY      | 0.825          | 20.96  | 0.115       | 2.92   | 0.610         | 15.49  | POLY BAGS       | ---   | NO                       | OB           |
| 68457-YYY      | 0.548          | 13.92  | 0.130       | 3.30   | 0.318         | 8.08   | POLY BAGS       | -     | NO                       |              |
| 68465-YYY      | 0.925          | 23.50  | 0.595       | 15.11  | 0.230         | 5.84   | POLY BAGS       | ---   | NO                       | OB           |
| 68466-YYY      | 0.925          | 23.50  | 0.128       | 3.25   | 0.697         | 17.70  | POLY BAGS       | -     | NO                       |              |
| 68472-YYY      | 0.913          | 23.19  | 0.413       | 10.49  | 0.400         | 10.16  | POLY BAGS       | ---   | NO                       | OB           |
| 68479-YYY      | 0.718          | 18.24  | 0.388       | 9.86   | 0.230         | 5.84   | POLY BAGS       | ---   | NO                       | OB           |
| 68483-YYY      | 0.835          | 21.21  | 0.417       | 10.59  | 0.318         | 8.08   | POLY BAGS       | ---   | NO                       | OB           |
| 68487-YYY      | 0.705          | 17.91  | 0.110       | 2.79   | 0.495         | 12.57  | POLY BAGS       | ---   | NO                       | OB           |
| 68489-YYY      | 1.095          | 27.81  | 0.765       | 19.43  | 0.230         | 5.84   | POLY BAGS       | ---   | NO                       | OB           |
| 68490-YYY      | 1.025          | 26.04  | 0.695       | 17.65  | 0.230         | 5.84   | POLY BAGS       | ---   | NO                       | OB           |
| 68497-YYY      | 0.612          | 15.54  | 0.085       | 2.16   | 0.427         | 10.85  | POLY BAGS       | -     | NO                       |              |
| 68603-YYY      | 0.555          | 14.10  | 0.120       | 3.05   | 0.335         | 8.51   | POLY BAGS       | -     | NO                       |              |
| 68604-YYY      | 0.600          | 15.24  | 0.120       | 3.05   | 0.380         | 9.65   | POLY BAGS       | -     | NO                       | NOTE 1,12    |



Copyright FCI.

D

|                                                                                       |                                                         |          |                                       |        |        |                                   |          |                                                                                                     |                                                                                                  |       |
|---------------------------------------------------------------------------------------|---------------------------------------------------------|----------|---------------------------------------|--------|--------|-----------------------------------|----------|-----------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------|-------|
| www.fciconnect.com                                                                    |                                                         |          | surface<br>ISO 1302                   |        | ✓      | tolerance std<br>ISO 406 ISO 1101 |          | projection<br> | INCH/MM<br> |       |
|                                                                                       |                                                         |          | TOLERANCES UNLESS OTHERWISE SPECIFIED |        |        |                                   |          |                                                                                                     |                                                                                                  |       |
| Dr                                                                                    | T.BREWBAKER                                             | 01/05/95 | ANGULAR                               | LINEAR | 0.X    |                                   | ±0.3     | size<br>A4                                                                                          | Scale<br>1.000                                                                                   |       |
| Eng                                                                                   | T.HANNA                                                 | 01/05/95 |                                       |        | 0.XX   |                                   | ±0.15    |                                                                                                     |                                                                                                  |       |
| Chr                                                                                   | J.MURPHY                                                | 01/05/95 |                                       |        | 0° ±2° |                                   | 0.XXX    |                                                                                                     |                                                                                                  | ±0.05 |
| Appr                                                                                  | T.HANNA                                                 | 01/05/95 | Product family                        |        |        |                                   | BERGSTIK |                                                                                                     | Spec ref                                                                                         |       |
|  | title<br>BERGSTIK® II HEADER<br>.100/2.54cc SR STRAIGHT |          |                                       |        |        | dwg no<br>68000                   |          |                                                                                                     | Rev.<br>DB                                                                                       |       |
|                                                                                       |                                                         |          |                                       |        |        |                                   |          |                                                                                                     |                                                                                                  |       |
|                                                                                       | catalog no                                              |          |                                       |        |        | CUSTOMER                          |          |                                                                                                     | sheet 4 of 8                                                                                     |       |

REV F - 2006-04-17

1

2

3

PDS: Rev :DB

STATUS:Released

Printed: Apr 01, 2014

1

2

3

4

| PRODUCT NUMBER | TOTAL PIN LGTH |        | TAIL LENGTH |        | MATING LENGTH |        |           |       | BERGSTRIPT™ | LF<br>OPTION |
|----------------|----------------|--------|-------------|--------|---------------|--------|-----------|-------|-------------|--------------|
|                | DIM F          | DIM F  | DIM G       | DIM G  | DIM H         | DIM H  |           |       | AVAILABLE   |              |
|                | ENGLISH        | METRIC | ENGLISH     | METRIC | ENGLISH       | METRIC | PACKAGING | NOTES |             |              |
| 68629-XY       | 0.621          | 15.77  | 0.203       | 5.16   | 0.318         | 8.08   | POLY BAGS | —     | NO          | NOTE 1,12    |
| 68630-XY       | 0.603          | 15.32  | 0.273       | 6.93   | 0.230         | 5.84   | POLY BAGS | —     | NO          |              |
| 68631-XY       | 0.703          | 17.86  | 0.203       | 5.16   | 0.400         | 10.16  | POLY BAGS | —     | NO          |              |
| 68632-XY       | 0.743          | 18.87  | 0.413       | 10.49  | 0.230         | 5.84   | POLY BAGS | —     | NO          |              |
| 68633-XY       | 0.643          | 16.33  | 0.225       | 5.72   | 0.318         | 8.08   | POLY BAGS | —     | NO          |              |
| 68634-XY       | 1.013          | 25.73  | 0.683       | 17.35  | 0.230         | 5.84   | POLY BAGS | —     | NO          |              |
| 68642-XY       | 0.913          | 23.19  | 0.583       | 14.81  | 0.230         | 5.84   | POLY BAGS | —     | NO          |              |
| 68652-XY       | 1.470          | 37.34  | 0.670       | 17.02  | 0.700         | 17.78  | POLY BAGS | —     | NO          |              |
| 68653-XY       | 0.735          | 18.67  | 0.095       | 2.41   | 0.540         | 13.72  | POLY BAGS | —     | NO          |              |
| 68654-XY       | 1.050          | 26.67  | 0.670       | 17.02  | 0.280         | 7.11   | POLY BAGS | —     | NO          |              |
| 68655-XY       | 0.708          | 17.98  | 0.290       | 7.37   | 0.318         | 8.08   | POLY BAGS | —     | NO          |              |
| 68656-XY       | 1.113          | 28.27  | 0.613       | 15.57  | 0.400         | 10.16  | POLY BAGS | —     | NO          |              |
| 68657-XY       | 0.588          | 14.94  | 0.368       | 9.35   | 0.120         | 3.05   | POLY BAGS | —     | NO          |              |
| 68658-XY       | 0.820          | 20.83  | 0.130       | 3.30   | 0.590         | 14.99  | POLY BAGS | —     | NO          |              |
| 68659-XY       | 0.608          | 15.44  | 0.398       | 10.11  | 0.110         | 2.79   | POLY BAGS | —     | NO          |              |
| 68686-XY       | 1.016          | 25.81  | 0.458       | 11.63  | 0.458         | 11.63  | POLY BAGS | —     | NO          |              |
| 68689-XY       | 0.913          | 23.19  | 0.213       | 5.41   | 0.600         | 15.24  | POLY BAGS | —     | NO          |              |
| 68705-XY       | 0.395          | 10.03  | 0.095       | 2.41   | 0.200         | 5.08   | POLY BAGS | —     | NO          |              |
| 68717-XY       | 0.615          | 15.62  | 0.285       | 7.24   | 0.230         | 5.84   | POLY BAGS | —     | NO          |              |
| 68730-XY       | 0.555          | 14.10  | 0.225       | 5.72   | 0.230         | 5.84   | POLY BAGS | —     | NO          |              |
| 68731-XY       | 0.880          | 22.35  | 0.440       | 11.18  | 0.340         | 8.64   | POLY BAGS | —     | NO          |              |
| 68735-XY       | 1.016          | 25.81  | 0.520       | 13.21  | 0.396         | 10.06  | POLY BAGS | —     | NO          |              |
| 68755-XY       | 1.166          | 29.62  | 0.533       | 13.54  | 0.533         | 13.54  | POLY BAGS | —     | NO          |              |
| 68760-XY       | 0.803          | 20.40  | 0.353       | 8.97   | 0.350         | 8.89   | POLY BAGS | —     | NO          |              |
| 68762-XY       | 0.588          | 14.94  | 0.213       | 5.41   | 0.275         | 6.99   | POLY BAGS | —     | NO          |              |
| 68771-XY       | 0.470          | 11.94  | 0.100       | 2.54   | 0.270         | 6.86   | POLY BAGS | —     | NO          |              |
| 68781-XY       | 0.691          | 17.55  | 0.273       | 6.93   | 0.318         | 8.08   | POLY BAGS | —     | NO          |              |

REV F - 2006-04-17

1

2

3

PDS: Rev :DB

STATUS:Released

Printed: Apr 01, 2014

A

B

C

D



Copyright FCI.

D

|                    |             |          |                     |                                   |                        |          |              |
|--------------------|-------------|----------|---------------------|-----------------------------------|------------------------|----------|--------------|
| www.fciconnect.com |             |          | surface<br>ISO 1302 | tolerance std<br>ISO 406 ISO 1101 | projection<br>ISO 1006 | INCH/MM  |              |
|                    |             |          | ANGULAR             | LINEAR                            | size                   | Scale    |              |
| Dr                 | T.BREWBAKER | 01/05/95 |                     |                                   | A4                     | 1.000    |              |
| Eng                | T.HANNA     | 01/05/95 |                     |                                   |                        |          |              |
| Chr                | J.MURPHY    | 01/05/95 | 0° ±2°              |                                   | ECN                    |          |              |
| Appr               | T.HANNA     | 01/05/95 | Product family      |                                   | BERGSTIK               | Spec ref |              |
| FCI                |             |          | title               |                                   |                        | dwg no   | Rev.         |
|                    |             |          | BERGSTIK® II HEADER |                                   |                        | 68000    | DB           |
|                    |             |          | catalog no          |                                   |                        | CUSTOMER | sheet 5 of 8 |

1

2

3

4

| PRODUCT NUMBER | TOTAL PIN LGTH |               | TAIL LENGTH |        | MATING LENGTH |        |                 |         | BERGSTRIPTM | LF        |
|----------------|----------------|---------------|-------------|--------|---------------|--------|-----------------|---------|-------------|-----------|
|                | DIM F          | DIM G         | DIM G       | DIM G  | DIM H         | DIM H  |                 |         | AVAILABLE   | OPTION    |
|                | ENGLISH        | METRIC        | ENGLISH     | METRIC | ENGLISH       | METRIC | PACKAGING       | NOTES   |             |           |
| 68795-XY       | 0.500          | 12.70         | 0.062       | 1.57   | 0.338         | 8.59   | POLY BAGS       | —       | NO          | OB        |
| 68796-XY       | 0.633          | 16.08         | 0.423       | 10.74  | 0.110         | 2.79   | POLY BAGS       | —       | NO          | OB        |
| 68797-XY       | 0.413          | 10.49         | 0.213       | 5.41   | 0.100         | 2.54   | POLY BAGS       | —       | NO          | NOTE 1,12 |
| 69148-XY       | 0.442          | 11.43         | 0.000       | 0.00   | 0.350         | 8.89   | POLY BAGS       | —       | NO          | OB        |
| 69152-XY       | 0.720          | 18.29         | 0.120       | 3.05   | 0.500         | 12.70  | POLY BAGS/TUBES | —       | NO          | OB        |
| 69173-XY       | 0.530          | 13.46         | 0.135       | 3.43   | 0.295         | 7.49   | POLY BAGS       | —       | NO          |           |
| 69188-XY       | 0.751          | 19.08         | 0.333       | 8.46   | 0.318         | 8.08   | POLY BAGS       | —       | NO          |           |
| 69751-XY       | 0.440          | 11.18         | 0.170       | 4.32   | 0.170         | 4.32   | POLY BAGS       | NOTE 10 | NO          | OB        |
| 71417-XY       | 0.664          | 16.87         | 0.115       | 2.92   | 0.449         | 11.40  | POLY BAGS       | NOTE 10 | NO          | OB        |
| 72260-XYH      | 0.930          | 23.62         | 0.090       | 2.29   | 0.740         | 18.80  | POLY BAGS       | —       | NO          | OB        |
| 72323-XYH      | 1.200          | 30.48         | 0.100       | 2.54   | 1.000         | 25.40  | POLY BAGS       | —       | NO          | OB        |
| 72457-XYH      | 1.100          | 27.94         | 0.090       | 2.29   | 0.910         | 23.11  | POLY BAGS       | —       | NO          | OB        |
| 73698-XYH      | 1.100          | 27.94         | 0.120       | 3.05   | 0.880         | 22.35  | POLY BAGS       | —       | NO          |           |
| 74464-XYH      | 1.028          | 26.11         | 0.610       | 15.49  | 0.318         | 8.08   | POLY BAGS       | —       | NO          | OB        |
| 78240-XY       | 0.663          | 16.84         | 0.333       | 8.46   | 0.230         | 5.84   | POLY BAGS       | —       | NO          | OB        |
| 78287-XY       | 0.678          | 17.22         | 0.120       | 3.05   | 0.458         | 11.63  | POLY BAGS       | —       | NO          | OB        |
| 78290-XY       | 1.250          | 31.75         | 0.500       | 12.70  | 0.650         | 16.51  | POLY BAGS       | —       | NO          |           |
| 78511-XY       | 0.538          | 13.67         | 0.120       | 3.05   | 0.318         | 8.08   | POLY BAGS/TUBES | —       | YES         |           |
| 78595-XY       |                | NOT AVAILABLE |             |        |               |        |                 | —       | —           |           |
| 78931-XY       |                | NOT AVAILABLE |             |        |               |        |                 | —       | —           |           |
| 78958-XY       |                | NOT AVAILABLE |             |        |               |        |                 | —       | —           |           |
| 78959-XY       |                | NOT AVAILABLE |             |        |               |        |                 | —       | —           |           |
| 78977-XY       |                | NOT AVAILABLE |             |        |               |        |                 | —       | —           |           |
| 78998-XY       | 0.430          | 10.92         | 0.155       | 3.94   | 0.175         | 4.45   | POLY BAGS       | —       | NO          |           |
| 78999-XY       |                | NOT AVAILABLE |             |        |               |        |                 | —       | —           | NOTE 1,12 |
| 79428-XY       | 0.695          | 17.65         | 0.120       | 3.05   | 0.475         | 12.07  | POLY BAGS       | —       | NO          | OB        |
| 79849-XY       | 0.620          | 15.75         | 0.120       | 3.05   | 0.400         | 10.16  | POLY BAGS       | —       | NO          | OB        |



Copyright FCI.

D

|                    |             |          |                                                         |  |                                   |  |                  |  |              |  |
|--------------------|-------------|----------|---------------------------------------------------------|--|-----------------------------------|--|------------------|--|--------------|--|
| www.fciconnect.com |             |          | surface<br>ISO 1302                                     |  | tolerance std<br>ISO 406 ISO 1101 |  | projection<br>A4 |  | INCH/MM      |  |
|                    |             |          | TOLERANCES UNLESS OTHERWISE SPECIFIED                   |  |                                   |  |                  |  |              |  |
| Dr                 | T.BREWBAKER | 01/05/95 | ANGULAR                                                 |  | LINEAR                            |  | size             |  | Scale        |  |
| Eng                | T.HANNA     | 01/05/95 |                                                         |  |                                   |  | A4               |  | 1.000        |  |
| Chr                | J.MURPHY    | 01/05/95 | 0° ±2°                                                  |  |                                   |  | ECN              |  |              |  |
| Appr               | T.HANNA     | 01/05/95 | Product family                                          |  | BERGSTIK                          |  | Spec ref         |  |              |  |
| FCI                |             |          | title<br>BERGSTIK® II HEADER<br>.100/2.54cc SR STRAIGHT |  |                                   |  | dwg no<br>68000  |  | Rev.<br>DB   |  |
|                    |             |          | catalog no                                              |  |                                   |  | CUSTOMER         |  | sheet 6 of 8 |  |

REV F - 2006-04-17

1

2

3

PDS: Rev :DB

STATUS:Released

Printed: Apr 01, 2014

1

2

3

4

A

B

C

D

A

B

C

D

| PRODUCT NUMBER | TOTAL PIN LGTH |        | TAIL LENGTH |        | MATING LENGTH |        | PACKAGING | NOTES   | BERGSTRIPTM<br>AVAILABLE | LF<br>OPTION |
|----------------|----------------|--------|-------------|--------|---------------|--------|-----------|---------|--------------------------|--------------|
|                | DIM F          | DIM F  | DIM G       | DIM G  | DIM H         | DIM H  |           |         |                          |              |
|                | ENGLISH        | METRIC | ENGLISH     | METRIC | ENGLISH       | METRIC |           |         |                          |              |
| 84918-XYH      | 0.340          | 8.64   | 0.120       | 3.05   | 0.120         | 3.05   | POLY BAGS | ---     | YES                      | OB           |
| 84921-XYH      | 0.370          | 9.40   | 0.150       | 3.81   | 0.120         | 3.05   | POLY BAGS | ---     | YES                      | OB           |
| 86506-XXX      | 0.440          | 11.18  | 0.120       | 3.05   | 0.220         | 5.59   | POLY BAGS | ---     | YES                      | OB           |
| 86579-XXX      | 0.450          | 11.43  | 0.120       | 3.05   | 0.230         | 5.84   | POLY BAGS | NOTE 9  | NO                       | OB           |
| 86634-XXX      |                | NOT    | AVAILABLE   |        |               |        |           | ---     | ---                      | NOTE 1,12    |
| 86635-XXX      |                | NOT    | AVAILABLE   |        |               |        |           | ---     | ---                      |              |
| 86636-XXX      |                | NOT    | AVAILABLE   |        |               |        |           | ---     | ---                      |              |
| 86637-XXX      |                | NOT    | AVAILABLE   |        |               |        |           | ---     | ---                      |              |
| 86638-XXX      |                | NOT    | AVAILABLE   |        |               |        |           | ---     | ---                      |              |
| 86793-XXX      | 0.900          | 22.86  | 0.100       | 2.54   | 0.700         | 17.78  | POLY BAGS | NOTE 10 | NO                       | OB           |
| 86899-XXX      | 1.020          | 25.91  | 0.120       | 3.05   | 0.800         | 20.32  | POLY BAGS | ---     | NO                       | OB           |
| 87185-XXX      | 1.238          | 31.45  | 0.095       | 2.41   | 1.043         | 26.49  | POLY BAGS | NOTE 10 | NO                       |              |
| 87204-XXX      | 0.895          | 22.73  | 0.120       | 3.05   | 0.675         | 17.15  | POLY BAGS | ---     | NO                       | OB           |
| 87241-XXX      | 1.000          | 25.40  | 0.120       | 3.05   | 0.780         | 19.81  | POLY BAGS | ---     | NO                       | OB           |
| 87502-XYH      | 1.130          | 28.70  | 0.110       | 2.79   | 0.920         | 23.37  | POLY BAGS | ---     | NO                       | OB           |
| 87827-XXX      | 0.380          | 9.65   | 0.120       | 3.05   | 0.160         | 4.06   | POLY BAGS | ---     | NO                       |              |
| 87916-XXX      | 1.058          | 26.87  | 0.128       | 3.25   | 0.830         | 21.08  | POLY BAGS | ---     | NO                       | NOTE 1,12    |
| 88005-XXX      | 0.536          | 13.61  | 0.095       | 2.41   | 0.341         | 8.66   | POLY BAGS | NOTE 10 | NO                       | OB           |
| 88706-XXX      | 0.900          | 22.86  | 0.100       | 2.54   | 0.700         | 17.78  | POLY BAGS | ---     | NO                       | OB           |
| 89232-XXX      | 0.325          | 8.26   | 0.000       | 0.00   | 0.230         | 5.84   | POLY BAGS | NOTE 7  | NO                       | OB           |



Copyright FCI.

|                                                                                       |                                                         |          |                         |        |                                   |                 |                                                                                                     |                |                   |  |
|---------------------------------------------------------------------------------------|---------------------------------------------------------|----------|-------------------------|--------|-----------------------------------|-----------------|-----------------------------------------------------------------------------------------------------|----------------|-------------------|--|
| www.fciconnect.com                                                                    |                                                         |          | surface<br>ISO 1302 ✓   |        | tolerance std<br>ISO 406 ISO 1101 |                 | projection<br> |                | INCH/MM<br>←————→ |  |
|                                                                                       |                                                         |          | TOLERANCES UNLESS       |        | OTHERWISE SPECIFIED               |                 |                                                                                                     |                |                   |  |
| Dr                                                                                    | T.BREWBAKER                                             | 01/05/95 | ANGULAR                 | LINEAR | 0.X                               | ±0.3            | size<br>A4                                                                                          | Scale<br>1.000 |                   |  |
| Eng                                                                                   | T.HANNA                                                 | 01/05/95 |                         |        | 0.XX                              | ±0.15           |                                                                                                     |                |                   |  |
| Chr                                                                                   | J.MURPHY                                                | 01/05/95 |                         |        | 0.XXX                             | ±0.05           |                                                                                                     |                |                   |  |
| Appr                                                                                  | T.HANNA                                                 | 01/05/95 | Product family BERGSTIK |        |                                   |                 | ECN Spec ref                                                                                        |                |                   |  |
|  | title<br>BERGSTIK® II HEADER<br>.100/2.54cc SR STRAIGHT |          |                         |        |                                   | dwg no<br>68000 | Rev<br>DE                                                                                           |                |                   |  |
|                                                                                       |                                                         |          |                         |        |                                   |                 |                                                                                                     |                |                   |  |
| catalog no                                                                            |                                                         |          |                         |        | CUSTOMER                          |                 | sheet 7 of 8                                                                                        |                |                   |  |

1

2

3

PDS: Rev :DB

STATUS:Released

Printed: Apr 01, 2014

1

2

3

4

| PRODUCT NUMBER | TOTAL PIN LGTH |        | TAIL LENGTH |        | MATING LENGTH |        |                     |         | BERGSTRIPTM | LF        |
|----------------|----------------|--------|-------------|--------|---------------|--------|---------------------|---------|-------------|-----------|
|                | DIM F          | DIM G  | DIM G       | DIM G  | DIM H         | DIM H  |                     |         | AVAILABLE   | OPTION    |
|                | ENGLISH        | METRIC | ENGLISH     | METRIC | ENGLISH       | METRIC | PACKAGING           | NOTES   |             |           |
| 90522-XY       | 0.668          | 16.97  | 0.135       | 3.43   | 0.433         | 11.00  | POLY BAGS           | NOTE 10 | NO          | OB        |
| 90547-XY       | 0.508          | 12.90  | 0.095       | 2.41   | 0.313         | 7.95   | POLY BAGS           | NOTE 10 | NO          | OB        |
| 90719-XY       | 0.384          | 9.75   | 0.106       | 2.69   | 0.178         | 4.52   | POLY BAGS           | -       | NO          |           |
| 90726-XY       | 0.440          | 11.18  | 0.110       | 2.79   | 0.230         | 5.84   | POLY BAGS           | -       | YES         | OB        |
| 91276-XY       | 1.225          | 31.12  | 0.225       | 5.72   | 0.900         | 22.86  | POLY BAGS           | -       | NO          | NOTE 1,12 |
| 92020-XY       | 0.372          | 9.45   | 0.094       | 2.39   | 0.178         | 4.52   | POLY BAGS           | -       | NO          | OB        |
| 92418-XY       | 0.572          | 14.53  | 0.118       | 3.00   | 0.354         | 8.99   | POLY BAGS           | -       | NO          | OB        |
| 93167-XY       | 0.394          | 10.01  | 0.059       | 1.50   | 0.235         | 5.97   | POLY BAGS           | -       | NO          | OB        |
| 93287-XYH      | 0.585          | 14.86  | 0.085       | 2.16   | 0.400         | 10.16  | POLY BAGS           | -       | NO          |           |
| 93944-XY       | 0.941          | 23.90  | 0.130       | 3.30   | 0.711         | 18.06  | POLY BAGS           | -       | NO          |           |
| 93992-XYH      | 0.415          | 10.54  | 0.085       | 2.16   | 0.230         | 5.84   | POLY BAGS           | -       | NO          |           |
| 94063-XY       | 0.376          | 9.55   | 0.138       | 3.51   | 0.138         | 3.51   | POLY BAGS           | NOTE 10 | NO          |           |
| 94094-XY       | 0.592          | 15.04  | 0.314       | 7.98   | 0.178         | 4.52   | POLY BAGS           | -       | NO          | OB        |
| 94544-XY       | 0.550          | 13.97  | 0.130       | 3.30   | 0.330         | 8.38   | POLY BAGS           | NOTE 10 | NO          | OB        |
| 94611-XYH      | 0.320          | 8.13   | 0.095       | 2.41   | 0.125         | 3.18   | POLY BAGS           | -       | NO          |           |
| 95017-XYH      | 0.560          | 14.22  | 0.060       | 1.52   | 0.400         | 10.16  | POLY BAGS           | -       | NO          | OB        |
| 95103-XY       | 1.064          | 27.03  | 0.433       | 11.00  | 0.531         | 13.49  | POLY BAGS           | NOTE 10 | NO          | OB        |
| 95104-XY       | 0.370          | 9.40   | 0.126       | 3.20   | 0.144         | 3.66   | POLY BAGS           | NOTE 10 | NO          | OB        |
| 95648-XYH      | 0.655          | 16.64  | 0.155       | 3.94   | 0.400         | 10.16  | POLY BAGS           | -       | NO          | OB        |
| 95655-XY       | 1.164          | 29.57  | 0.095       | 2.41   | 0.969         | 24.61  | POLY BAGS           | NOTE 10 | NO          | OB        |
| 98001-XYH      | 0.610          | 15.49  | 0.420       | 10.67  | 0.090         | 2.29   | POLY BAGS           | -       | NO          | OB        |
| 98136-XYH      | 0.475          | 12.07  | 0.095       | 2.41   | 0.280         | 7.11   | POLY BAGS           | -       | NO          | OB        |
| 10004394-XYH   | 0.290          | 7.37   | 0.095       | 2.41   | 0.095         | 2.41   | POLY BAGS           | -       | NO          | OB        |
| 10076764-XYH   | 0.479          | 12.19  | 0.114       | 2.9    | 0.265         | 6.75   | POLY BAGS           | -       | YES         | OB        |
| 10103017-XY    | 0.335          | 8.51   | 0.130       | 3.30   | 0.105         | 2.67   | POLY BAGS           | -       | NO          | OB        |
| 10121349-XY    | 0.626          | 15.9   | 0.120       | 3.05   | 0.406         | 10.3   | POLY BAGS/TAPE REEL | -       | NO          | NOTE 1,12 |

REV F - 2006-04-17

1

2

3

4

PDS: Rev :DB

STATUS:Released

Printed: Apr 01, 2014



Copyright FCI.

D

|                    |             |          |                     |                                   |                         |            |
|--------------------|-------------|----------|---------------------|-----------------------------------|-------------------------|------------|
| www.fciconnect.com |             |          | surface<br>ISO 1302 | tolerance std<br>ISO 406 ISO 1101 | projection<br>A4        | INCH/MM    |
|                    |             |          | ANGULAR             | LINEAR                            | size                    | Scale      |
| Dr                 | T.BREWBAKER | 01/05/95 | 0°                  | ±2°                               | 0.X                     | ±0.3       |
| Eng                | T.HANNA     | 01/05/95 | 0°                  | ±2°                               | 0.XX                    | ±0.15      |
| Chr                | J.MURPHY    | 01/05/95 | 0°                  | ±2°                               | 0.XXX                   | ±0.05      |
| Appr               | T.HANNA     | 01/05/95 | Product family      |                                   | BERGSTIK                | Spec ref   |
|                    |             |          | title               |                                   | BERGSTIK® II HEADER     | dwg no     |
|                    |             |          |                     |                                   | .100/2.54cc SR STRAIGHT | 68000      |
|                    |             |          | catalog no          |                                   | CUSTOMER                | Rev.<br>DB |
|                    |             |          |                     |                                   | sheet 8 of 8            |            |