


- NOTES:
- 1.0 ELECTRICAL SPECIFICATIONS
 - 1.1 FREQUENCY RANGE: DC TO 18.0 GHz
 - 1.2 MAXIMUM INPUT POWER:
 - AT +25°C: 2 WATTS
 - AT +125°C: 0.5 WATTS
 - 1.3 OPERATING TEMPERATURE RANGE:
 - 55°C to +125°C
 - 1.4 IMPEDANCE: 50 OHMS
 - 1.5 MAXIMUM VSWR: 1.03 + 0.005f (GHz)

2.0 MARK UNIT AS SHOWN.
REF.: INK-02611-27-17

3.0 DIMENSIONS IN PARENTHESIS ARE
IN MILLIMETERS.



DWG NO. WAS: 02357-01-00

REV.	DESCRIPTION	DATE
-	RELEASED	3/21/79
A	ECR 6545	6/27/89
A1	REDRAW ON CAD-UPDATE	2/27/92
	MARKING-ADD SPECS.	
B	ECN 12868	8/23/93
C	ECN 13621	5/19/94
C1	ADDED TITLEBLOCK	10/26/05

NOTICE: The information contained in this drawing is proprietary and must not be used without the permission of Emerson Network Power.	CAGE CODE 34078		MIDWEST MICROWAVE	
	 EMERSON Network Power Connectivity Solutions		TITLE TERMINATION OUTLINE DRAWING	
UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES AND TOLERANCES ARE: 3 PLACE DECIMALS ±.005 2 PLACE DECIMALS ±.02 FRACTIONS ±1/64 PARALLELITY: T.I.R. _____ FLATNESS: T.I.R. _____ CONCENTRICITY: T.I.R. _____ ANGLES AND PERPENDICULARITY: ±1°	DRAWN/DATE A.BEATTY 3/27/92	ENG./DATE G.KOZAK 3/30/92	DRAWING NUMBER TRM-2001-MC-NNN-02-01	
	CHECKED/DATE	APPROVED/DATE	REV. C1	
			SCALE: 3=1	SHEET 1 of 1