






NOTES:

1. MATERIAL: A - NYLON, UL94V-0, COLOR: WHITE
B - NYLON, UL94V-0, COLOR: MOLDED BLACK
2. FINISH: SEE TERMINAL DRAWING
3. PRODUCT SPECIFICATION: PS-10-07.
4. PACKAGING: PER PK-2695-001
5. HOUSING TO BE USED WITH CRIMP TERMINAL SERIES 2759, 6459, 41572. PARTS MADE AFTER 4/19/2012 WILL ALSO ACCEPT 4809 AND 8088 SERIES TERMINALS. FOR USE WITH 22-30 GAUGE WIRE WITH (1.57)/.062 DIAMETER MAXIMUM WIRE INSULATION.
6. LAST CIRCUIT NUMBER NOT PRESENT ON 2-6 CKT AND MAY OR MAY NOT BE PRESENT ON 7-16 CKT SIZES.
7. CIRCUIT NUMBER "1" AND ENGINEERING NUMBER TO APPEAR ON PARTS 3 CKTS AND HIGHER.
8. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.
9. THE PARTS LISTED ON THIS DRAWING ARE CONSTRUCTED TO MEET THE REQUIREMENT FOR DIRECT SUPPORT OF UNINSULATED LIVE PARTS AS DESCRIBED IN UL508C.
10. THIS DRAWING REPLACES 26950000-SD.

QUALITY SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
A = 0	REDRAWN IN NX EC NO: 115759 DRWN: JQUILES CHKD: MKIPPER REV APPR: FSMITH	2017/06/01 2017/06/08 2017/06/15	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION UNITS		SCALE		molex® KK 2.54/.100 CRIMP HOUSING 2695 SERIES HALOGEN FREE					
E = 0						MM/IN		5:1							
E = 0			MM	INCH	DRWN BY		DATE		PRODUCT CUSTOMER DRAWING SERIES MATERIAL NUMBER CUSTOMER 2695 SEE CHART GENERAL MARKET						
F = 0			4 PLACES ± ±		JQUILES		2017/06/02								
G = 0			3 PLACES ± ± 0.005		CHK'D BY		DATE								
H = 0			2 PLACES ± 0.13 ± 0.01		MKIPPER		2017/06/08								
I = 0			1 PLACES ± 0.25 ±		APPR BY		DATE								
J = 0			0 PLACES ± ±		FSMITH		2017/06/09								
K = 0			ANGULAR TOL ± 0.5			DRAWING SIZE		THIRD ANGLE PROJECTION		DOCUMENT NUMBER DOC TYPE DOC PART SHEET NUMBER 26950000-SD PSD 000 1 OF 2					
L = 0			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			C									

