

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT

By

ALL RIGHTS RESERVED


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	AV3	REVISED PER ECR-16-009296	28JUN2016	BW	RS



- 1 BRASS PER QQ-B-626.
- 2 BERYLLIUM COPPER PER ASTM-B-196
- 3 NYLON PER ASTM-D-4066, BLACK
- 4 POLYMETHYLPENTENE GENERAL PURPOSE, NATURAL
- 5 0.00076[.000030] MINIMUM GOLD PER MIL-G-45204.
- 6 0.00254[.000100] MINIMUM GOLD PER MIL-G-45204.
- 7 SHIELDED CABLE #26=NAS-702 CLASS A & C, AND MIL-W-16878 TYPES E & EE, SHIELDED CABLE #24=NAS-702 CLASS A & C, AND MIL-W-16878 TYPES E & EE, SHIELDED CABLE #22=NAS-702 CLASS C, AND MIL-W-16878 TYPE E, AND MIL-C-7078A TYPE I NUMBER 1 DIELECTRIC .068 O.D.
- 8 RG-174/U, RG-179A/U, RG-187/U, AND 21-598.
- 9 SHIELDED CABLE #26=NAS-702 CLASS A, AND MIL-C-7078A TYPE II.
10. SEE IS 408-1770
- 11 NYLON PER ASTM-D-4066, NATURAL
- 12 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

12	OBSOLETE	<u>5</u>	<u>5</u>	.034 OUNCES	—	—	0.81[.032]	—	—	—	1-201144-8
		—	—	1.65 GRAMS MAX	<u>8</u>	45368-2	—	9-328666-3	201142-2	201144-1	1-201144-1
	OBSOLETE	<u>6</u>	<u>6</u>	.034 OUNCES	—	—	0.81[.032]	—	—	—	201144-7
	OBSOLETE	<u>6</u>	<u>6</u>	.034 OUNCES	—	—	0.58[.023]	—	—	—	201144-6
		<u>5</u>	<u>5</u>	.034 OUNCES	—	—	0.81[.032]	—	—	—	201144-5
		<u>5</u>	<u>5</u>	.034 OUNCES	—	—	1.07[.042]	—	—	—	201144-3
		<u>5</u>	<u>5</u>	.034 OUNCES	—	—	0.58[.023]	—	—	—	201144-1
		CONTACT PLATING	SHELL PLATING	WEIGHT	CABLE OR WIRE SIZE	CRIMP TOOL	Y	(3) FERRULE QTY=1	(2) SPRING RETENTION QTY=1	(1) SOCKET ASSY QTY=1	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN J. LIPPERT	18 DEC 89	 TE Connectivity
		CHK. M. SNEED	22 FEB 90	
		APPRO. B. ADAMS	22 FEB 90	
DIMENSIONS: mm [INCHES] 		TOLERANCES UNLESS OTHERWISE SPECIFIED: PRODUCT SPEC 108-12021 APPLICATION SPEC		NAME
MATERIAL		WEIGHT		SIZE
-		0		A1
		CUSTOMER DRAWING		CAGE CODE
				DRAWING NO
				RESTRICTED TO
				00779
				201144
				SCALE
				8:1
				SHEET
				1 of 1
				REV
				AV3