




HONEYWELL PART NUMBER
12SX4-T
PRODUCT CODE VDK1085

REV	DOCUMENT	CHANGED BY	CHECK
8	0038449	VS 28APR08	BLR



NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .188±.002 CENTERS
- 2 - TERMINALS ARE PLATED FOR SOLDERING
- 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 250° F
- 4 - MOVABLE CONTACT MATERIAL-24K SOLID GOLD
- 5 - STATIONARY CONTACT MATERIAL - GOLD ALLOY

RELEASE NO.	PR-2264-T
REPLACES	

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES ± THIRD ANGLE PROJECTION 			DRAWN	SPK	13FEB08	Honeywell				
OPERATING FORCE — — — — 2.5-5 OZ		CONTACT ARRANGEMENT SPDT						CHECK	RJ	13FEB08					
RELEASE FORCE— — — — — 1 OZ MIN		30 VOLTS DC RATING			0.030 0.015 0.005			THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC				
DIFFERENTIAL TRAVEL— — — .002 MAX			SEA LEVEL	50,000 FT											
OVERTRAVEL — — — — — .004 MIN		INDUCTIVE			0.5 AMP	0.5 AMP	INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME		REV	
		RESISTIVE			1 AMP	1 AMP				B	I	12SX4-T		8	
		MAXIMUM INRUSH 2 AMP						RASTER			SCALE	-	WEIGHT:.003 LB MAX	SHEET 1 OF 1	
		APPROVALS	KEMA, CE	1A 250 V ~ T125 25E3											
			UL, CSA	1A 125 VAC			BRAND	L22J							