

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT - By -


LOC

DIST


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
F		DOVE TAIL ADDED / Schwalbenschwanz eingefuegt	28JUL2006	C.H.	C.G.
G		DRAWING ADAPTED / Zeichnung angepasst	14AUG2007	Abr	C.G.
H		SPOT WELDING CHANGED INTO LINE WELDING	27SEP2012	Sch	Abr


A-A




B-B



A B




C-C

NOTES
Bemerkungen


- 1 1-3 μm Sn
1-3 μm Sn
- 2 3-4 μm GALVANIC Ag
REST GALV. Sn (1-3 μm)
3-4 μm galvanisch Ag
Rest galv. Sn (1-3 μm)
- 3 WIRE RANGE
Drahtgroessenbereich (mm²): >1-2.5
- 4 INSULATION RANGE FOR SWS Ø6 (mm): 2.0-2.7
Isolationsbereich fuer EDS Ø6

LASER WELDED (LINE)
Laserschweissung (Linie)

Teilansicht A



OPTIONAL

2
1

GERMAN SILVER Neusilber	PLAIN/blank	0-962954-5	H
CuNiSi	PRESILVERED vorversilbert	0-962954-2	H
CuNiSi	PRETINNED vorverzinnt	0-962954-1	H
MATERIAL	FINISH	PART NO.	REV.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	0 PLC ± 1 PLC ± ±0.2mm 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±1.5° FINISH
MATERIAL	

DWN	E. Palmie'	06FEB1995
CHK	H. Lutsch	06FEB1995
APVD		
PRODUCT SPEC	108-18472	
APPLICATION SPEC	114-18118	
WEIGHT	-	
CUSTOMER DRAWING		

TE

TE Connectivity

NAME				Ø 4MM SOCKET CONTACT, SWS Ø 4mm Buchsenkontakt, EDS			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO				
A3	00779	C-962954					
SCALE		SHEET	1 OF 1	REV	H		