




Identification

Part No.

Drawing


Dimensions in mm

Jumper cable

2 x LC duplex
Multi Mode 50/125 μm

Length: a = 1 m
a = 2 m
a = 3 m
a = 4 m
a = 5 m
a = 6 m
a = 7 m
a = 8 m
a = 9 m
a = 10 m

33 01 241 0010 005
33 01 241 0020 005
33 01 241 0030 005
33 01 241 0040 005
33 01 241 0050 005
33 01 241 0060 005
33 01 241 0070 005
33 01 241 0080 005
33 01 241 0090 005
33 01 241 0100 005




Jumper cable

2 x SC duplex
Multi Mode 50/125 μm

Length: a = 1 m
a = 2 m
a = 3 m
a = 4 m
a = 5 m
a = 6 m
a = 7 m
a = 8 m
a = 9 m
a = 10 m

33 01 241 0010 006
33 01 241 0020 006
33 01 241 0030 006
33 01 241 0040 006
33 01 241 0050 006
33 01 241 0060 006
33 01 241 0070 006
33 01 241 0080 006
33 01 241 0090 006
33 01 241 0100 006



Jumper cable

2 x ST duplex
Multi Mode 50/125 μm

Length: a = 1 m
a = 2 m
a = 3 m
a = 4 m
a = 5 m
a = 6 m
a = 7 m
a = 8 m
a = 9 m
a = 10 m

33 01 241 0010 007
33 01 241 0020 007
33 01 241 0030 007
33 01 241 0040 007
33 01 241 0050 007
33 01 241 0060 007
33 01 241 0070 007
33 01 241 0080 007
33 01 241 0090 007
33 01 241 0100 007

