






Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du Propriete de c FCI. Droits de reproduction FCI.

FCI

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NO.
68794




mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		A FCI	
ltr	ecn no	dr	date	linear	.X ± 0.3	projection	INCH/MM	title	
E	N05-015	ZC	6/10/05		.XX ± 0.13				
					.XXX ± 0.05				
				angles	$\pm$	scale	1:1	product family QUICKIE	
				dr	J.W. BAIR 8/1/90				
				enr	M.SMYK 8/1/90				
				chr	M.SMYK 8/1/90	size	A3	dwg no 68794	
				appd	M.SMYK 8/1/90				
sheet index	revision sheet								

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NO.



2 X 5
STYLE B





2 X 7
STYLE C



2 X 8 THUR 2 X 30
STYLE D

NOTES:

- ① SAME PIN POSITION TOLERANCE APPLIES TO BOTH ENDS OF EACH TERMINAL.
- ② MOLDING MATERIAL: 30% GLASS-FILLED POLYESTER, FLAME RETARDANT PER UL-94-V0 COLOR: BLUE.
3. 1° MAX DRAFT PERMISSIBLE ON ALL SURFACES.
4. 4 POUNDS / 1.8 KILOGRAMS MIN. TERMINAL PULL-OUT FORCE.
5. TERMINAL MATERIAL: 3/4 HARD PHOSPHORUS BRONZE.
6. POLARIZING KEYS INSTALLED IN HEADERS.
- ⑦ THIS PRODUCT IS MADE FROM HEADER NO. 66506 AND POLARIZING KEY NO. 66423.
- ⑧ MOLDED-IN KEYS ARE MANUFACTURER'S OPTION.
9. 68794-***LF IS JUST A LEAD FREE PRODUCT.
10. THE HOUSING OF XXXXX-XYLF WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER PROCESS.

mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		FCI www.fciconnect.com									
ltr	ecn no	dr	date	linear	.X ± 0.3				projection 	title HEADER QUICKIE SLIM LINE VERTICAL 4 WALLED									
E					.XX ± 0.13														
					.XXX ± 0.05														
				angles	±					product family QUICKIE size dwg no 68794									
				dr	J.W. BAIR	8/1/90													
				enrg	M.SMYK	8/1/90													
				chr	M.SMYK	8/1/90		scale 1:1	A3										
				appd	M.SMYK	8/1/90													
sheet index		revision sheet																	

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du Propriete de c FCI. Droits de reproduction FCI.

FCI

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

1			2			3							4			5			6
	SIZE	STYLE	DIM A	DIM B	DIM C		DIM J		TERMINAL PLATING				TERM TYPE	CUSTOMER RESTRICTED					
68794-001(LF)	U N A S S I G N E D																		
-002(LF)	U N A S S I G N E D																		
-003(LF)	U N A S S I G N E D																		
-004(LF)	U N A S S I G N E D																		
-005(LF)	U N A S S I G N E D																		
-006(LF)	U N A S S I G N E D																		
-007(LF)	2 x 10	D	1. 28/32. 5	1. 22/31. 0	. 900/22. 86		. 105/2. 67		30U* /. 76u Au OVER 50u* /1. 27u Ni				ROUND	NO					
-008(LF)	2 x 10		1. 28/32. 5	1. 22/31. 0	. 900/22. 86		. 150/3. 81		30U* /. 76u Au OVER 50u* /1. 27u Ni				ROUND						
-009(LF)	2 x 10		1. 28/32. 5	1. 22/31. 0	. 900/22. 86		. 675/17. 15		30U* /. 76u Au OVER 50u* /1. 27u Ni				SQ						
-010(LF)	2 x 10		1. 28/32. 5	1. 22/31. 0	. 900/22. 86		. 105/2. 67		150u* /3. 81u Sn				SQ						
-011(LF)	2 x 10		1. 28/32. 5	1. 22/31. 0	. 900/22. 86		. 150/3. 81		150u* /3. 81u Sn				SQ						
-012(LF)	2 x 10		1. 28/32. 5	1. 22/31. 0	. 900/22. 86		. 675/17. 15		150u* /3. 81u Sn				SQ						
-013(LF)	2 x 13		1. 58/40. 1	1. 52/38. 6	1. 200/30. 48		. 105/2. 67		30U* /. 76u Au OVER 50u* /1. 27u Ni				ROUND						
-014(LF)	2 x 13		1. 58/40. 1	1. 52/38. 6	1. 200/30. 48		. 150/3. 81		30U* /. 76u Au OVER 50u* /1. 27u Ni				ROUND						
-015(LF)	2 x 13		1. 58/40. 1	1. 52/38. 6	1. 200/30. 48		. 675/17. 15		30U* /. 76u Au OVER 50u* /1. 27u Ni				SQ						
-016(LF)	2 x 13		1. 58/40. 1	1. 52/38. 6	1. 200/30. 48		. 105/2. 67		150u* /3. 81u Sn				SQ						
-017(LF)	2 x 13		1. 58/40. 1	1. 52/38. 6	1. 200/30. 48		. 150/3. 81		150u* /3. 81u Sn				SQ						
-018(LF)	2 x 13		1. 58/40. 1	1. 52/38. 6	1. 200/30. 48		. 675/17. 15		150u* /3. 81u Sn										
-019(LF)	2 x 17		1. 98/50. 3	1. 92/48. 8	1. 600/40. 64		. 105/2. 67		30U* /. 76u Au OVER 50u* /1. 27u Ni				ROUND						
-020(LF)	2 x 17		1. 98/50. 3	1. 92/48. 8	1. 600/40. 64		. 150/3. 81		30U* /. 76u Au OVER 50u* /1. 27u Ni				ROUND						
-021(LF)	2 x 17		1. 98/50. 3	1. 92/48. 8	1. 600/40. 64		. 675/17. 15		30U* /. 76u Au OVER 50u* /1. 27u Ni				SQ						
-022(LF)	2 x 17		1. 98/50. 3	1. 92/48. 8	1. 600/40. 64		. 105/2. 67		150u* /3. 81u Sn				SQ						
-023(LF)	2 x 17		1. 98/50. 3	1. 92/48. 8	1. 600/40. 64		. 150/3. 81		150u* /3. 81u Sn				SQ						
-024(LF)	2 x 17		1. 98/50. 3	1. 92/48. 8	1. 600/40. 64		. 675/17. 15		150u* /3. 81u Sn				SQ						
-025(LF)	2 x 20		2. 28/57. 9	2. 22/56. 4	1. 900/48. 26		. 105/2. 67		30U* /. 76u Au OVER 50u* /1. 27u Ni				ROUND						
-026(LF)	2 x 20		2. 28/57. 9	2. 22/56. 4	1. 900/48. 26		. 150/3. 81		30U* /. 76u Au OVER 50u* /1. 27u Ni				ROUND						
-027(LF)	2 x 20		2. 28/57. 9	2. 22/56. 4	1. 900/48. 26		. 675/17. 15		30U* /. 76u Au OVER 50u* /1. 27u Ni				SQ						
-028(LF)	2 x 20		2. 28/57. 9	2. 22/56. 4	1. 900/48. 26		. 105/2. 67		150u* /3. 81u Sn				SQ						
-029(LF)	2 x 20		2. 28/57. 9	2. 22/56. 4	1. 900/48. 26		. 150/3. 81		150u* /3. 81u Sn				SQ						
-030(LF)	2 x 20		2. 28/57. 9	2. 22/56. 4	1. 900/48. 26		. 675/17. 15		150u* /3. 81u Sn				SQ						
-031(LF)	2 x 25		2. 78/70. 6	2. 72/69. 1	2. 400/60. 96		. 105/2. 67		30U* /. 76u Au OVER 50u* /1. 27u Ni				ROUND						
-032(LF)	2 x 25		2. 78/70. 6	2. 72/69. 1	2. 400/60. 96		. 150/3. 81		30U* /. 76u Au OVER 50u* /1. 27u Ni				ROUND						
-033(LF)	2 x 25		2. 78/70. 6	2. 72/69. 1	2. 400/60. 96		. 675/17. 15		30U* /. 76u Au OVER 50u* /1. 27u Ni				SQ						
-034(LF)	2 x 25		2. 78/70. 6	2. 72/69. 1	2. 400/60. 96		. 105/2. 67		150u* /3. 81u Sn				SQ						
66506-035(LF)	2 x 25	D	2. 78/70. 6	2. 72/69. 1	2. 400/60. 96		. 150/3. 81		150u* /3. 81u Sn				SQ	NO					

mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		 www.fciconnect.com			
ltr	ecn no	dr	date	linear	.X ± 0.3			projection	title HEADER QUICKIE SLIM LINE VERTICAL 4 WALLED				
E					.XX ± 0.13								
					.XXX ± 0.05								
				angles	±				product family QUICKIE size dwg no 68794				
				dr	J.W. BAIR	8/1/90	INCH/MM						
				enr	M.SMYK	8/1/90	← →						
				chr	M.SMYK	8/1/90	scale	1:1	A3	sheet 3 of 8			
				appd	M.SMYK	8/1/90							
sheet index	revision												
	sheet												

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du Propriete de c FCI. Droits de reproduction FCI.

FCI

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

A

B

C

D

1			2			3							4	5			6
	SIZE	STYLE	DIM A	DIM B	DIM C	DIM J	TERMINAL PLATING			TERM TYPE	CUSTOMER RESTRICTED						
68794-036(LF)	2 X 25	D	2. 78/70. 6	2. 72/69. 1	2. 400/60. 96	. 675/17. 15	150u"/3. 81u TIN			SQUARE	ND						
-037(LF)	2 X 7	C	. 98/24. 9	. 92/23. 4	. 600/15. 24	. 105/2. 67	30u' /0. 76U Au OVER 50u' /1. 27u Ni			ROUND							
-038(LF)	2 X 7					. 150/3. 81	30u' /0. 76U Au OVER 50u' /1. 27u Ni			ROUND							
-039(LF)	2 X 7					. 675/17. 15	30u' /0. 76U Au OVER 50u' /1. 27u Ni			SQUARE							
-040(LF)	2 X 7					. 105/2. 67	150u"/3. 81u TIN			SQUARE							
-041(LF)	2 X 7					. 150/3. 81	150u"/3. 81u TIN			SQUARE							
-042(LF)	2 X 7	C	. 98/24. 9	. 92/23. 4	. 600/15. 24	. 675/17. 15	150u"/3. 81u TIN			SQUARE							
-043(LF)	2 X 8	D	1. 08/27. 4	1. 02/25. 9	. 700/17. 78	. 105/2. 67	30u' /0. 76U Au OVER 50u' /1. 27u Ni			ROUND							
-044(LF)	2 X 8					. 150/3. 81	30u' /0. 76U Au OVER 50u' /1. 27u Ni			ROUND							
-045(LF)	2 X 8					. 675/17. 15	30u' /0. 76U Au OVER 50u' /1. 27u Ni			SQUARE							
-046(LF)	2 X 8					. 105/2. 67	150u"/3. 81u TIN			SQUARE							
-047(LF)	2 X 8					. 150/3. 81	150u"/3. 81u TIN			SQUARE							
-048(LF)	2 X 8	D	1. 08/27. 4	1. 02/25. 9	. 700/17. 78	. 675/17. 15	150u"/3. 81u TIN			SQUARE	ND						
-049(LF)	U N A S S I G N E D																
-050(LF)	2 X 10	D	1. 28/32. 5	1. 22/31. 0	. 900/22. 86	. 150/3. 81	30u' /. 76u GXT WITH GOLD FLASH			ROUND	ND						
-051(LF)	2 X 13	D	1. 58/40. 1	1. 52/38. 6	1. 200/30. 48												
-052(LF)	2 X 17	D	1. 98/50. 3	1. 92/48. 8	1. 600/40. 64												
-053(LF)	2 X 23	D	2. 28/57. 9	2. 22/56. 4	1. 900/48. 26												
-054(LF)	2 X 25	D	2. 78/70. 6	2. 72/69. 1	2. 400/60. 96												
-055(LF)	2 X 7	C	. 98/24. 9	. 92/23. 4	. 600/15. 24												
-056(LF)	2 X 8	D	1. 08/27. 4	1. 02/25. 9	. 700/17. 78	. 150/3. 81	30u' /. 76u GXT WITH GOLD FLASH										
-057(LF)	2 X 30		3. 28/83. 3	3. 22/81. 8	2. 900/73. 66	. 105/2. 67	30u' /0. 76U Au OVER 50u' /1. 27u Ni										
-058(LF)	2 X 30					. 150/3. 81	30u' /0. 76U Au OVER 50u' /1. 27u Ni			ROUND							
-059(LF)	2 X 30					. 675/17. 15	30u' /0. 76U Au OVER 50u' /1. 27u Ni			SQUARE							
-060(LF)	2 X 30					. 105/2. 67	150u"/3. 81u TIN			SQUARE							
-061(LF)	2 X 30					. 150/3. 81	150u"/3. 81u TIN			SQUARE							
-062(LF)	2 X 30					. 675/17. 15	150u"/3. 81u TIN			SQUARE							
-063(LF)	2 X 30					. 105/2. 67	30u' /. 76u GXT WITH GOLD FLASH			ROUND							
-064(LF)	2 X 30					. 150/3. 81	30u' /. 76u GXT WITH GOLD FLASH			ROUND							
-065(LF)	2 X 30	D	3. 28/83. 3	3. 22/81. 8	2. 900/73. 66	. 675/17. 15	30u' /. 76u GXT WITH GOLD FLASH			SQUARE							
-066(LF)	U N A S S I G N E D																
-067(LF)	U N A S S I G N E D																
-068(LF)	2 X 7	C	. 98/24. 9	. 92/23. 4	. 600/15. 24	. 105/2. 67	30u' /. 76u GXT WITH GOLD FLASH			ROUND							
-069(LF)	2 X 7	C	. 98/24. 9	. 92/23. 4	. 600/15. 24	. 675/17. 15	30u' /. 76u GXT WITH GOLD FLASH			SQUARE							
68794-070(LF)	2 X 8	D	1. 08/27. 4	1. 02/25. 9	. 700/17. 78	. 105/2. 67	30u' /. 76u GXT WITH GOLD FLASH			ROUND	ND						

mat'l. code

tr
ecn no
dr
date

E

linear

angles

dr
enr
chr
appd

sheet
index

tolerances unless
otherwise specified

.X ± 0.3
.XX ± 0.13
.XXX ± 0.05
±

CUSTOMER
COPY

projection

INCH/MM

scale

1:1

A3

product family
size

68794

code

sheet
4 of 8

A

B

C

mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		 www.fciconnect.com						
ltr	ecn no	dr	date	linear	.X ± 0.3			projection		title HEADER QUICKIE SLIM LINE VERTICAL 4 WALLED						
E					.XX ± 0.13											
					.XXX ± 0.05											
				angles	±			INCH/MM ←→	scale 1:1	product family QUICKIE size dwg no A3 68794		code sheet 4 of 8				
				dr	J.W. BAIR	8/1/90										
				enr	M.SMYK	8/1/90										
				chr	M.SMYK	8/1/90										
				appd	M.SMYK	8/1/90										
sheet index	revision sheet															

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du Propriete de c FCI. Droits de reproduction FCI.

FCI

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

	SIZE	STYLE	DIM A	DIM B	DIM C	DIM J	TERMINAL PLATING	TERM TYPE	CUSTOMER RESTRICTED
68794-071(LF)	2 X 8	D	1.08/27.4	1.02/25.9	.700/17.78	.675/17.15	30u"/0.76u GXT WITH GOLD FLASH	SQ	NO
-072(LF)	2 X 10		1.28/32.5	1.22/31.0	.900/22.86	.105/2.67		RD	
-073(LF)	2 X 10		1.28/32.5	1.22/31.0	.900/22.86	.675/17.15		SQ	
-074(LF)	2 X 13		1.58/40.1	1.52/38.6	1.200/30.48	.105/2.67		RD	
-075(LF)	2 X 13		1.58/40.1	1.52/38.6	1.200/30.48	.675/17.15		SQ	
-076(LF)	2 X 17		1.98/50.3	1.92/48.8	1.600/40.64	.105/2.67		RD	
-077(LF)	2 X 17		1.98/50.3	1.92/48.8	1.600/40.64	.675/17.15		SQ	
-078(LF)	2 X 20		2.28/57.9	2.22/56.4	1.900/48.26	.105/2.67		RD	
-079(LF)	2 X 20		2.28/57.9	2.22/56.4	1.900/48.26	.675/17.15		SQ	
-080(LF)	2 X 25		2.78/70.6	2.72/69.1	2.400/60.96	.105/2.67		RD	
-081(LF)	2 X 25	D	2.78/70.6	2.72/69.1	2.400/60.96	.675/17.15	30u"/0.76u GXT WITH GOLD FLASH	SQ	
-082(LF)	UNASSIGNED								
-083(LF)	UNASSIGNED								
-084(LF)	UNASSIGNED								
-085(LF)	2 X 7	C	.98/24.9	.92/23.4	.600/15.24	.105/2.67	15u"/.38u Au OVER 50u"/1.27u Ni	RD	
-086(LF)	2 X 7	C	.98/24.9	.92/23.4	.600/15.24	.150/3.81		RD	
-087(LF)	2 X 7	C	.98/24.9	.92/23.4	.600/15.24	.675/17.15		SQ	
-088(LF)	2 X 8	D	1.08/27.4	1.02/25.9	.700/17.78	.105/2.67		RD	
-089(LF)	2 X 8		1.08/27.4	1.02/25.9	.700/17.78	.150/3.81		RD	
-090(LF)	2 X 8		1.08/27.4	1.02/25.9	.700/17.78	.675/17.15		SQ	
-091(LF)	2 X 10		1.28/32.5	1.22/31.0	.900/22.86	.105/2.67		RD	
-092(LF)	2 X 10		1.28/32.5	1.22/31.0	.900/22.86	.150/3.81		RD	
-093(LF)	2 X 10		1.28/32.5	1.22/31.0	.900/22.86	.675/17.15		SQ	
-094(LF)	2 X 13		1.58/40.1	1.52/38.6	1.200/30.48	.105/2.67		RD	
-095(LF)	2 X 13		1.58/40.1	1.52/38.6	1.200/30.48	.150/3.81		RD	
-096(LF)	2 X 13		1.58/40.1	1.52/38.6	1.200/30.48	.675/17.15		SQ	
-097(LF)	2 X 17		1.98/50.3	1.92/48.8	1.600/40.64	.105/2.67		RD	
-098(LF)	2 X 17		1.98/50.3	1.92/48.8	1.600/40.64	.150/3.81		RD	
-099(LF)	2 X 17		1.98/50.3	1.92/48.8	1.600/40.64	.675/17.15		SQ	
-100(LF)	2 X 20		2.28/57.9	2.22/56.4	1.900/48.26	.105/2.67		RD	
-101(LF)	2 X 20		2.28/57.9	2.22/56.4	1.900/48.26	.150/3.81		RD	
-102(LF)	2 X 20		2.28/57.9	2.22/56.4	1.900/48.26	.675/17.15		SQ	
-103(LF)	2 X 25		2.78/70.6	2.72/69.1	2.400/60.96	.105/2.67		RD	
-104(LF)	2 X 25		2.78/70.6	2.72/69.1	2.400/60.96	.150/3.81		RD	
68794-105(LF)	2 X 25	D	2.78/70.6	2.72/69.1	2.400/60.96	.675/17.15	15u"/.38u Au OVER 50u"/1.27u Ni	SQ	NO

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		 www.fciconnect.com			
ltr	ecn no	dr	date	linear	.X ± 0.3	projection	title		
E					.XX ± 0.13				HEADER QUICKIE SLIM LINE VERTICAL 4 WALLED
					.XXX ± 0.05				
				angles	±	INCH/MM	product family QUICKIE		
				dr	J.W. BAIR			8/1/90	code
				enrg	M.SMYK			8/1/90	
				chr	M.SMYK			8/1/90	
				appd	M.SMYK			8/1/90	
sheet index	revision sheet					scale 1:1	A3	68794	sheet 5 of 8

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du Propriete de c FCI. Droits de reproduction FCI.

FCI

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NO.	SIZE	STYLE	DIM A	DIM B	DIM C	DIM J	TERMINAL PLATING	TERM TYPE	CUSTOMER RESTRICTED
68794-106(LF)	2 X 30	D	3. 28/83. 3	3. 22/81. 8	2. 900/73. 66	. 105/2. 67	15u/. 38u Au OVER 50u*/1. 27u Ni	ROUND	NO
-107(LF)	2 X 30	D	3. 28/83. 3	3. 22/81. 8	2. 900/73. 66	. 150/3. 81	15u/. 38u Au OVER 50u*/1. 27u Ni	ROUND	
-108(LF)	2 X 30	D	3. 28/83. 3	3. 22/81. 8	2. 900/73. 66	. 675/17. 15	15u/. 38u Au OVER 50u*/1. 27u Ni	SQ	
-109(LF)	2 X 5	B	. 780/19. 81	. 72/18. 3	. 400/10. 16	. 105/2. 67	30u*/. 76u Au OVER 50u*/1. 27u Ni	ROUND	
-110(LF)						. 150/3. 81	30u*/. 76u Au OVER 50u*/1. 27u Ni	ROUND	
-111(LF)						. 675/17. 15	30u*/. 76u Au OVER 50u*/1. 27u Ni	SQ	
-112(LF)						. 105/2. 67	150u*/3. 81u Sn	SQ	
-113(LF)						. 150/3. 81	150u*/3. 81u Sn	SQ	
-114(LF)						. 675/17. 15	150u*/3. 81u Sn	SQ	
-115(LF)						. 105/2. 67	15u*/. 38u Au OVER 50u*/1. 27u Ni	ROUND	
-116(LF)						. 150/3. 81	15u*/. 38u Au OVER 50u*/1. 27u Ni	ROUND	
-117(LF)						. 675/17. 15	15u*/. 38u Au OVER 50u*/1. 27u Ni	SQ	
-118(LF)						. 105/2. 67	30u*/. 76u GXT WITH GOLD FLASH	ROUND	
-119(LF)						. 150/3. 81	30u*/. 76u GXT WITH GOLD FLASH	ROUND	
68794-120(LF)	2 x 5	B	. 780/19. 81	. 72/18. 3	. 400/10. 16	. 675/17. 15	30u*/. 76u GXT WITH GOLD FLASH	SQ	NO
68794-121(LF)	DISCONTINUED								
THRU (LF)									
68794-216(LF)									
68794-217(LF)	2 x 12	D	1. 48/38. 0	1. 42/36. 1	1. 100/27. 94	. 105/2. 67	15u/. 38u Au OVER 50u*/1. 27u Ni	ROUND	NO
-218(LF)						. 105/2. 67	30u*/. 76u Au OVER 50u*/1. 27u Ni	ROUND	
-219(LF)						. 105/2. 67	30u*/. 76u GXT WITH GOLD FLASH	ROUND	
-220(LF)						. 105/2. 67	150u*/3. 81u Sn	SQ	
-221(LF)						. 150/3. 81	15u/. 38u Au OVER 50u*/1. 27u Ni	ROUND	
-222(LF)						. 150/3. 81	30u*/. 76u Au OVER 50u*/1. 27u Ni	ROUND	
-223(LF)						. 150/3. 81	30u*/. 76u GXT WITH GOLD FLASH	ROUND	
-224(LF)						. 150/3. 81	150u*/3. 81u Sn	SQ	
-225(LF)						. 675/17. 15	15u/. 38u Au OVER 50u*/1. 27u Ni	SQ	
-226(LF)						. 675/17. 15	30u*/. 76u Au OVER 50u*/1. 27u Ni	SQ	
-227(LF)						. 675/17. 15	30u*/. 76u GXT WITH GOLD FLASH	SQ	
-228(LF)	2 x 12		1. 48/38. 0	1. 42/36. 1	1. 100/27. 94	. 675/17. 15	150u*/3. 81u Sn	SQ	
-229(LF)	2 x 15		1. 78/45. 2	1. 72/43. 7	1. 400/35. 56	. 105/2. 67	15u/. 38u Au OVER 50u*/1. 27u Ni	ROUND	
-230(LF)						. 105/2. 67	30u*/. 76u Au OVER 50u*/1. 27u Ni	ROUND	
-231(LF)						. 105/2. 67	30u*/. 76u GXT WITH GOLD FLASH	ROUND	
-232(LF)						. 105/2. 67	150u*/3. 81u Sn	SQ	
68794-233(LF)	2 x 15	D	1. 78/45. 2	1. 72/43. 7	1. 400/35. 56	. 150/3. 81	15u/. 38u Au OVER 50u*/1. 27u Ni	ROUND	NO

mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		 www.fciconnect.com							
ltr	ecn no	dr	date	linear	.X ± 0.3				title	HEADER QUICKIE SLIM LINE VERTICAL 4 WALLED							
E					.XX ± 0.13												
					.XXX ± 0.05												
				angles	±				product family	QUICKIE	code						
				dr	J.W. BAIR	8/1/90	INCH/MM					size	dwg no	sheet			
				enr	M.SMYK	8/1/90	scale								A3	68794	6 of 8
				chr	M.SMYK	8/1/90											
				appd	M.SMYK	8/1/90											
sheet index	revision																

	POSITION	STYLE	DIM A	DIM B	DIM C	DIM J	TERMINAL PLATING	TERM TYPE	CUSTOMER RESTRICTED
68794-234(LF)	2 X 15	D	1. 78/45. 2	1. 72/43. 7	1. 400/35. 56	. 150/3. 81	30u" / . 76u Au OVER 50u" / 1/. 27u Ni	ROUND	NO
-235(LF)						. 150/3. 81	30u" / . 76u GXT WITH GOLD FLASH	ROUND	
-236(LF)						. 150/3. 81	150u" / 3. 81u Sn	SQ	
-237(LF)						. 675/17. 15	15u" / . 38u Au OVER 50u" / 1. 27u Ni	SQ	
-238(LF)						. 675/17. 15	30u" / . 76u Au OVER 50u" / 1/. 27u Ni	SQ	
-239(LF)						. 675/17. 15	30u" / . 76u GXT WITH GOLD FLASH	SQ	
-240(LF)	2 X 15		1. 78/45. 2	1. 72/43. 7	1. 400/35. 56	. 675/17. 15	150u" / 3. 81u Sn	SQ	
-241(LF)	2 X 22		2. 48/63. 0	2. 42/61. 5	2. 100/53. 34	. 105/2. 67	15u" / . 38u Au OVER 50u" / 1. 27u Ni	ROUND	
-242(LF)						. 105/2. 67	30u" / . 76u Au OVER 50u" / 1/. 27u Ni	ROUND	
-243(LF)						. 105/2. 67	30u" / . 76u GXT WITH GOLD FLASH	ROUND	
-244(LF)						. 105/2. 67	150u" / 3. 81u Sn	SQ	
-245(LF)						. 150/3. 81	15u" / . 38u Au OVER 50u" / 1. 27u Ni	ROUND	
-246(LF)						. 150/3. 81	30u" / . 76u Au OVER 50u" / 1/. 27u Ni	ROUND	
-247(LF)						. 150/3. 81	30u" / . 76u GXT WITH GOLD FLASH	ROUND	
-248(LF)						. 150/3. 81	150u" / 3. 81u Sn	SQ	
-249(LF)						. 675/17. 15	15u" / . 38u Au OVER 50u" / 1. 27u Ni	SQ	
-250(LF)						. 675/17. 15	30u" / . 76u Au OVER 50u" / 1/. 27u Ni	SQ	
-251(LF)						. 675/17. 15	30u" / . 76u GXT WITH GOLD FLASH	SQ	
-252(LF)	2 X 22	D	2. 48/63. 0	2. 42/61. 5	2. 100/53. 34	. 675/17. 15	150u" / 3. 81u Sn	SQ	
-253(LF)	2 X 17	A	1. 98/50. 3	1. 92/48. 8	1. 600/40. 64	. 105/2. 67	15u" / . 38u Au OVER 50u" / 1. 27u Ni	SQ	NO
-254(LF)	U N A S S I G N E D								
-255(LF)	2 X 5	B	. 78/19. 8	. 72/18. 3	. 400/10. 16	. 105/2. 67	30u" / . 76u Au OVER 50u" / 1/. 27u Ni	ROUND	YES
-256(LF)	2 X 7	C	. 98/24. 9	. 92/23. 4	. 600/15. 24				
-257(LF)	2 X 8	D	1. 08/27. 4	1. 02/25. 9	. 700/17. 78				
-258(LF)	2 X 10		1. 28/32. 5	1. 22/31. 0	. 900/22. 86				
-259(LF)	2 X 12		1. 48/38. 0	1. 42/36. 1	1. 100/27. 94				
-260(LF)	2 X 13		1. 58/40. 1	1. 52/38. 6	1. 200/30. 48				
-261(LF)	2 X 15		1. 78/45. 2	1. 72/43. 7	1. 400/35. 56				
-262(LF)	2 X 17		1. 98/50. 3	1. 92/48. 8	1. 600/40. 64				
-263(LF)	2 X 20		2. 28/57. 9	2. 22/56. 4	1. 900/48. 26				
-264(LF)	2 X 22		2. 48/63. 0	2. 42/61. 5	2. 100/53. 34				
-265(LF)	2 X 25		2. 78/70. 6	2. 72/69. 1	2. 400/60. 96				
-266(LF)	2 X 30	D	3. 28/83. 3	3. 22/81. 8	2. 900/73. 66	. 105/2. 67	30u" / . 76u Au OVER 50u" / 1/. 27u Ni	ROUND	YES
-267(LF)	U N A S S I G N E D								
68794-268(LF)	2 X 5	B	. 78/19. 8	. 72/18. 3	. 400/10. 16	. 105/2. 67	30u" / . 76u GXT WITH GOLD FLASH	ROUND	YES

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		 www.fciconnect.com	
ltr	ecn no	dr	date	linear	.X ± 0.3	projection 	title HEADER QUICKIE SLIM LINE VERTICAL 4 WALLED	product family QUICKIE	code
E					.XX ± 0.13				
					.XXX ± 0.05				
				angles	±	INCH/MM 	scale 1:1	size A3	dwg no 68794
				dr	J.W. BAIR	8/1/90			
				enr	M.SMYK	8/1/90			
				chr	M.SMYK	8/1/90	sheet 7 of 8		
				appd	M.SMYK	8/1/90			
sheet index	revision sheet								

A

B

1 | 2

3 |

4

	POSITION	STYLE	DIM A	DIM B	DIM C	DIM J	TERMINAL PLATING	TERM TYPE	CUSTOMER RESTRICTED
68794-269(LF)	2 X 7	C	. 98/24. 9	. 92/23. 4	. 600/15. 24	. 105/2. 67	30u" /. 76u GXT WITH GOLD FLASH	ROUND	YES
-270(LF)	2 X 8	D	1. 08/27. 4	1. 02/25. 9	. 700/17. 78				
-271(LF)	2 X 10		1. 28/32. 5	1. 22/31. 0	. 900/22. 86				
-272(LF)	2 X 12		1. 48/38. 0	1. 42/36. 1	1. 100/27. 94				
-273(LF)	2 X 13		1. 58/40. 1	1. 52/38. 6	1. 200/30. 48				
-274(LF)	2 X 15		1. 78/45. 2	1. 72/43. 7	1. 400/35. 56				
-275(LF)	2 X 17		1. 98/50. 3	1. 92/48. 8	1. 600/40. 64				
-276(LF)	2 X 20		2. 28/57. 9	2. 22/56. 4	1. 900/48. 26				
-277(LF)	2 X 22		2. 48/63. 0	2. 42/61. 5	2. 100/53. 34				
-278(LF)	2 X 25		2. 78/70. 6	2. 72/69. 1	2. 400/60. 96				
-279(LF)	2 X 30		3. 28/83. 3	3. 22/81. 8	2. 900/73. 66		30u" /. 76u GXT WITH GOLD FLASH	ROUND	YES
68794-280(LF)	2 X 10	D	1. 28/32. 5	1. 22/31. 0	. 900/22. 86	. 105/2. 67	150u" /3. 81u Sn	SQUARE	NO

A

B

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY		A FCI www.fciconnect.com			
ltr	ecn no	dr	date	linear	.XX±.01/.X±.3		projection 	title HEADER QUICKIE SLIM LINE VERTICAL 4 WALLED				
E					.XXX±.005/.XX±.13							
					.XXX±.0020/.XXX±.051							
				angles	0°±2°			product family Quickie size dwg no A 68794	code —			
				dr	J.W.BAIR	8/1/90						
				engr	M.SMYK	8/1/90						
				chr	M.SMYK	8/1/90	scale 5:1					
				appd	M.SMYK	8/1/90			sheet 8 of 8			
sheet index	revision sheet											

1 |

2 |

PDM: Rev:E

3 |

STATUS Released

Printed: Apr 12, 2011

4