| Part 1027-32J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 3.3 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 90 MHz |
| DCR | 0.85 Ω |
| Max Current | 285 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-66F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 82 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 14 MHz |
| DCR | 7.3 Ω |
| Max Current | 88 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-66G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 82 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 14 MHz |
| DCR | 7.3 Ω |
| Max Current | 88 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-64J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 68 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 15 MHz |
| DCR | 6.7 Ω |
| Max Current | 92 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-64H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 68 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 15 MHz |
| DCR | 6.7 Ω |
| Max Current | 92 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-64G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 68 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 15 MHz |
| DCR | 6.7 Ω |
| Max Current | 92 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-64F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 68 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 15 MHz |
| DCR | 6.7 Ω |
| Max Current | 92 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-64K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 68 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 15 MHz |
| DCR | 6.7 Ω |
| Max Current | 92 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-62K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 56 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 16 MHz |
| DCR | 5.7 Ω |
| Max Current | 100 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-62F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 56 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 16 MHz |
| DCR | 5.7 Ω |
| Max Current | 100 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-62H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 56 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 16 MHz |
| DCR | 5.7 Ω |
| Max Current | 100 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-62G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 56 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 16 MHz |
| DCR | 5.7 Ω |
| Max Current | 100 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-66H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 82 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 14 MHz |
| DCR | 7.3 Ω |
| Max Current | 88 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-70J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 120 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 12 MHz |
| DCR | 13 Ω |
| Max Current | 66 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-60K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 47 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 18 MHz |
| DCR | 4.5 Ω |
| Max Current | 110 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-62J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 56 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 16 MHz |
| DCR | 5.7 Ω |
| Max Current | 100 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-66J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 82 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 14 MHz |
| DCR | 7.3 Ω |
| Max Current | 88 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-66K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 82 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 14 MHz |
| DCR | 7.3 Ω |
| Max Current | 88 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-68F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 100 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 13 MHz |
| DCR | 8 Ω |
| Max Current | 84 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-68G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 100 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 13 MHz |
| DCR | 8 Ω |
| Max Current | 84 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-68H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 100 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 13 MHz |
| DCR | 8 Ω |
| Max Current | 84 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-68J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 100 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 13 MHz |
| DCR | 8 Ω |
| Max Current | 84 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-68K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 100 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 13 MHz |
| DCR | 8 Ω |
| Max Current | 84 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-70F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 120 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 12 MHz |
| DCR | 13 Ω |
| Max Current | 66 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-70H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 120 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 12 MHz |
| DCR | 13 Ω |
| Max Current | 66 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-70K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 120 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 12 MHz |
| DCR | 13 Ω |
| Max Current | 66 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-72F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 150 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 11 MHz |
| DCR | 15 Ω |
| Max Current | 61 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-72G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 150 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 11 MHz |
| DCR | 15 Ω |
| Max Current | 61 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-60J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 47 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 18 MHz |
| DCR | 4.5 Ω |
| Max Current | 110 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-52J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 22 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 25 MHz |
| DCR | 3.3 Ω |
| Max Current | 144 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-70G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 120 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 12 MHz |
| DCR | 13 Ω |
| Max Current | 66 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-54J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 27 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 20 MHz |
| DCR | 3.5 Ω |
| Max Current | 140 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-48J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 15 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 35 MHz |
| DCR | 2.8 Ω |
| Max Current | 157 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-48K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 15 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 35 MHz |
| DCR | 2.8 Ω |
| Max Current | 157 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-50F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 18 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 30 MHz |
| DCR | 3.1 Ω |
| Max Current | 149 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-50G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 18 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 30 MHz |
| DCR | 3.1 Ω |
| Max Current | 149 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-50H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 18 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 30 MHz |
| DCR | 3.1 Ω |
| Max Current | 149 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-50J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 18 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 30 MHz |
| DCR | 3.1 Ω |
| Max Current | 149 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-50K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 18 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 30 MHz |
| DCR | 3.1 Ω |
| Max Current | 149 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-52F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 22 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 25 MHz |
| DCR | 3.3 Ω |
| Max Current | 144 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-52G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 22 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 25 MHz |
| DCR | 3.3 Ω |
| Max Current | 144 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-52H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 22 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 25 MHz |
| DCR | 3.3 Ω |
| Max Current | 144 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-80K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 330 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 7 MHz |
| DCR | 28 Ω |
| Max Current | 45 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-52K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 22 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 25 MHz |
| DCR | 3.3 Ω |
| Max Current | 144 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-72H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 150 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 11 MHz |
| DCR | 15 Ω |
| Max Current | 61 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-54F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 27 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 20 MHz |
| DCR | 3.5 Ω |
| Max Current | 140 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-56K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 33 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 22 MHz |
| DCR | 3.4 Ω |
| Max Current | 130 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-60G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 47 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 18 MHz |
| DCR | 4.5 Ω |
| Max Current | 110 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-60F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 47 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 18 MHz |
| DCR | 4.5 Ω |
| Max Current | 110 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-58K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 39 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 20 MHz |
| DCR | 3.6 Ω |
| Max Current | 125 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-58J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 39 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 20 MHz |
| DCR | 3.6 Ω |
| Max Current | 125 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-58H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 39 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 20 MHz |
| DCR | 3.6 Ω |
| Max Current | 125 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-54G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 27 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 20 MHz |
| DCR | 3.5 Ω |
| Max Current | 140 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-58F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 39 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 20 MHz |
| DCR | 3.6 Ω |
| Max Current | 125 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-54H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 27 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 20 MHz |
| DCR | 3.5 Ω |
| Max Current | 140 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-56J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 33 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 22 MHz |
| DCR | 3.4 Ω |
| Max Current | 130 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-56H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 33 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 22 MHz |
| DCR | 3.4 Ω |
| Max Current | 130 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-56G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 33 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 22 MHz |
| DCR | 3.4 Ω |
| Max Current | 130 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-56F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 33 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 22 MHz |
| DCR | 3.4 Ω |
| Max Current | 130 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-54K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 27 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 20 MHz |
| DCR | 3.5 Ω |
| Max Current | 140 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-60H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 47 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 18 MHz |
| DCR | 4.5 Ω |
| Max Current | 110 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-58G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 39 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 20 MHz |
| DCR | 3.6 Ω |
| Max Current | 125 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-92G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 1000 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 3.2 MHz |
| DCR | 75 Ω |
| Max Current | 27 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-86H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 560 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 5 MHz |
| DCR | 46 Ω |
| Max Current | 35 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-86J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 560 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 5 MHz |
| DCR | 46 Ω |
| Max Current | 35 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-86K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 560 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 5 MHz |
| DCR | 46 Ω |
| Max Current | 35 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-88F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 680 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 4.2 MHz |
| DCR | 60 Ω |
| Max Current | 30 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-88G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 680 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 4.2 MHz |
| DCR | 60 Ω |
| Max Current | 30 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-88H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 680 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 4.2 MHz |
| DCR | 60 Ω |
| Max Current | 30 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-88J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 680 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 4.2 MHz |
| DCR | 60 Ω |
| Max Current | 30 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-88K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 680 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 4.2 MHz |
| DCR | 60 Ω |
| Max Current | 30 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-90F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 820 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 3.8 MHz |
| DCR | 65 Ω |
| Max Current | 29 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-90G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 820 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 3.8 MHz |
| DCR | 65 Ω |
| Max Current | 29 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-90H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 820 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 3.8 MHz |
| DCR | 65 Ω |
| Max Current | 29 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-90J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 820 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 3.8 MHz |
| DCR | 65 Ω |
| Max Current | 29 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-80H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 330 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 7 MHz |
| DCR | 28 Ω |
| Max Current | 45 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-92F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 1000 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 3.2 MHz |
| DCR | 75 Ω |
| Max Current | 27 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-84K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 470 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 6 MHz |
| DCR | 42 Ω |
| Max Current | 36 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-92H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 1000 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 3.2 MHz |
| DCR | 75 Ω |
| Max Current | 27 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-92J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 1000 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 3.2 MHz |
| DCR | 75 Ω |
| Max Current | 27 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-92K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 1000 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 3.2 MHz |
| DCR | 75 Ω |
| Max Current | 27 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-94F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.1 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 640 MHz |
| DCR | 0.08 Ω |
| Max Current | 1380 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-94G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.1 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 640 MHz |
| DCR | 0.08 Ω |
| Max Current | 1380 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-94H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.1 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 640 MHz |
| DCR | 0.08 Ω |
| Max Current | 1380 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-94J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.1 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 640 MHz |
| DCR | 0.08 Ω |
| Max Current | 1380 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-94K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.1 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 640 MHz |
| DCR | 0.08 Ω |
| Max Current | 1380 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-96F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.12 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 600 MHz |
| DCR | 0.09 Ω |
| Max Current | 1300 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-96G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.12 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 600 MHz |
| DCR | 0.09 Ω |
| Max Current | 1300 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-96H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.12 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 600 MHz |
| DCR | 0.09 Ω |
| Max Current | 1300 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-96J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.12 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 600 MHz |
| DCR | 0.09 Ω |
| Max Current | 1300 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-96K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.12 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 600 MHz |
| DCR | 0.09 Ω |
| Max Current | 1300 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-90K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 820 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 3.8 MHz |
| DCR | 65 Ω |
| Max Current | 29 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-80G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 330 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 7 MHz |
| DCR | 28 Ω |
| Max Current | 45 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-72K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 150 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 11 MHz |
| DCR | 15 Ω |
| Max Current | 61 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-74F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 180 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 9.5 MHz |
| DCR | 17 Ω |
| Max Current | 57 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-74G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 180 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 9.5 MHz |
| DCR | 17 Ω |
| Max Current | 57 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-74H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 180 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 9.5 MHz |
| DCR | 17 Ω |
| Max Current | 57 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-74J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 180 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 9.5 MHz |
| DCR | 17 Ω |
| Max Current | 57 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-74K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 180 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 9.5 MHz |
| DCR | 17 Ω |
| Max Current | 57 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-76F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 220 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 9 MHz |
| DCR | 21 Ω |
| Max Current | 52 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-76G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 220 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 9 MHz |
| DCR | 21 Ω |
| Max Current | 52 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-76J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 220 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 9 MHz |
| DCR | 21 Ω |
| Max Current | 52 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-78F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 270 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 8 MHz |
| DCR | 25 Ω |
| Max Current | 47 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-78G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 270 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 8 MHz |
| DCR | 25 Ω |
| Max Current | 47 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-78H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 270 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 8 MHz |
| DCR | 25 Ω |
| Max Current | 47 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-78J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 270 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 8 MHz |
| DCR | 25 Ω |
| Max Current | 47 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-86G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 560 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 5 MHz |
| DCR | 46 Ω |
| Max Current | 35 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-82H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 390 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 6.5 MHz |
| DCR | 35 Ω |
| Max Current | 40 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-72J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 150 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 11 MHz |
| DCR | 15 Ω |
| Max Current | 61 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-84J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 470 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 6 MHz |
| DCR | 42 Ω |
| Max Current | 36 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-84H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 470 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 6 MHz |
| DCR | 42 Ω |
| Max Current | 36 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-84G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 470 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 6 MHz |
| DCR | 42 Ω |
| Max Current | 36 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-84F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 470 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 6 MHz |
| DCR | 42 Ω |
| Max Current | 36 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-78K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 270 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 8 MHz |
| DCR | 25 Ω |
| Max Current | 47 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-82J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 390 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 6.5 MHz |
| DCR | 35 Ω |
| Max Current | 40 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-80F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 330 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 7 MHz |
| DCR | 28 Ω |
| Max Current | 45 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-82G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 390 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 6.5 MHz |
| DCR | 35 Ω |
| Max Current | 40 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-82F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 390 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 6.5 MHz |
| DCR | 35 Ω |
| Max Current | 40 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-76H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 220 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 9 MHz |
| DCR | 21 Ω |
| Max Current | 52 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-80J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 330 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 7 MHz |
| DCR | 28 Ω |
| Max Current | 45 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-48H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 15 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 35 MHz |
| DCR | 2.8 Ω |
| Max Current | 157 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-86F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 560 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 5 MHz |
| DCR | 46 Ω |
| Max Current | 35 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-82K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 390 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 6.5 MHz |
| DCR | 35 Ω |
| Max Current | 40 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-18F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.82 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 250 MHz |
| DCR | 0.85 Ω |
| Max Current | 420 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-12G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.47 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 330 MHz |
| DCR | 0.35 Ω |
| Max Current | 660 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-12H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.47 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 330 MHz |
| DCR | 0.35 Ω |
| Max Current | 660 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-12J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.47 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 330 MHz |
| DCR | 0.35 Ω |
| Max Current | 660 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-12K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.47 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 330 MHz |
| DCR | 0.35 Ω |
| Max Current | 660 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-14F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.56 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 300 MHz |
| DCR | 0.5 Ω |
| Max Current | 550 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-14G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.56 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 300 MHz |
| DCR | 0.5 Ω |
| Max Current | 550 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-14H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.56 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 300 MHz |
| DCR | 0.5 Ω |
| Max Current | 550 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-14J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.56 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 300 MHz |
| DCR | 0.5 Ω |
| Max Current | 550 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-14K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.56 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 300 MHz |
| DCR | 0.5 Ω |
| Max Current | 550 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-16F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.68 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 275 MHz |
| DCR | 0.6 Ω |
| Max Current | 500 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-16G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.68 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 275 MHz |
| DCR | 0.6 Ω |
| Max Current | 500 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-16H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.68 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 275 MHz |
| DCR | 0.6 Ω |
| Max Current | 500 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-22K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 1.2 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 150 MHz |
| DCR | 0.18 Ω |
| Max Current | 620 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-16K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.68 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 275 MHz |
| DCR | 0.6 Ω |
| Max Current | 500 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-10J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.39 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 365 MHz |
| DCR | 0.3 Ω |
| Max Current | 710 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-18G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.82 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 250 MHz |
| DCR | 0.85 Ω |
| Max Current | 420 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-18H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.82 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 250 MHz |
| DCR | 0.85 Ω |
| Max Current | 420 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-18J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.82 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 250 MHz |
| DCR | 0.85 Ω |
| Max Current | 420 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-18K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.82 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 250 MHz |
| DCR | 0.85 Ω |
| Max Current | 420 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-20F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 1 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 230 MHz |
| DCR | 1 Ω |
| Max Current | 390 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-20G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 1 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 230 MHz |
| DCR | 1 Ω |
| Max Current | 390 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-20H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 1 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 230 MHz |
| DCR | 1 Ω |
| Max Current | 390 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-20J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 1 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 230 MHz |
| DCR | 1 Ω |
| Max Current | 390 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-20K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 1 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 230 MHz |
| DCR | 1 Ω |
| Max Current | 390 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-22F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 1.2 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 150 MHz |
| DCR | 0.18 Ω |
| Max Current | 620 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-22G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 1.2 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 150 MHz |
| DCR | 0.18 Ω |
| Max Current | 620 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-22H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 1.2 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 150 MHz |
| DCR | 0.18 Ω |
| Max Current | 620 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-22J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 1.2 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 150 MHz |
| DCR | 0.18 Ω |
| Max Current | 620 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-16J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.68 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 275 MHz |
| DCR | 0.6 Ω |
| Max Current | 500 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-04J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.22 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 470 MHz |
| DCR | 0.14 Ω |
| Max Current | 1040 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-00F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.15 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 570 MHz |
| DCR | 0.1 Ω |
| Max Current | 1230 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-76K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 220 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 9 MHz |
| DCR | 21 Ω |
| Max Current | 52 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.1 MHz |
| Q Test Freq | 0.1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-48G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 15 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 35 MHz |
| DCR | 2.8 Ω |
| Max Current | 157 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-00G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.15 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 570 MHz |
| DCR | 0.1 Ω |
| Max Current | 1230 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-00H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.15 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 570 MHz |
| DCR | 0.1 Ω |
| Max Current | 1230 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-00J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.15 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 570 MHz |
| DCR | 0.1 Ω |
| Max Current | 1230 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-00K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.15 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 570 MHz |
| DCR | 0.1 Ω |
| Max Current | 1230 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-02F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.18 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 500 MHz |
| DCR | 0.12 Ω |
| Max Current | 1120 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-02G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.18 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 500 MHz |
| DCR | 0.12 Ω |
| Max Current | 1120 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-02H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.18 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 500 MHz |
| DCR | 0.12 Ω |
| Max Current | 1120 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-02J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.18 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 500 MHz |
| DCR | 0.12 Ω |
| Max Current | 1120 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-02K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.18 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 500 MHz |
| DCR | 0.12 Ω |
| Max Current | 1120 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-04F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.22 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 470 MHz |
| DCR | 0.14 Ω |
| Max Current | 1040 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-12F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.47 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 330 MHz |
| DCR | 0.35 Ω |
| Max Current | 660 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-08G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.33 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 410 MHz |
| DCR | 0.22 Ω |
| Max Current | 830 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-06J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.27 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 430 MHz |
| DCR | 0.17 Ω |
| Max Current | 945 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-10H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.39 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 365 MHz |
| DCR | 0.3 Ω |
| Max Current | 710 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-10G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.39 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 365 MHz |
| DCR | 0.3 Ω |
| Max Current | 710 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-10F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.39 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 365 MHz |
| DCR | 0.3 Ω |
| Max Current | 710 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-08K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.33 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 410 MHz |
| DCR | 0.22 Ω |
| Max Current | 830 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-04G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.22 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 470 MHz |
| DCR | 0.14 Ω |
| Max Current | 1040 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-08H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.33 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 410 MHz |
| DCR | 0.22 Ω |
| Max Current | 830 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-04H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.22 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 470 MHz |
| DCR | 0.14 Ω |
| Max Current | 1040 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-08F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.33 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 410 MHz |
| DCR | 0.22 Ω |
| Max Current | 830 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-06K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.27 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 430 MHz |
| DCR | 0.17 Ω |
| Max Current | 945 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-06H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.27 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 430 MHz |
| DCR | 0.17 Ω |
| Max Current | 945 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-06F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.27 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 430 MHz |
| DCR | 0.17 Ω |
| Max Current | 945 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-04K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.22 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 470 MHz |
| DCR | 0.14 Ω |
| Max Current | 1040 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-10K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.39 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 365 MHz |
| DCR | 0.3 Ω |
| Max Current | 710 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-08J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.33 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 410 MHz |
| DCR | 0.22 Ω |
| Max Current | 830 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-38H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 5.6 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 65 MHz |
| DCR | 1.8 Ω |
| Max Current | 195 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-36F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 4.7 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 75 MHz |
| DCR | 1.2 Ω |
| Max Current | 239 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-40J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 6.8 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 60 MHz |
| DCR | 2 Ω |
| Max Current | 185 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-40H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 6.8 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 60 MHz |
| DCR | 2 Ω |
| Max Current | 185 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-40G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 6.8 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 60 MHz |
| DCR | 2 Ω |
| Max Current | 185 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-40F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 6.8 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 60 MHz |
| DCR | 2 Ω |
| Max Current | 185 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-42F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 8.2 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 55 MHz |
| DCR | 2.7 Ω |
| Max Current | 160 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-38J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 5.6 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 65 MHz |
| DCR | 1.8 Ω |
| Max Current | 195 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-42G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 8.2 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 55 MHz |
| DCR | 2.7 Ω |
| Max Current | 160 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-38G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 5.6 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 65 MHz |
| DCR | 1.8 Ω |
| Max Current | 195 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-38F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 5.6 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 65 MHz |
| DCR | 1.8 Ω |
| Max Current | 195 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-36K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 4.7 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 75 MHz |
| DCR | 1.2 Ω |
| Max Current | 239 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-36J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 4.7 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 75 MHz |
| DCR | 1.2 Ω |
| Max Current | 239 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-36H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 4.7 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 75 MHz |
| DCR | 1.2 Ω |
| Max Current | 239 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-36G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 4.7 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 75 MHz |
| DCR | 1.2 Ω |
| Max Current | 239 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-38K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 5.6 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 65 MHz |
| DCR | 1.8 Ω |
| Max Current | 195 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-46F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 12 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 37 MHz |
| DCR | 2.7 Ω |
| Max Current | 160 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-48F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 15 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 35 MHz |
| DCR | 2.8 Ω |
| Max Current | 157 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-46K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 12 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 37 MHz |
| DCR | 2.7 Ω |
| Max Current | 160 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-46J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 12 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 37 MHz |
| DCR | 2.7 Ω |
| Max Current | 160 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-06G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 0.27 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 430 MHz |
| DCR | 0.17 Ω |
| Max Current | 945 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 4 MHz |
| Q Test Freq | 4 MHz |
| Core | Phenolic |
| Sleeve | Not Applicable |

| Part 1027-24F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 1.5 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 140 MHz |
| DCR | 0.22 Ω |
| Max Current | 560 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-40K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 6.8 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 60 MHz |
| DCR | 2 Ω |
| Max Current | 185 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-46G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 12 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 37 MHz |
| DCR | 2.7 Ω |
| Max Current | 160 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-42J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 8.2 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 55 MHz |
| DCR | 2.7 Ω |
| Max Current | 160 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-44K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 10 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 40 MHz |
| DCR | 3.4 Ω |
| Max Current | 142 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-44J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 10 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 40 MHz |
| DCR | 3.4 Ω |
| Max Current | 142 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-44H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 10 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 40 MHz |
| DCR | 3.4 Ω |
| Max Current | 142 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-44G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 10 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 40 MHz |
| DCR | 3.4 Ω |
| Max Current | 142 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-42K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 8.2 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 55 MHz |
| DCR | 2.7 Ω |
| Max Current | 160 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-42H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 8.2 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 55 MHz |
| DCR | 2.7 Ω |
| Max Current | 160 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-46H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 12 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 37 MHz |
| DCR | 2.7 Ω |
| Max Current | 160 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 0.4 MHz |
| Q Test Freq | 0.4 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-26F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 1.8 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 125 MHz |
| DCR | 0.3 Ω |
| Max Current | 480 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-26K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 1.8 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 125 MHz |
| DCR | 0.3 Ω |
| Max Current | 480 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-28J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 2.2 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 115 MHz |
| DCR | 0.41 Ω |
| Max Current | 410 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-34K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 3.9 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 80 MHz |
| DCR | 1 Ω |
| Max Current | 263 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-28G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 2.2 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 115 MHz |
| DCR | 0.41 Ω |
| Max Current | 410 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-28F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 2.2 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 115 MHz |
| DCR | 0.41 Ω |
| Max Current | 410 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-30F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 2.7 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 100 MHz |
| DCR | 0.56 Ω |
| Max Current | 350 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-24J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 1.5 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 140 MHz |
| DCR | 0.22 Ω |
| Max Current | 560 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-28K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 2.2 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 115 MHz |
| DCR | 0.41 Ω |
| Max Current | 410 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-26J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 1.8 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 125 MHz |
| DCR | 0.3 Ω |
| Max Current | 480 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-26H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 1.8 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 125 MHz |
| DCR | 0.3 Ω |
| Max Current | 480 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-26G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 1.8 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 125 MHz |
| DCR | 0.3 Ω |
| Max Current | 480 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-24G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 1.5 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 140 MHz |
| DCR | 0.22 Ω |
| Max Current | 560 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-24H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 1.5 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 140 MHz |
| DCR | 0.22 Ω |
| Max Current | 560 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-44F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 10 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 40 MHz |
| DCR | 3.4 Ω |
| Max Current | 142 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-24K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 1.5 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 140 MHz |
| DCR | 0.22 Ω |
| Max Current | 560 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-32G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 3.3 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 90 MHz |
| DCR | 0.85 Ω |
| Max Current | 285 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-34J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 3.9 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 80 MHz |
| DCR | 1 Ω |
| Max Current | 263 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-34H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 3.9 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 80 MHz |
| DCR | 1 Ω |
| Max Current | 263 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-34G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 3.9 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 80 MHz |
| DCR | 1 Ω |
| Max Current | 263 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-34F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 3.9 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 80 MHz |
| DCR | 1 Ω |
| Max Current | 263 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-32K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 3.3 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 90 MHz |
| DCR | 0.85 Ω |
| Max Current | 285 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-28H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 2.2 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 115 MHz |
| DCR | 0.41 Ω |
| Max Current | 410 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-32H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 3.3 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 90 MHz |
| DCR | 0.85 Ω |
| Max Current | 285 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-30G | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 2.7 µH |
| Tolerance | ± 2 |
| Q | |
| SRF | 100 MHz |
| DCR | 0.56 Ω |
| Max Current | 350 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-32F | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 3.3 µH |
| Tolerance | ± 1 |
| Q | |
| SRF | 90 MHz |
| DCR | 0.85 Ω |
| Max Current | 285 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-30K | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 2.7 µH |
| Tolerance | ± 10 |
| Q | |
| SRF | 100 MHz |
| DCR | 0.56 Ω |
| Max Current | 350 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-30J | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 2.7 µH |
| Tolerance | ± 5 |
| Q | |
| SRF | 100 MHz |
| DCR | 0.56 Ω |
| Max Current | 350 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

| Part 1027-30H | Check Stock |
|---|---|
| Series | 1027 |
| Type | RF Inductors |
| Description | Molded Unshielded RF Coil |
| Mounting | Through Hole |
| Shielded | No |
| QPL | No |
| COTS | No |
| ROHS | No |
| MIL No. | Not Applicable |
| Length | 0.25 inches |
| Width | 0.095 inches |
| Height | inches |
| Lead Length | 1.5 inches |
| Weight | 0.3 grams |
| Inductance | 2.7 µH |
| Tolerance | ± 3 |
| Q | |
| SRF | 100 MHz |
| DCR | 0.56 Ω |
| Max Current | 350 mA |
| Inc Current | |
| Inc Current % | |
| Ind Test Freq | 1 MHz |
| Q Test Freq | 1 MHz |
| Core | Iron |
| Sleeve | Not Applicable |

Parts

1027-00F Molded Unshielded RF Coil
1027-00G Molded Unshielded RF Coil
1027-00H Molded Unshielded RF Coil
1027-00J Molded Unshielded RF Coil
1027-00K Molded Unshielded RF Coil
1027-02F Molded Unshielded RF Coil
1027-02G Molded Unshielded RF Coil
1027-02H Molded Unshielded RF Coil
1027-02J Molded Unshielded RF Coil
1027-02K Molded Unshielded RF Coil
1027-04F Molded Unshielded RF Coil
1027-04G Molded Unshielded RF Coil

1027-04H Molded Unshielded RF Coil
1027-04J Molded Unshielded RF Coil
1027-04K Molded Unshielded RF Coil
1027-06F Molded Unshielded RF Coil
1027-06G Molded Unshielded RF Coil
1027-06H Molded Unshielded RF Coil
1027-06J Molded Unshielded RF Coil
1027-06K Molded Unshielded RF Coil
1027-08F Molded Unshielded RF Coil
1027-08G Molded Unshielded RF Coil
1027-08H Molded Unshielded RF Coil
1027-08J Molded Unshielded RF Coil
1027-08K Molded Unshielded RF Coil
1027-10F Molded Unshielded RF Coil
1027-10G Molded Unshielded RF Coil
1027-10H Molded Unshielded RF Coil
1027-10J Molded Unshielded RF Coil
1027-10K Molded Unshielded RF Coil
1027-12F Molded Unshielded RF Coil
1027-12G Molded Unshielded RF Coil
1027-12H Molded Unshielded RF Coil
1027-12J Molded Unshielded RF Coil
1027-12K Molded Unshielded RF Coil
1027-14F Molded Unshielded RF Coil
1027-14G Molded Unshielded RF Coil
1027-14H Molded Unshielded RF Coil
1027-14J Molded Unshielded RF Coil
1027-14K Molded Unshielded RF Coil
1027-16F Molded Unshielded RF Coil
1027-16G Molded Unshielded RF Coil
1027-16H Molded Unshielded RF Coil
1027-16J Molded Unshielded RF Coil
1027-16K Molded Unshielded RF Coil
1027-18F Molded Unshielded RF Coil
1027-18G Molded Unshielded RF Coil
1027-18H Molded Unshielded RF Coil
1027-18J Molded Unshielded RF Coil
1027-18K Molded Unshielded RF Coil
1027-20F Molded Unshielded RF Coil
1027-20G Molded Unshielded RF Coil
1027-20H Molded Unshielded RF Coil
1027-20J Molded Unshielded RF Coil
1027-20K Molded Unshielded RF Coil
1027-22F Molded Unshielded RF Coil
1027-22G Molded Unshielded RF Coil
1027-22H Molded Unshielded RF Coil
1027-22J Molded Unshielded RF Coil
1027-22K Molded Unshielded RF Coil
1027-24F Molded Unshielded RF Coil
1027-24G Molded Unshielded RF Coil

1027-24H Molded Unshielded RF Coil
1027-24J Molded Unshielded RF Coil
1027-24K Molded Unshielded RF Coil
1027-26F Molded Unshielded RF Coil
1027-26G Molded Unshielded RF Coil
1027-26H Molded Unshielded RF Coil
1027-26J Molded Unshielded RF Coil
1027-26K Molded Unshielded RF Coil
1027-28F Molded Unshielded RF Coil
1027-28G Molded Unshielded RF Coil
1027-28H Molded Unshielded RF Coil
1027-28J Molded Unshielded RF Coil
1027-28K Molded Unshielded RF Coil
1027-30F Molded Unshielded RF Coil
1027-30G Molded Unshielded RF Coil
1027-30H Molded Unshielded RF Coil
1027-30J Molded Unshielded RF Coil
1027-30K Molded Unshielded RF Coil
1027-32F Molded Unshielded RF Coil
1027-32G Molded Unshielded RF Coil
1027-32H Molded Unshielded RF Coil
1027-32J Molded Unshielded RF Coil
1027-32K Molded Unshielded RF Coil
1027-34F Molded Unshielded RF Coil
1027-34G Molded Unshielded RF Coil
1027-34H Molded Unshielded RF Coil
1027-34J Molded Unshielded RF Coil
1027-34K Molded Unshielded RF Coil
1027-36F Molded Unshielded RF Coil
1027-36G Molded Unshielded RF Coil
1027-36H Molded Unshielded RF Coil
1027-36J Molded Unshielded RF Coil
1027-36K Molded Unshielded RF Coil
1027-38F Molded Unshielded RF Coil
1027-38G Molded Unshielded RF Coil
1027-38H Molded Unshielded RF Coil
1027-38J Molded Unshielded RF Coil
1027-38K Molded Unshielded RF Coil
1027-40F Molded Unshielded RF Coil
1027-40G Molded Unshielded RF Coil
1027-40H Molded Unshielded RF Coil
1027-40J Molded Unshielded RF Coil
1027-40K Molded Unshielded RF Coil
1027-42F Molded Unshielded RF Coil
1027-42G Molded Unshielded RF Coil
1027-42H Molded Unshielded RF Coil
1027-42J Molded Unshielded RF Coil
1027-42K Molded Unshielded RF Coil
1027-44F Molded Unshielded RF Coil
1027-44G Molded Unshielded RF Coil

1027-44H Molded Unshielded RF Coil
1027-44J Molded Unshielded RF Coil
1027-44K Molded Unshielded RF Coil
1027-46F Molded Unshielded RF Coil
1027-46G Molded Unshielded RF Coil
1027-46H Molded Unshielded RF Coil
1027-46J Molded Unshielded RF Coil
1027-46K Molded Unshielded RF Coil
1027-48F Molded Unshielded RF Coil
1027-48G Molded Unshielded RF Coil
1027-48H Molded Unshielded RF Coil
1027-48J Molded Unshielded RF Coil
1027-48K Molded Unshielded RF Coil
1027-50F Molded Unshielded RF Coil
1027-50G Molded Unshielded RF Coil
1027-50H Molded Unshielded RF Coil
1027-50J Molded Unshielded RF Coil
1027-50K Molded Unshielded RF Coil
1027-52F Molded Unshielded RF Coil
1027-52G Molded Unshielded RF Coil
1027-52H Molded Unshielded RF Coil
1027-52J Molded Unshielded RF Coil
1027-52K Molded Unshielded RF Coil
1027-54F Molded Unshielded RF Coil
1027-54G Molded Unshielded RF Coil
1027-54H Molded Unshielded RF Coil
1027-54J Molded Unshielded RF Coil
1027-54K Molded Unshielded RF Coil
1027-56F Molded Unshielded RF Coil
1027-56G Molded Unshielded RF Coil
1027-56H Molded Unshielded RF Coil
1027-56J Molded Unshielded RF Coil
1027-56K Molded Unshielded RF Coil
1027-58F Molded Unshielded RF Coil
1027-58G Molded Unshielded RF Coil
1027-58H Molded Unshielded RF Coil
1027-58J Molded Unshielded RF Coil
1027-58K Molded Unshielded RF Coil
1027-60F Molded Unshielded RF Coil
1027-60G Molded Unshielded RF Coil
1027-60H Molded Unshielded RF Coil
1027-60J Molded Unshielded RF Coil
1027-60K Molded Unshielded RF Coil
1027-62F Molded Unshielded RF Coil
1027-62G Molded Unshielded RF Coil
1027-62H Molded Unshielded RF Coil
1027-62J Molded Unshielded RF Coil
1027-62K Molded Unshielded RF Coil
1027-64F Molded Unshielded RF Coil
1027-64G Molded Unshielded RF Coil

1027-64H Molded Unshielded RF Coil
1027-64J Molded Unshielded RF Coil
1027-64K Molded Unshielded RF Coil
1027-66F Molded Unshielded RF Coil
1027-66G Molded Unshielded RF Coil
1027-66H Molded Unshielded RF Coil
1027-66J Molded Unshielded RF Coil
1027-66K Molded Unshielded RF Coil
1027-68F Molded Unshielded RF Coil
1027-68G Molded Unshielded RF Coil
1027-68H Molded Unshielded RF Coil
1027-68J Molded Unshielded RF Coil
1027-68K Molded Unshielded RF Coil
1027-70F Molded Unshielded RF Coil
1027-70G Molded Unshielded RF Coil
1027-70H Molded Unshielded RF Coil
1027-70J Molded Unshielded RF Coil
1027-70K Molded Unshielded RF Coil
1027-72F Molded Unshielded RF Coil
1027-72G Molded Unshielded RF Coil
1027-72H Molded Unshielded RF Coil
1027-72J Molded Unshielded RF Coil
1027-72K Molded Unshielded RF Coil
1027-74F Molded Unshielded RF Coil
1027-74G Molded Unshielded RF Coil
1027-74H Molded Unshielded RF Coil
1027-74J Molded Unshielded RF Coil
1027-74K Molded Unshielded RF Coil
1027-76F Molded Unshielded RF Coil
1027-76G Molded Unshielded RF Coil
1027-76H Molded Unshielded RF Coil
1027-76J Molded Unshielded RF Coil
1027-76K Molded Unshielded RF Coil
1027-78F Molded Unshielded RF Coil
1027-78G Molded Unshielded RF Coil
1027-78H Molded Unshielded RF Coil
1027-78J Molded Unshielded RF Coil
1027-78K Molded Unshielded RF Coil
1027-80F Molded Unshielded RF Coil
1027-80G Molded Unshielded RF Coil
1027-80H Molded Unshielded RF Coil
1027-80J Molded Unshielded RF Coil
1027-80K Molded Unshielded RF Coil
1027-82F Molded Unshielded RF Coil
1027-82G Molded Unshielded RF Coil
1027-82H Molded Unshielded RF Coil
1027-82J Molded Unshielded RF Coil
1027-82K Molded Unshielded RF Coil
1027-84F Molded Unshielded RF Coil
1027-84G Molded Unshielded RF Coil

1027-84H Molded Unshielded RF Coil
1027-84J Molded Unshielded RF Coil
1027-84K Molded Unshielded RF Coil
1027-86F Molded Unshielded RF Coil
1027-86G Molded Unshielded RF Coil
1027-86H Molded Unshielded RF Coil
1027-86J Molded Unshielded RF Coil
1027-86K Molded Unshielded RF Coil
1027-88F Molded Unshielded RF Coil
1027-88G Molded Unshielded RF Coil
1027-88H Molded Unshielded RF Coil
1027-88J Molded Unshielded RF Coil
1027-88K Molded Unshielded RF Coil
1027-90F Molded Unshielded RF Coil
1027-90G Molded Unshielded RF Coil
1027-90H Molded Unshielded RF Coil
1027-90J Molded Unshielded RF Coil
1027-90K Molded Unshielded RF Coil
1027-92F Molded Unshielded RF Coil
1027-92G Molded Unshielded RF Coil
1027-92H Molded Unshielded RF Coil
1027-92J Molded Unshielded RF Coil
1027-92K Molded Unshielded RF Coil
1027-94F Molded Unshielded RF Coil
1027-94G Molded Unshielded RF Coil
1027-94H Molded Unshielded RF Coil
1027-94J Molded Unshielded RF Coil
1027-94K Molded Unshielded RF Coil
1027-96F Molded Unshielded RF Coil
1027-96G Molded Unshielded RF Coil
1027-96H Molded Unshielded RF Coil
1027-96J Molded Unshielded RF Coil
1027-96K Molded Unshielded RF Coil