


GENERAL PURPOSE SNAP ACTION



Retail Part No.	Bulk Part No.	Fig. No.	Amps **VAC	Amps 125 VDC	Amps 250 VDC	HP 125 VAC	HP 250 VAC	PT Max. (In)	OT Min. (In)	DT Max. (In)	OF Max. Oz. (grams)	Actuator	Actuator Length (In)	Terminal Type	Spec Drawing Page No.
35-461	35-461-BU	1	15			3/4	1-1/2	0.050	0.050		20 (567)	PI		QC .250"	297-A
35-462	35-462-BU	2	15			3/4	1-1/2	0.050	0.187		20 (567)	PI w/OT		QC .250"	297-B
35-463	35-463-BU	3	15			3/4	1-1/2	0.281	0.062	0.094	20 (567)	Ro	1.50	QC .250"	297-C
35-464	35-464-BU	4	15			3/4	1-1/2	0.312	0.187	0.062	20 (567)	Lever	2.50	QC .250"	297-D
35-830	35-830-BU	5	15			3/4	1-1/2	0.050	0.050	0.010	20 (567)	Red Pb		QC .250"	297-E
35-831	35-831-BU	5	15			3/4	1-1/2	0.050	0.050	0.010	20 (567)	Black Pb		QC .250"	297-E
35-990	35-990-BU	*6	15			3/4	1-1/2	0.050	0.050	0.010	30 (850)	PI		QC .250"	297-F
35-992	35-992-BU	*7	15			3/4	1-1/2	0.312	0.187	0.062	30 (850)	Lever	2.50	QC .250"	297-F
35-3900	35-3900-BU	8	15					0.016	0.005	0.002	12.3 (350)	PP		Sc	297-G
35-3901	35-3901-BU	8	15	1/2	1/4			0.016	0.005	0.002	12.3 (350)	PP		Sc	297-G
35-3907	35-3907-BU	9	15					0.158	0.063	0.002	5.3 (151)	LRO	1.783	Sc	297-O
35-3910	35-3910-BU	10	20	1/2	1/4	1	2	0.028	0.140	0.008	22.9 (650)	RP		Sc	297-I
35-3911	35-3911-BU	10	15					0.016	0.140	0.002	12.3 (349)	RP		Sc	297-I
35-828	35-828-BU	11	20	1/2	1/4	1	2	0.156	0.062	0.050	5-13 (142-370)	LL	1.95	Sc	297-H
35-829	35-829-BU	11	15	1/2	1/4	1	2	0.156	0.062	0.050	5-13 (142-370)	LL	1.97	Sd	297-H
35-890	35-890-BU	12	20	1/2	1/4			0.380	0.190	0.156	3.5-26 (100-740)	Lever	2.50	Sc	297-J
35-892	35-892-BU	13	20	1/2	1/4	1	2	0.020	0.055	0.002	12.3 (350)	SP		Sd/Sc	297-K&L
35-894	35-894-BU	14	20	1/2	1/4	1	2	0.020	0.005	0.002	12.3 (350)	PP		Sd/Sc	297-L
35-896	35-896-BU	15	20+	1/2	1/4			0.020	0.220		13 (370)	PI w/OT		Sd/Sc	297-M
35-980	35-980-BU	14	20	1/2	1/4			0.030	0.005	0.005	26 (740)	PP		Sd/Sc	297-L
35-982	35-982-BU	15	20+	1/2	1/4			0.030	0.220		26 (740)	PI w/OT		Sd/Sc	297-M
35-984	35-984-BU	12	20	1/2	1/4			0.380	0.190	0.047	2.5-9 (60-255)	Lever	2.50	Sd/Sc	297-J
35-987	35-987-BU	16	15					0.280	0.157	0.327	3.5 (100)	Ro	1.05	Sc	297-N
35-3903	35-3903-BU	13	20	1/2	1/4	3/4	1 1/2	0.020	0.055	0.002	12.3 (350)	SP		Sc	297-K
35-3904	35-3904-BU	17	20	1/2	1/4	1/2	1	0.158	0.062	0.050	5.3 (150)	LL	1.95	Sc	297-H

Notes: All of the above have momentary action
All have SPDT, but 35-990 & 35-992

*DPDT
**125/250VAC
†480VAC

DT=Differential Travel
HP=Horse Power
HRO=Hinged Roller
LRO=Leaf Rollers
LL=Leaf Lever

OF=Operating Force
OT=Over Travel
Pb=Pushbuttons
PI=Plunger

PT=Pre-Travel
QC=Quick Connect
RP=Roller Plunger
Sc=Screw

Sd=Solder
ShRo=Short Roller
SP=Stub Plunger
PP=Pin Plunger
Ro=Roller

Note: All figures are for illustration purpose only, and the number/type of terminals may vary.

GCETM ELECTRONICS

Technical drawing of a mechanical part (A) showing dimensions and a datum. The drawing includes a central rectangular feature with a width dimension of $\pm .50$ (12, 7) and a vertical dimension of $\pm .265 \pm .030$ (7, 24 $\pm .76$) labeled as OPER. POS. Datum features are indicated by circles with crosses.

