

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A2	REVISED PER ECO-11-004917	11MAR11	RK	HMR

MATERIAL:
HOUSING: NYLON, UL94V-0, BLACK.
TERMINALS: BRASS, BRIGHT TIN PLATED.
SCREWS: 6-32, STEEL, ZINC CHROMATE FINISH.


ELECTRICAL:
MAXIMUM CURRENT: 20A
OPERATING VOLTAGE: 600V
WIRE RANGE: 12-22 AWG

ENVIRONMENT:
OPERATING TEMP.: -60°C TO +105°C

- 1 MARKED WITH WHITE INK APPROX AS SHOWN.
- 2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



11.937	27	SSB7FP270102	2-1546973-7
11.500	26	SSB7FP260102	2-1546973-6
11.062	25	SSB7FP250102	2-1546973-5
10.625	24	SSB7FP240102	2-1546973-4
10.187	23	SSB7FP230102	2-1546973-3
9.750	22	SSB7FP220102	2-1546973-2
9.312	21	SSB7FP210102	2-1546973-1
8.875	20	SSB7FP200102	2-1546973-0
8.437	19	SSB7FP190102	1-1546973-9
8.000	18	SSB7FP180102	1-1546973-8
7.562	17	SSB7FP170102	1-1546973-7
7.125	16	SSB7FP160102	1-1546973-6
6.687	15	SSB7FP150102	1-1546973-5
6.250	14	SSB7FP140102	4-1437416-4
5.812	13	SSB7FP130102	1-1546973-3
5.375	12	SSB7FP120102	1-1546973-2
4.937	11	SSB7FP110102	1-1546973-1
4.500	10	SSB7FP100102	1-1546973-0
4.062	9	SSB7FP090102	1546973-9
3.625	8	SSB7FP080102	1546973-8
3.187	7	SSB7FP070102	1546973-7
2.750	6	SSB7FP060102	1546973-6
2.312	5	SSB7FP050102	1546973-5
1.875	4	SSB7FP04010211	9-796602-1
1.875	4	SSB7FP040102	9-796602-0
1.437	3	SSB7FP030102	1546973-3
1.000	2	SSB7FP020102	1546973-2
DIM A	NO. OF POS.	CATALOG NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLGEL 3/3/04	 TE Connectivity				
		CHK S YODER 3/3/04					
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD S YODER 3/3/04	NAME SSB7FPXX0102 — —				
	0 PLC ± — 1 PLC ± — 2 PLC ± .02 3 PLC ± .010 4 PLC ± — ANGLES ± 1°	PRODUCT SPEC —					
		APPLICATION SPEC —					
MATERIAL —	FINISH —	WEIGHT —	SIZE A3	CAGE CODE 00779	DRAWING NO C-9-796602-0	RESTRICTED TO —	
CUSTOMER DRAWING			SCALE NTS	SHEET 1 OF 1	REV A2		