






FCIconnect.com


Copyright FCI

PRODUCT NUMBER
SEE TABLE




VIEW E-E
SCALE 4/1

VIEW F-F
SCALE 4/1



SECTION X-X



DETAIL J
SCALE 3/1

mat'l. code —				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection ISO 1101	product family RIBCAGE			
ltr	ecn no	dr	date	tolerances unless otherwise specified		INCH/MM scale 4:1	title			
D	V10994	DWL	3/9/01	angles	linear		.050/1.27cc V.C.C S/M W/.044/1.12 SHORT PEG			
E	v11674	CRG	6/14/01							
F	M05-0123	MHT	6/09/05	0°±2'						
G	M06-0225	ERE	6/12/06	dr	M. CLOUSER	6/11/97	FCI			
H	M06-0370	MHT	9/25/08	engr	D. WHITING	6/11/97				
J	M09-0058	CMR	4/06/09	chr	C. GINGRICH	6/11/97				
K	ELX-N-010003	YO	1/30/12	appd	D. WHITING	6/11/97				
sheet	revision	K	K				dwg no			
index	sheet	1	2				73542			
							type Product Customer Drawing			
							sheet 1 of 2 size A3			

PRODUCT NUMBER NOTE 6	SIZE	DIM A	DIM B	DIM C	DIM D
73542-605	2 X 5	.266/6.76	.200/5.08	.370/9.40	.3200/8.128
↑ -610	2 X 10	.516/13.11	.450/11.43	.620/15.75	.5700/14.478
↑ -615	2 X 15	.766/19.46	.700/17.78	.870/22.10	.8200/20.828
↑ -620	2 X 20	1.016/25.81	.950/24.13	1.120/28.45	1.0700/27.178
↑ -625	2 X 25	1.266/32.16	1.200/30.48	1.370/34.80	1.3200/33.528
↑ -630	2 X 30	1.516/38.51	1.450/36.83	1.620/41.15	1.5700/39.878
↑ -635	2 X 35	1.766/44.86	1.700/43.18	1.870/47.50	1.8200/46.228
↑ -640	2 X 40	2.016/51.21	1.950/49.53	2.120/53.85	2.0700/52.578
↑ -645	2 X 45	2.266/57.56	2.200/55.88	2.370/60.20	2.3200/58.928
↓ 73542-650	2 X 50	2.516/63.91	2.450/62.23	2.620/66.55	2.5700/65.278




FIGURE A
RECOMMENDED
P.C.B. LAYOUT

- NOTES:

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI:](#)

[73542-610](#) [73542-620](#) [73542-625](#) [73542-630](#) [73542-635](#) [73542-650](#) [73542-645](#) [73542-645LF](#) [73542-605LF](#)
[73542-610LF](#) [73542-620LF](#) [73542-625LF](#) [73542-630LF](#) [73542-635LF](#) [73542-650LF](#) [73542-640LF](#)