


LOC	DIST	REVISIONS				
FT	0	P	LTR	DESCRIPTION	DATE	APVD
			H2	REVISED PER ECO-11-004917	11MAR11	RK HMR

- 1 MATERIAL: BODY — COPPER ALLOY
BAND — BeCu
- 2 FINISH: BODY AND BAND — .0002 IN. SILVER
OVER .00004 IN. NICKEL.
3. WIRE BARREL WILL ACCEPT 12–14 AWG WIRE.
4. MATES WITH AMP PART NUMBER 193841–1.
- 5 FINISH: BODY — 30 uIN GOLD MIN. OVER 50 uIN
NICKEL MIN. BAND— GOLD
- 6 FINISH: BODY AND BAND —
AT MINIMUM, HARD GOLD FLASH OVER 40 uINCHES
80–20 Pd/Ni OVER 100 uINCHES NICKEL.
7. ALL DIMENSIONS ARE REFERENCE.



OBSOLETE	6	193842–3
	5	193842–2
	2	193842–1
	FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. M. SVOBODA	03–18–94	TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK	—			
		APVD	—	NAME SOCKET ASSY, 2mm, 12–14 AWG HIGHCURRENT MATE–N–LOK II		
		PRODUCT SPEC	—			
MATERIAL 1		APPLICATION SPEC	—	SIZE	CAGE CODE	DRAWING NO
		FINISH	—	A3	00779	C=193842
		WEIGHT	—	RESTRICTED TO		
		CUSTOMER DRAWING			SCALE	SHEET
					—	1 OF 1
						REV H2