


Star Magnetics™

Fast Ethernet (10/100) & Gigabit (10/100/1000)



- Manufacturing design complies with IEEE 802.3 standard
- Designed for reflow soldering process up to 235°C IR reflow
- Compact footprint

Electrical Specifications @ 25°C — Operating Temperature 0°C to 70°C

Part Number Data Rate (Mbps)		Turns Ratio		Number of Ports	Insertion Loss (dB MAX)				Return Loss (Z out = 100 Ω ±15%)				Crosstalk (adjacent channels, dB MIN)			Hipot (V _{RMS} MIN)
10/100	10/100/1000	TX	RX		0.1 MHz	1 MHz	100 MHz	125 MHz	30 MHz	60 MHz	80 MHz	100 MHz	30 MHz	60 MHz	100 MHz	
H0055 ¹	—	1:1	1:1	1	-2.5	—	-1.0	—	-16	-10	-10	—	-45	-40	-33	1500
H0056 ²	—	1:1	1:1	1	—	-0.8	-0.9	—	-16	-10	-10	—	-45	-40	-33	1500
H1259	—	1:1	1:1	4	-1.2	—	-1.4	—	-16	-10	-10	—	-45	-40	-33	1500
H1260	—	1:1	1:1	1	-1.1	—	-1.1	—	-16	-10	-10	—	-35	-30	-30	1500
H1265	—	1:1	1:1	1	-1.3	—	-1.0	—	-16	-10	-10	—	-40	-38	-33	1500
H1266	—	1:1	1:1	4	-1.2	—	-1.0	—	-16	-10	-10	—	-45	-40	-30	1500
H1278	—	1:1	1:1	1	-1.1	—	-1.0	—	-16	-10	-10	—	-45	-40	-33	1500
—	H5062	1:1	1:1	1	-1.1	—	-1.0	-2.0	-18	-12	-12	-10	-43	-37	-33	1500


1. H0055 is designed to meet 200 μH nom.

2. H0056 is designed to meet 300 μH nom.

NOTE: "—" = not tested at that frequency.

Mechanicals

H0055



Weight355 grams
Tape & Reel . . .1000/reel
Tube40/tube


Dimensions: $\frac{\text{Inches}}{\text{mm}}$ Unless otherwise specified, all tolerances are $\pm \frac{.010}{0,25}$

Star Magnetics™ Fast Ethernet (10/100) & Gigabit (10/100/1000)



Mechanicals (continued)

H0056




Weight3 grams
Tape & Reel . . .2000/reel
Tube40/tube

Dimensions: $\frac{\text{Inches}}{\text{mm}}$


Unless otherwise specified, all tolerances are $\pm \frac{.010}{0,25}$

H1259, H1266



Weight4.8 grams
Tape & Reel . . .250/reel
Tube15/tube

H1260




Weight2.8 grams
Tube45/tube
Tape & Reel . . .600/reel

Dimensions: $\frac{\text{Inches}}{\text{mm}}$


Unless otherwise specified, all tolerances are $\pm \frac{.010}{0,25}$

H1265



Weight3.0 grams
Tube20/tube
Tape & Reel . . .300/reel

H1278




Weight1.7 grams
Tape & Reel . . .350/reel
Tube30/tube

Dimensions: $\frac{\text{Inches}}{\text{mm}}$

Unless otherwise specified, all tolerances are $\pm \frac{.010}{0,25}$

H5062



Weight2.7 grams
Tape & Reel . . .300/reel
Tube25/tube


Star Magnetics™

Fast Ethernet (10/100) & Gigabit (10/100/1000)




Schematics


H0055




H0056




H1259



H1260



H1265



H1265: 3-core design (T3 same toroid core)



Star Magnetics™

Fast Ethernet (10/100) & Gigabit (10/100/1000)




Schematics (continued)



H1266



H1278



H5062



For More Information :

UNITED STATES (Worldwide)

12220 World Trade Drive
San Diego, CA 92128
U.S.A.
<http://www.pulseeng.com>
TEL: 858 674 8100
FAX: 858 674 8262

UNITED KINGDOM (Northern Europe)

1 & 2 Huxley Road
The Surrey Research Park
Guildford, Surrey GU2 5RE
United Kingdom
TEL: 44 1483 401700
FAX: 44 1483 401701

FRANCE (Southern Europe)

Zone Industrielle
F-39270
Orgelet
France
TEL: 33 3 84 35 04 04
FAX: 33 3 84 25 46 41

SINGAPORE (Southern Asia)

150 Kampong Ampat
#07-01/02
KA Centre
Singapore 368324
TEL: 65 6287 8998
FAX: 65 6280 0080

TAIWAN, R.O.C. (Northern Asia)

3F-4, No. 81, Sec. 1
HsinTai Wu Road
Hsi-Chih, Taipei Hsien
Taiwan, R.O.C.
Tel: 886 2 2698 0228
FAX: 886 2 2698 0948

HONG KONG (China/Hong Kong)

9/F, Phase 2, Tai Sang
Shatin Warehouse Centre
6 Wong Chuk Yeung Street
Fotan Shatin, Hong Kong
TEL: 852 2788 6588
FAX: 852 2776 1055

DISTRIBUTOR

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners.

♻️ Printed on recycled paper. ©Copyright, 2003, Pulse Engineering, Inc. All rights reserved.