



ESQ-110-44-T-D



ESW-115-12-G-S

ESQ-132-14-G-D

**ESW, ESQ SERIES**

ELEVATED SOCKET

TSW, MTSW, EW,
MTLW, TSS, ZSS, TSM,
DW, ZW, HW, TSSH, HTSS

For complete specifications
see www.samtec.com?ESW or
www.samtec.com?ESQ

Lead-Free Solderable:
Wave only

For complete scope
of recognitions see
www.samtec.com/quality



TIGER
BUY
CONTACT

- Other platings


Note:
Some lengths, styles and options are non-standard, non-returnable.

TYPE STRIP	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	OTHER OPTION
ESW = Solder Tail	01 thru 36			-L = 10 μ" (0.25 μm) Gold contact, Matte Tin on tail	-S = Single Row	-LL = Locking Lead
ESQ = Square Tail				-G = 20 μ" (0.51 μm) Gold contact, Gold Flash on Balance	-D = Double Row	 Two leads per strip crimped. N/A with single row 1 or 2 positions.
				-T = Matte Tin (N/A w/LIF contact)	-T = Triple Row (ESQ only)	

→ (2.54) .100 X No. of Positions + (0.51) .020 ←

Specify LEAD STYLE
from chart below.

STANDARD INSERTION FORCE	LOW INSERTION FORCE	A	B
– 12	– 37	(2.29) .090	(11.05) .435
– 13	– 38	(7.36) .290	
– 23	– 48	(4.83) .190	(13.59) .535
– 33	– 58	(2.29) .090	(16.13) .635
– 14	– 39	(12.19) .480	(11.05) .435
– 24	– 49	(9.65) .380	(13.59) .535
– 34	– 59	(7.11) .280	(16.13) .635
– 44	– 69	(4.57) .180	(18.67) .735



APPLICATIONS




Self Nesting Sockets

(ESQ Series)

PC/104™ J1/P1 “Stackthrough” Connectors	
Standard Insertion Force	ESQ-132-14-G-D
Low Insertion Force	ESQ-132-39-G-D
PC/104™ J1 “Non-Stackthrough” Connectors	
Standard Insertion Force	ESQ-132-12-G-D
Low Insertion Force	ESQ-132-37-G-D
PC/104™ J2/P2 “Stackthrough” Connectors	
Standard Insertion Force	ESQ-120-14-G-D
Low Insertion Force	ESQ-120-39-G-D

PC/104 is a trademark of the PC/104 Consortium.



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.

Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.