




REV.	DATE	DESCRIPTION
NC	02/15/03	INITIAL RELEASE



RECOMMENDED
CABLE STRIPPING DIM'S

NOTE:

1. CRIMPED FERRULE
HEX CRIMP SIZE .213"
2. CENTER CONTACT TO SOLDER

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex						
8						DRAWN	G.R.S.	02/15/03								
7						CHECKED										
6						ISSUED				PART DESCRIPTION						
5	NUT	BRASS	NICKEL	1			SHEET	1 OF 1		BNC R/A CRIMP PLUG (FOR RG-58/U, 141/U CABLE)						
4	FERRULE	COPPER	NICKEL	1						PART NO.						
3	CONTACT PIN	BRASS	GOLD	1						112162						
2	INSULATOR	DELRIN	NATURAL	1						DWG. NO.						
1	BODY	BRASS	NICKEL	1					112162.DWG							
	DESCRIPTION	MATERIAL	FINISH	QTY			CAD FILE		C:/112/112162.DWG		REV.	NC	SIZE	A	SCALE	NA