

Heater Cord Type HPN

90°C 300 Volt UL/CSA Portable Cord



TYPE HPN - 300 VOLT - UL/CSA

CATALOG NUMBER	NO. OF COND.	AWG SIZE	COND. STRAND	NOMINAL INS. THICKNESS		NOMINAL O.D.		CURRENT AMPS	APPROX. NET WT. LBS/M ⁽¹⁾ (S)	STD. CTN.
				INCHES	mm	INCHES	mm			
25202	2	18	41/34	0.045	0.76	0.145 X 0.285	3.68 X 7.24	10	31	1000'
25212	2	16	65/34	0.045	1.14	0.155 X 0.300	3.94 X 7.62	15	38	1000'

^(S) Actual shipping weight may vary.

Product Construction:

Conductor:

- 18 through 16 AWG fully annealed stranded bare copper per ASTM B-174

Insulation/Jacket:

- Carolprene®, black
- Temperature range: -20°C to +90°C

Jacket Marking:

- CAROL (SIZE) (mm²) TYPE HPN (UL)
E# HEATER CORD (90°C) CSA LL# CPE
300 VOLT MADE IN USA

Applications:

- Portable heaters
- Toasters
- Irons
- Soldering irons
- Paint removers
- Other heat-related applications for industrial, commercial and home use

Features:

- Heat-resistant
- Oil-resistant

Industry Approvals:

- UL Listed
- CSA Certified

Packaging:

- 250' (76.2 m) spools
- Other put-ups available on special order