

## Honeywell Sensing and Control



Home > Products > Conductive Plastic Potentiometers > 53 > Product Page

### 53C22K

#### Order Product and Get Support

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- Test and Measurement Catalog
- RoHS Product List
- Customer Feedback



*Actual product appearance may vary.*

**53 Series Industrial Potentiometer, Conductive Plastic Element, Solder lug Terminals, 2 W Power Rating, 2 kOhm Resistance Value**

#### Features

Robust nickel-plated brass shaft and bushings  
Conductive plastic element  
Linear taper  
25,000 cycle rotational life  
Locking style bushing

#### Potential Applications

Manual controls (throttle, joystick)  
Electric vehicles  
Personal mobility  
Off-road vehicles  
Welding and heating  
Telecommunications

#### Description

The 53 Series is an economical potentiometer made with a rugged construction. It offers a 2 watt power rating and the benefits of a conductive plastic element. It is available in a special construction that accepts a rotary switch (purchased separately).

#### Supporting Documentation

None Available

#### My Links

- Login to iCOM
- Login as Rep/AD
- Login as Guest
- Login to Digital University

#### Keyword Search

Search for product and support information.

#### Product Search

Part number search:

Use (\*) to expand search

→ Specification Search

#### Product Specifications

Product Specifications	
Potentiometer Type	Industrial
Element Type	Conductive Plastic
Terminal	Solder lug
Power Rating	2 W
Resistance Value	2 kOhm
Resistance Tolerance	± 10 %
Linearity	± 5 %
Bushing Thread	9,53 mm [0.375 in] x 32 NEF-2A
Bushing Length	12,7 mm[0.5 in]
Bushing Type	Locking
Shaft Diameter	6,35 mm [0.25 in]
Shaft Length	15,88 mm [0.625 in]
Shaft Ending	Slotted
Body	27.8 mm [1.094 in] diameter max.

	except at terminal standoff
Electrical Taper	Linear
Operating Temperature	-55 °C to 120 °C [-67 °F to 248 °F]
Working Voltage (Max.)	500 V
Rotational Life	25000 cycles
Mechanical Rotation	312°
Availability	Global
Series Name	53
UNSPSC Code	4111363300
UNSPSC Commodity	4111363300 Potentiometers

[Terms & Conditions](#) | [Privacy Statement](#) | [Site Map](#)